

Part Number

XPB449-103MB1TL21

Basic, Non-Surge

Power Configuration

30A, 120/208V WYE, 8.6kW

Physical Configuration

66 in / 1682 mm Vertical

Description

The XPB449-103MB1TL21 non-surge unit is ideal for facilities already equipped with surge protection.

Product Summary

XPB449-103MB1TL21 - Non-Surge, 30A, 120/208V WYE, 3 Phase, Vertical, (36) IEC C13,(6) IEC C19,(2) NEMA 5-20R,breakered, 10 ft power cord with L21-30P

Monitoring

None

Plug Form



L21-30P

Receptacle



IEC C13 (Quantity: 36)



IEC C19 (Quantity: 6)



NEMA 5-20R (Quantity: 2)

XPB449-103MB1TL21 - Product Specification and Options

Quantity Of Inputs	1
Voltage	120/208V WYE
Current	30A x 3 Phase WYE
VA per Input (Load Capacity)	8.6kW
Frequency	50/60 Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/5
Power Cable Length	10ft
Plug Type	NEMA L21-30P Twistlock
Combined Total Receptacle/Socket Quantity	44
Receptacle/Socket Type #1	IEC C13
Quantity on Face #1	36
Quantity per Breaker and Phase Combination #1	12
Style #1	Banks of 6
Maximum Output per Receptacle/Socket #1	15A per receptacle bank
Voltage per Receptacle/Socket #1	208V
Receptacle/Socket Type #2	IEC C19
Quantity on Face #2	6
Quantity per Breaker and Phase Combination #2	2
Style #2	Individual
Maximum Output per Receptacle/Socket #2	20A
Voltage per Receptacle/Socket #2	208V
Receptacle/Socket Type #3	NEMA 5-20R
Quantity on Face #3	2
Quantity X Phase Only - #3	2
Style #3	Individual
Maximum Output per Receptacle/Socket #3	20A
Voltage per Receptacle/Socket #3	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	66in / 1682mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	NOM-003-SCFI-2000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Doghouse (D)	1.44in
Shipped Weight	18lbs (8.16kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2910,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 81764860
Email: salesasia@geistglobal.com