



Part Number 2XPR060-103L20TL5
 Basic, Non-Surge
 Power Configuration 30A, 120V, 2.8kW
 Physical Configuration 19 in / 483 mm Horizontal



Description	The 2XPR060-103L20TL5 non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	2XPR060-103L20TL5 - Non-Surge, 30A, 120V, Horizontal, (6) NEMA L5-20R, breakered, 10 ft power cord with L5-30P
Monitoring	None
Plug Form	 L5-30P
Receptacle	 NEMA L5-20R (Quantity: 6)



2XPR060-103L20TL5 - Product Specification and Options

Quantity Of Inputs	1
Voltage	120V
Current	30A
VA per Input (Load Capacity)	2.8kW
Frequency	50/60 Hz
Over Current Protection	(2) 20A Single Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L5-30P Twistlock
Receptacle/Socket Type #1	NEMA L5-20R
Quantity on Rear #1	6
Quantity per Breaker #1	3
Style #1	Individual
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	120V
Heavy Steel -Black Powder Coat	Yes
Configuration	19in / 435mm Horizontal Rackmount
19in Recess Mount	Yes
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	NOM-003-SCFI-2000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	3.39in x 17in x 6in
Shipped Weight	15lbs (6.8kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100
www.geisteurope.com

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com

Geist Asia

Hong Kong
Tel: +852 90361927

Email: salesasia@geistglobal.com