

VRELN100-103C13TL5

Part Number: VRELN100-103C13TL5
Category: Basic
Sub Category: Basic
Power Configuration: 30A, 120V, 2.8kW
Physical Configuration: 17 in / 432 mm, Horizontal/Vertical



Description: The VRELN100-103C13TL5 non-surge unit is ideal for facilities already equipped with surge protection.

Product Summary: VRELN100-103C13TL5, Basic, 30A, 120V, Horizontal/Vertical, (10) IEC C13, breakered, 10 ft power cord with L5-30P, Black Powder Coat.

Plug Form:



L5-30P

Receptacle:



IEC C13
(Quantity: 10)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com

Product Specification and Options:

Quantity Of Inputs	1
Voltage	120V
Current	30A
VA per Input (Load Capacity)	2.8kW
Frequency	50/60 Hz
Over Current Protection	(2) 15A Thermal Breakers
Switch	No
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L5-30P Twistlock
Receptacle/Socket Type #1	IEC C13
Quantity on Face #1	10
Quantity per Breaker #1	5
Style #1	Banks of 5
Maximum Output per Receptacle/Socket #1	15A per receptacle bank
Voltage per Receptacle/Socket #1	120V
Continuous Operating Temperature Range	10-45C / 50-113F
Heavy Steel - Powder Coat Finish	Black
Configuration	17in / 432mm Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed Accessory 1950
Chassis Dimensions (LxWxD)	17.00in x 1.72in x 1.61in
Shipped Weight	6lbs (2.72kg)

Geist Americas

800.432.3219
geistglobal.com

Geist DCIM
1.877.449.4150
geistglobal.com

Geist Europe

+44 (0) 1823.275100
geistglobal.com

Geist Asia

China
+86.755.86639505
geistglobal.com