





Part Number VRELAN080-103I44TL6
 Basic, Non-Surge
 Power Configuration 30A, 208V, 4.9kW
 Physical Configuration 17 in / 432 mm Horizontal/Vertical



Description	The VRELAN080-103I44TL6 non-surge unit is ideal for facilities already equipped with surge protection.
Product Summary	VRELAN080-103I44TL6 - Non-Surge, 30A, 208V, Horizontal/Vertical, (4) IEC C13,(4) IEC C19, breakered, 10 ft power cord with L6-30P, Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input, , Aggregate - Total Unit Monitoring
Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Plug Form	 L6-30P
Receptacle	 IEC C13 (Quantity: 4)  IEC C19 (Quantity: 4)

VRELAN080-103144TL6 - Product Specification and Options

Monitoring	Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	208V
Current	30A
VA per Input (Load Capacity)	4.9kW
Frequency	50/60 Hz
Over Current Protection	(4) 15A Thermal Breakers
Switch	No
Power Cable Wire Gauge	10/3
Power Cable Length	10ft
Plug Type	NEMA L6-30P Twistlock
Combined Total Receptacle/Socket Quantity	8
Receptacle/Socket Type #1	IEC C13
Quantity on Face #1	4
Quantity per Breaker #1	2
Style #1	Banks of 2
Maximum Output per Receptacle/Socket #1	15A per receptacle bank
Voltage per Receptacle/Socket #1	208V
Receptacle/Socket Type #2	IEC C19
Quantity on Face #2	4
Quantity per Breaker Pair #2	2
Style #2	Individual
Maximum Output per Receptacle/Socket #2	20A
Voltage per Receptacle/Socket #2	208V
Heavy Steel -Black Powder Coat	Yes
Configuration	17in Vertical/Horizontal Rackmount
19in Panel Mount Brackets	Yes
SLB-4 Brackets	Yes
Made in the USA	Yes
Product Warranty	Three Year
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed Accessory 1950
Chassis Dimensions (LxWxD)	17.0in x 1.72in x 1.85in
Shipped Weight	7lbs (3.18kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,

Geist Asia

Hong Kong
Tel: +852 90361927

Email: salesasia@geistglobal.com

www.geistglobal.com

+44 (0) 1823 275100
www.geisteurope.com

Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com