





## XPB128-103L20TL15 - Product Specification and Options

Quantity Of Inputs	1
Voltage	208V Delta
Current	30A x 3 Phase DELTA
VA per Input (Load Capacity)	8.6kW
Frequency	50/60 Hz
Over Current Protection	(3) 20A Double Pole Magnetic Breakers
Switch	Breaker/Switch Combination
Power Cable Wire Gauge	10/4
Power Cable Length	10ft
Plug Type	NEMA L15-30P Twistlock
Receptacle/Socket Type #1	NEMA L6-20R
Quantity on Face #1	12
Quantity per Breaker and Phase Combination #1	4
Style #1	Individual
Maximum Output per Receptacle/Socket #1	20A
Voltage per Receptacle/Socket #1	208V
Heavy Steel -Black Powder Coat	Yes
Configuration	66in / 1682mm Vertical Rackmount
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in
Made in the USA	Yes
Product Warranty	Lifetime
Certification/Agency Approvals	NOM-003-SCFI-2000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (LxWxD)	66.25in x 2.0in x 2.0in
Doghouse (D)	1.44in
Shipped Weight	17lbs (7.71kg)

### Geist Americas

1821 Yolande Ave  
Lincoln, NE 68521 USA  
1.800.432.3219 or  
1.402.474.3400  
www.geistglobal.com

### Geist Europe

Unit 1, The Monarch Centre,  
Venture Way,  
Priorswood, Taunton,  
Somerset, TA2 8DE UK  
+44 (0) 1823 275100  
www.geisteurope.com

### Geist Asia

China  
Tiley Plaza Bldg. A, Unit #2808,  
No. 199 Haide 3 Road,  
Nanshan Shenzhen,  
Guangdong Province, China.  
Postal Code: 518000  
Tel: +86.755.86639505  
www.geistglobal.com

### Geist Asia

Hong Kong  
Tel: +852 90361927  
Email: salesasia@geistglobal.com