



## Line Array Speakers - Amplified - Wired/UHF Wireless PA

One lightweight, slim, compact line array design. Three different systems; Passive (non-powered) extension speaker, Amplified speaker with a built-in 30 Watt amplifier and a Neutrik combo microphone connector, lastly a Amplified speaker with built-in 30 Watt amplifier and a 16 channel wireless microphone kit. All can be mounted either horizontal or vertically. Mounting bracket included.

**New!**

### General:

Dimensions: 17" L x 3.4" H x 5.0" D

Weight: 4.5 lbs

Bracket: "C" shape for wall or frame mounting,  
"L" for rackmount

Case Color: Gray or Black



HORIZONTAL MOUNT



Speakers mount easily to  
a whiteboard or cart.



### Model S1234 – Passive Speaker

Enclosure: Sealed Type / Rotational Molded  
Power Handling: 30 Watts  
Rated Impedance: 4 ohm  
Frequency Response: 400 – 12,000 Hz  
Speaker Type: 2 inch, full range, cone-type x 6  
Input Connector: 1 – Spring Loaded Speaker Terminal  
Enclosure Color: Silver Gray  
Grille: Perforated / Black

### Model SS1234 – 50 W. Amplified Speaker with Wired Microphone (Same as above with the addition of amplifier)

Amplifier: 50 Watts  
Inputs: 1 – RCA, Audio  
1 – 1/4" Microphone Jack  
1 – 3.5mm Line Level  
1 – 12V DC  
1 – Spring Loaded Speaker Terminal  
Outputs: 1 – 3.5mm Line Level  
Controls: Volume / On / Off

### Model SW1234 – 16 Channel UHF Wireless Microphone / Amplified Speaker

(Same as SS model with addition of a 16  
channel UHF wireless microphone)

	Model #	Ship Weight	MSRP
Line Array Speaker Sealed Type/Rotational Molded	S1234	.5 lbs.	\$329.00
Line Array Speaker 50 W. Amplified Speaker with Wired Microphone (Same as above with the addition of amplifier)	SS1234	.5 lbs.	\$449.00
Line Array Speaker (Same as above with addition of a 16 channel UHF wireless microphone)	SW1234	.6 lbs.	\$599.00