



2016 Manual SRM Series Product Brochure

The Manual SRM series front projection screen has a special built-in Slow Retract Mechanism to allow a safe and quiet return to the screen's housing.




Member



Manual SRM Series



The Manual SRM series front projection screen has a special built-in Slow Retract Mechanism to allow a safe and quiet return to the screen's housing.



Screen Material:

- MaxWhite™ 1.1 Gain Screen Material is durable and easy to clean
- 180° wide viewing angle for commercial and residential presentations
- Black backed screen material eliminates light penetration for superior color reproduction
- Black masking enhances picture contrast

Casing and Installation:

- Durable metal casing
- Dual wall and ceiling installation design
- Includes wood screws and drywall anchors
- Optional 6" and 12" brackets available

Control System:


- Slow Retract Mechanism (SRM)- Retracts slowly back into housing after releasing handle without the need to hold on to handle
- Auto-locking mechanism with variable height settings
- Manually operated (lanyard included)
- Automatically retracts into housing hands-free

Warranty:

- 2-year parts and labor
- 3-year warranty for ENR-G (Educational, Non-profit, Religious or Government/Military) - US only

Certified

- GREENGUARD® and GREENGUARD® Gold Certified UL | 2818



ZVMAXLB6-B: Black 6" L Bracket Set
ZVMAXLB6-W: White 6" L Bracket Set

Manual SRM Series: Slow Retract Manual Pull Down Projector Screen

Model	Nominal Diagonal	View Height (in)	View Width (in)	View Height (cm)	View Width (cm)	Net Weight (lbs)	Gross Weight (lbs)	Net Weight (kgs)	Gross Weight (kgs)	Packaging Dimension (LxHxW)	Gain	Screen Material	Case Color
M85XWS1-SRM	85"(1:1)	60.0	60.0	152.4	152.4	13.2	16.1	6.0	7.3	69"x4.3"x5"	1.1	MaxWhite™	White
M99NWS1-SRM	99"(1:1)	70.0	70.0	177.8	177.8	15.7	18.5	7.1	8.4	80.3"x4.3"x5"	1.1	MaxWhite™	White
M113NWS1-SRM	113"(1:1)	80.0	80.0	203.2	203.2	18.1	21.8	8.2	9.9	90.2"x5.2"x5.6"	1.1	MaxWhite™	White
M84NWX-SRM	84"(4:3)	50.3	67.0	127.8	170.2	13.5	16.2	6.2	7.4	77.6"x5.5"x5.5"	1.1	MaxWhite™	White
M100NWX-SRM	100"(4:3)	60.0	80.0	152.4	203.2	16.8	20.3	7.6	9.2	88.2"x4.3"x5"	1.1	MaxWhite™	White
M120XWV2-SRM	120"(4:3)	72.0	96.0	182.9	243.8	20.5	24.3	9.3	11.1	106.3"x5.5"x5.9"	1.1	MaxWhite™	White
M100XWH2-SRM	100"(16:9)	49.0	87.0	124.5	221.0	17.4	21.2	7.9	9.6	97.6"x 5.5"x5.5"	1.1	MaxWhite™	White
M120XWH2-SRM	120"(16:9)	58.8	104.6	149.4	265.7	21.2	25.7	9.6	11.7	115"x 5.5"x5.5"	1.1	MaxWhite™	White
M94NWX-SRM	94"(16:10)	49.8	79.7	126.5	202.4	15.0	18.3	33.1	40.3	90.15"x5.51"x5.51"	1.1	MaxWhite™	White
M113NWX-SRM	113"(16:10)	60.0	96.0	152.4	243.8	18.7	22.1	41.2	48.6	106.3"x5.51"x5.51"	1.1	MaxWhite™	White

Manual SRM Series Dimensions Table

Model	Screen Diag. & Aspect Ratio	Case Length (A)	Screen Width (A2)	View Width (A1)	Weight Bar Length (A3)	Screen Material to Bottom Bar (B4)	B3	View Height (B1)	Overall Height (B)	End cap Height (B5)	End cap Width (C)	Top Masking Border (B2)	Screen material to Wall (C1)
M85XWS1-SRM	85" (1:1)	1688	1603	1527	1684	62	1703	1527	1795	92	79.5	114	20
M99NWS1-SRM	99" (1:1)	1940	1854	1778	1936	62	1954	1778	2046	92	79.5	114	20
M113NWS1-SRM	113" (1:1)	2195	2106	2030	2191	62	2206	2030	2298	92	79.5	114	20
M84NWX-SRM	84" (4:3)	1870	1783	1707	1866	62	1456	1280	1548	92	79.5	114	20
M100NWX-SRM	100" (4:3)	2194	2108	2032	2190	62	1700	1524	1792	92	79.5	114	20
M120XWV2-SRM	120" (4:3)	2610	2514	2438	2606	62	2005	1829	2097	92	79.5	114	20
M100XWH2-SRM	100"(16:9)	2376	2290	2214	2372	62	1421	1245	1513	92	79.5	114	20
M120XWH2-SRM	120"(16:9)	2818	2733	2657	2814	62	1670	1494	1762	92	79.5	114	20
M94NWX-SRM	94"(16:10)	2195	2101	2024	2191	62	1441	1265	1533	92	79.5	114	20
M113NWX-SRM	113"(16:10)	2610	2510	2434	2606	62	1697	1521	1789	92	79.5	114	20

Unit: mm

Model	Screen Diag. & Aspect Ratio	Case Length (A)	Screen Width (A2)	View Width (A1)	Weight Bar Length (A3)	Screen Material to Bottom Bar (B4)	B3	View Height (B1)	Overall Height (B)	End cap Height (B5)	End cap Width (C)	Top Masking Border (B2)	Screen material to Wall (C1)
M85XWS1-SRM	85" (1:1)	66.5	63.1	60.1	66.3	2.4	67.0	60.1	70.7	3.6	3.1	4.5	0.8
M99NWS1-SRM	99" (1:1)	76.4	73.0	70.0	76.2	2.4	76.9	70.0	80.6	3.6	3.1	4.5	0.8
M113NWS1-SRM	113" (1:1)	86.4	82.9	79.9	86.3	2.4	86.9	79.9	90.5	3.6	3.1	4.5	0.8
M84NWX-SRM	84" (4:3)	73.6	70.2	67.2	73.5	2.4	57.3	50.4	60.9	3.6	3.1	4.5	0.8
M100NWX-SRM	100" (4:3)	86.4	83.0	80.0	86.2	2.4	66.9	60.0	70.6	3.6	3.1	4.5	0.8
M120XWV2-SRM	120" (4:3)	102.8	99.0	96.0	102.6	2.4	78.9	72.0	82.6	3.6	3.1	4.5	0.8
M100XWH2-SRM	100"(16:9)	93.5	90.2	87.2	93.4	2.4	55.9	49.0	59.6	3.6	3.1	4.5	0.8
M120XWH2-SRM	120"(16:9)	110.9	107.6	104.6	110.8	2.4	65.7	58.8	69.4	3.6	3.1	4.5	0.8
M94NWX-SRM	94"(16:10)	86.4	82.7	79.7	86.3	2.4	56.7	49.8	60.4	3.6	3.1	4.5	0.8
M113NWX-SRM	113"(16:10)	102.8	98.8	95.8	102.6	2.4	66.8	59.9	70.4	3.6	3.1	4.5	0.8

Unit: inch

Note: Data Error ±1". The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

