

15m / 50 ft Active USB 2.0 A to B Cable - M/M

StarTech ID: USB2HAB50AC



The USB2HAB50AC 50ft / 15m USB A to B cable incorporates bus-powered active circuitry, which enables it to perform beyond the 5-meter limit of a standard USB cable.

The longer connection provides enough cable length to connect your USB 2.0 peripherals up to 15m away from your PC, Laptop or Server, allowing you to position your devices as needed.

This active USB 2.0 cable is designed with top quality materials for high durability, and is backed by StarTech.com's 2-year warranty.

Applications

• Connect a USB Type B peripheral (hard drive enclosure, printer, keyboard, mouse, modem, etc.) up to 50ft away from your PC, Laptop or Server – beyond the USB 2.0 5-meter limitation

Features

- 1x USB 'A' male connector
- 1x USB 'B' male connector
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered, no external power source required
- Aluminum-Mylar Foil with Braided Shielding
- Compatible with PC Windows® 8/7/Vista/XP and Mac computer systems





Technical Specifications

Warranty 2 Years
Connector Plating Nickel

Cable Jacket Type PVC - Polyvinyl Chloride

Cable Shield Type Aluminum-Mylar Foil with Braid

Connector A 1 - USB A (4 pin) Male
Connector B 1 - USB B (4 pin) Male
Type and Rate USB 2.0 - 480 Mbit/s

Cable Length 49.2 ft [15 m]

Color Black
Connector Style Straight

Product Length 49.2 ft [15 m]
Product Weight 21.4 oz [607 g]

Wire Gauge 24 AWG

Package Quantity 1

Shipping (Package) Weight 26.5 oz [751 g]

Included in Package 1 - 50 ft 15m Active USB 2.0 A to B Cable - M/M

Certifications, Reports and Compatibility





