

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Protect It! 6-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 990 Joules, Low-Profile Right-Angle 5-15P plug

MODEL NUMBER: TLP608











Features

- 990 joules AC surge suppression shields equipment from the strongest surges and line noise
- 6 AC outlets with room for 1 transformer plugs without blocking outlets covers computers and

peripherals

- 8 foot AC line cable
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Right angle flat plug
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm surge suppression status
- Attractive gray suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 3rd Edition Rated (500V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

Highlights

- 6 outlets / 8-ft. cord
- 990 joule rating

Package Includes

- TLP608
- Instruction manual with warranty information



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

OVERVIEW		
UPC Code	037332177025	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	35500	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	8	
Right-Angle Plug	Yes	
Input Cord Length (m)	2.44	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	60 Hz	
Output (Watts)	1800	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Outlet Orientation	Single row	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch	
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	990	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression	
Clamping Voltage (RMS)	150	
UL1449 Let Through Rating	500V	
EMI / RFI Filtering	Up to 20 dB	



Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection	No	
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
PHYSICAL		
Color	Light Gray	
Antimicrobial Coating	No	
Color (AC Line Cord)	Light Gray	
Housing Color	Cool Grey 2C	
Integrated Keyhole Mounting Slots	Yes	
Keyhole Slot Mounting Measurement (Center to Center)	Distance between slots = 101mm; Distance between slot height = 28mm	
Material of Construction	Plastic	
Outlets Measurement (Center to Center)	28.5mm	
Receptacle Color	Light gray	
Shipping Dimensions (hwd / cm)	30.99 x 4.57 x 14.99	
Shipping Dimensions (hwd / in.)	12.20 x 1.80 x 5.90	
Shipping Weight (kg)	0.64	
Shipping Weight (lbs.)	1.41	
Unit Dimensions (hwd / cm)	27.43 x 4.70 x 3.12	
Unit Dimensions (hwd / in.)	10.80 x 1.85 x 1.23	
Unit Weight (kg)	0.51	
Unit Weight (lbs.)	1.12	
SPECIAL FEATURES		
Rotatable Outlets	No	
STANDARDS & COMPLIANCE		
Canada	cUL	
Approvals	Exceeds IEEE 587 category A&B specifications	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION	
UL1363 (Power Tap)	UL1363	
UL497A (Communications)	UL497A	



FCC Part 68 (Communications)	FCC Part 68
Industry Canada (Communications)	Industry Canada
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies