

## USB 3.0 External Flash Multi Media Memory Card Reader – SDHC MicroSD

StarTech ID: FCREADMICRO3



The FCREADMICRO3 USB 3.0 Multi-media Card Reader offers quick access to the most popular flash card formats, from any computer with a USB port (optimal performance with 3.0, backward compatible with USB 2.0).

Suitable for quickly accessing memory cards of virtually any portable media device (e.g. digital cameras, MP3 players, etc.), this versatile media card reader supports the most popular card types, including:

- Secure Digital (SD)
- Multi-Media Card (MMC)
- Mini-SD, Micro-SD/SDHC (T-flash)
- SDHC
- SDXC
- RS-MMC
- Mobile-MMC and MMC-micro
- Memory Stick (MS)
- Memory Stick PRO (MS-PRO)
- MS Duo
- MS-PRO Duo
- Memory Stick XC
- Micro-MS (M2)
- MSPRO-HG Duo 8-bit mode.

An ideal Laptop or Desktop accessory, this pocket-sized memory card reader is lightweight, portable, and backed by a StarTech.com 2-year warranty with free lifetime technical support.





#### **Applications**

- Mobile users/travelers who need a compact and lightweight card reader small enough to fit in a pocket
- Photographers who need to regularly transfer files from their camera memory card to a computer
- Transferring files to and from a variety of portable devices, each using a different memory card format

#### **Features**

- High Speed USB 3.0 host interface with support for transfer rates up to 5 Gbps
- Support for Secure Digital (SD), MultiMedia Card (MMC), Mini-SD, Micro-SD/SDHC (T-flash), SDHC, SDXC, RS-MMC, Mobile-MMC and MMC-micro, Memory Stick (MS), Memory Stick PRO (MS-PRO), MS Duo, MS-PRO Duo, Memory Stick XC, Micro-MS (M2), and MSPRO-HG Duo 8-bit mode
- Ultra-compact and lightweight design
- Powered directly from the USB port
- Plug-and-Play and Hot-Swap compatible





#### **Technical Specifications**

Warranty 2 Years Bus Type USB 3.0

Chipset ID Realtek RTS5307

Interface USB 3.0

Connector Type(s) 1 - USB 3.0 A (9 pin; SuperSpeed) Male

External Ports 1 - Memory Stick / Memory Stick Pro Slot Female

External Ports 1 - Memory Stick Duo / Memory Stick Pro Duo Slot Female

External Ports 1 - Memory Stick Micro (M2) Slot Female

External Ports 1 - MiniSD / MicroSD / MMC Slot Female

External Ports 1 - SD / MMC Slot Female

External Ports 1 - SFF-8482 (29 pin; Data & Power; Internal SAS) Female

Maximum Data 5 Gbit/s

Transfer Rate

Memory Media Type HS-MMC, HC-MMC (High Speed/High Capacity Multimedia Card)

Memory Media Type M2 (Memory Stick Micro)

Memory Media Type Memory Stick

Memory Media Type Micro-SDHC (Micro Secure Digital High Capacity)
Memory Media Type Mini-SD, Micro-SD (Mini/Micro Secure Digital)

Memory Media Type MS Duo, MS Pro Duo, MS Pro-HG Duo

Memory Media Type Multi Media Card

Memory Media Type RS-MMC (Reduced Size Multimedia Card)
Memory Media Type SD/MMC (Secure Digital/Multimedia Card)

Memory Media Type SDHC (Secure Digital High Capacity)

OS Compatibility Windows 2000/ XP(32/64-bit)/ Server 2003(32/64-bit)/ Server 2008 R2/ Vista(32/64-bit)/

7(32/64-bit)/ 8 (32/64-bit)

Mac OSX

Linux kernel 2.4.x or later

Color Black Enclosure Type Plastic

Product Height 0.6 in [15 mm]
Product Length 2.8 in [72 mm]
Product Weight 0.5 oz [15 g]
Product Width 0.9 in [23 mm]
Power Adapter USB-Powered

Included





# Hard-to-find made easy®

Humidity < 80% R.H.

Operating 0°C to 40°C (32°F to 104°F)

Temperature

Storage Temperature -20°C to 60°C (-4°F to 140°F)

Shipping (Package) 3.4 oz [95 g]

Weight

Included in Package 1 - USB 3.0 Multi Media Memory Card Reader Adapter

Included in Package 1 - Instruction Manual

### Certifications, Reports and Compatibility











