

Tensioned Large Advantage Deluxe Electrol

For larger venue installs, the Tensioned Large Advantage® Deluxe Electrol® is designed to eliminate the extra step of finishing the screen with trim. The Advantage line of projection screens is designed with ceiling trim already in place. Once the screen is installed, the screen's trim conceals the rough opening eliminating the need to complete additional trim work.

Sliding installation brackets make it easy to attach the screen housing to the structure above the drop ceiling.

Tensioned screens ensure the smoothest surface possible, and all Deluxe screens feature a closure door that hides the open space and screen in the ceiling, providing a cleaner aesthetic.

The screen features simple in ceiling installation that can be done in two stages. The screen case can be installed during the rough-in construction stage and the fabric assembly can be completed during the finishing stage.

Features

- Standard Low Voltage Control (LVC) to keep your screen operation flexible
- Smooth Roll Technology to keep your screen perfectly flat
- Slim-Tab, a lower profile and stronger tab design to keep your screen perfectly taut
- Tensioning Cable System to prevent warping and ensure even lateral tension
- UL Plenum rated case
- White powder-coated closure doors and case for a clean aesthetic
- Decora-style, three-button wall switch
- Standard black backing retains projected brightness on front projection surfaces
- Seamless surfaces in all models

Optional Accessories:

- Radio Frequency Wireless Remote
- Infrared Wireless Remote
- Locking Switch Cover Plate
- Red Laser Pointers
- Green Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer



16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
108" x 192"	274 x 488	220"	559	220¾"	561
121" x 216"	307 x 549	247"	627	246½"	627
135" x 240"	343 x 610	275"	699	272½"	693
146" x 260"	371 x 660	298"	757	294¼"	747

16:10 Wide Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
110" x 176"	279 x 447	208"	528	205"	521
120" x 192"	305 x 488	226"	574	222¼"	565

4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
126" x 168"	320 x 427	210"	533	199¼"	506
132" x 176"	335 x 447	220"	559	208¼"	529
144" x 192"	366 x 488	240"	610	225¾"	573
162" x 216"	411 x 549	270"	686	251¼"	638

Available with the Following Screen Surfaces



HD Progressive 0.9
Half Angle: 85° Gain: 0.9



HD Progressive 1.1
Half Angle: 85° Gain: 1.1



HD Progressive 1.3
Half Angle: 75° Gain: 1.3



Da-Mat
Half Angle: 60° Gain: 1.0



High Contrast Da-Mat
Half Angle: 45° Gain: 0.8



Cinema Vision
Half Angle: 45° Gain: 1.3



High Contrast Cinema Vision
Half Angle: 50° Gain: 1.1



Pearlescent
Half Angle: 40° Gain: 1.5



Dual Vision
Half Angle: 65° Gain: 0.9



Da-Tex
Half Angle: 30° Gain: 1.3

Product images



Case Profile



In Ceiling (Closed)



In Ceiling (Open)



A Milestone AV Technologies Brand

3100 North Detroit Street
Warsaw, Indiana 46582
P: 574.267.8101 or 800.622.3737
F: 574.267.7804 or 877.325.4832
E: info@da-lite.com
www.da-lite.com

DL-O416 07:14
© 2014 Milestone AV Technologies LLC. Printed in U.S.A.