


**ECONOMY / BASIC LCD**



# 17RCE

BUILT TO RUN 24 X 7 X 365 CONTINUOUSLY

## OVERVIEW

The ORION 17RCE LCD CCTV series is commercial grade - built to run 24 x 7 x 365 continuously. The RCE series offers versatility with multiple input under economy value and can be used for both security and industrial solutions.

## FEATURES

- 17 Inch Screen Size
- 1280 x 1024 Native Display Resolution
- BNC Video 2 In / 1 Out, HDMI 1 In, VGA 1 In, Audio 1 In / 1 Out
- 6ms, 350 Nits, 500:1 Contrast
- 4:3 Aspect Ratio
- 2W x 2 Built-In Speakers
- Mount Options: Wall, Ceiling or Rack



### SPECIFICATIONS

17RCE	
<b>Display</b>	
Screen Size	17 Inch
Max. Resolution	1280 x 1024 @ 75Hz
Pixel Pitch	0.264 x 0.264mm
Brightness	350cd/m <sup>2</sup>
Contrast Ratio	500 : 1
Aspect Ratio	4 : 3
Viewing Angle (H/V)	160° / 140°
Display Color	16.2 Million
Response Time	< 6ms
Video System	NTSC / PAL
<b>Interface</b>	
Video In / Out (BNC Type)	2 In / 1 Out
HDMI In	1 In
VGA In (15Pin D-Sub)	1 In
Audio In (RCA Type)	1 In
Audio Out	1 Out
<b>Transmitter</b>	
Remote Control	Yes
<b>Audio</b>	
Built-in Speakers	Yes
<b>Features</b>	
Filter Type	2D Comb Filter
Multi Language	English, Chinese
<b>General</b>	
Outline Dimension (W x H x D)	15.04" x 12.46" x 1.71"
Net Weight	7.37 lbs
Material / Color	ABS Plastic / Black
Desk Top Stand	Tilt Back
Part / Labor	3year / 3year
Consumption: < On	< 35W
	AC100 ~ 240V(50/60Hz)
Electrical Ratings	DC12V / 4A
Operating Temperature	0 ~ 40°C / 32 ~ 104°F
Storage Temperature	-20 ~ 60°C / -4 ~ 140°F
<b>Mounts</b>	
VESA™ Mount Size	75 x 75mm
Wall	WB-5, WB-10, WB-30, WB-31
Ceiling	CMK-01
Rack	RMK-08


\*Design and specifications are subject to change without notice

### TILT CAPABILITY


RCE series has flexible tiltable desktop stand capability



### INPUT INTERFACE



### DIMENSIONS



### OPTIONAL MOUNTS

