

Mini USB Bluetooth® 4.0 Adapter - 50m (165ft) Class 1 EDR Wireless Dongle

StarTech ID: *USBBT1EDR4*



The USBBT1EDR4 USB to Class 1 Mini Bluetooth® Dongle lets you add Bluetooth wireless capabilities to a laptop or desktop computer through USB, with support for transfer distances of up to 50m (165ft).

Compliant with Bluetooth 4.0 LE +EDR, the USB Bluetooth adapter offers data transfer rates up to 3 Mbps and low power consumption. This Bluetooth Smart Ready transceiver is an effective way to connect to a rapidly growing list of the Bluetooth Smart peripherals on the market, including the latest Apple® and Android smartphones and tablets. Bluetooth v4.0 also integrates added security for all transfers using 128-bit AES encryption.

A conveniently portable device, this ultra-compact adapter is unobtrusive when connected to your laptop, so you won't have to remove it each time you store your laptop in a carrying case or bag. The adapter is also backward compatible with previous Bluetooth standards (v3.0, 2.0, 1.2 and 1.1) to ensure connectivity with all of your Bluetooth devices.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Connect Bluetooth peripherals such as keyboard/mouse or smart phones to your computer system
- Reduce cable clutter by using wireless Bluetooth devices (such as keyboard/mouse) instead of traditional wired devices
- Connect peripherals wirelessly to a computer in a remote/secure location
- Connect peripherals in an industrial setting where the computer can be kept away from the work areas

Features

- Bluetooth® 4.0 LE compliant Bluetooth Smart Ready transceiver
- Class 1 device with 50m (165ft) effective range
- Support for Enhanced Data Rate (EDR) with data transfer rates up to 3 Mbps
- Low power consumption
- Ultra-compact form factor
- Backward compatible with Bluetooth v3.0, 2.0, 1.2 and 1.1 devices
- Power / Linking / Standby LED indicator

Technical Specifications

Warranty	2 Years
Bus Type	USB 2.0
Chipset ID	CSR - CSR8510A06
Industry Standards	Bluetooth v4.0, v3.0, EDR
Connector Type(s)	1 - Bluetooth Class 1.0
Connector Type(s)	1 - USB A (4 pin) Male
Frequency	2.402-2.48GHz ISM Band
Max Distance	50 m / 165 ft
Maximum Data Transfer Rate	3 Mbps
Modulation	GFSK,p/4 DQPSK, 8DPSK
OS Compatibility	Windows® 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows® Server 2008 R2, 2003(32/64) Mac OS 10.x, 9.x
Color	Black
Enclosure Type	Plastic
Product Height	0.2 in [5.5 mm]
Product Length	0.9 in [21.9 mm]
Product Weight	0.1 oz [3 g]
Product Width	0.6 in [14.4 mm]
LED Indicators	1 - Power / Standby / Link
Power Adapter Included	USB-Powered
Humidity	0~75% RH
Operating Temperature	-10°C to 50°C (14°F to 122°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
System and Cable Requirements	Available USB port
Shipping (Package) Weight	2.6 oz [75 g]
Shipping (Package) Weight	3.5 oz [100 g]
Included in Package	1 - USB Bluetooth Adapter
Included in Package	1 - Driver DVD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

