

HD 1080p LED Monitor

M19LED 19" LED monitor

M215LED 21.5" LED monitor


Features

- Flat-panel LED - backlit LCD
- HDMI, VGA (D-Sub 15 pins) and BNC video inputs
- 1920(H) x 1080(V) HD 1080p resolution
- Built-in speakers
- Convenient front controls for screen programming
- Input signal detection provides easy connection
- 290cd/m2 brightness
- 16:9 display ratio
- 500:1 contrast ratio
- Displays up to 16.7 million colors
- Regulated 12VDC 5.0 amp (UL & CSA listed power supply included)
- VESA compatible
- 1 year warranty




ECO-FRIENDLY - LOW ENERGY CONSUMPTION
GREENER THAN LCDs

Specifications	M19LED	M215LED
Composite Output	BNC 1	
Composite Input	BNC 1	
Single Connector	VGA x 1, RCA x 2, PC Audio x 1, HDMI x 1	
Speaker	1W+1W	
Display Mode	VGA / BNC / PC / HDMI	
AC Power	AC 100 - 240V 50/60Hz	
Operating Temperature	14° F – 122° F	
Storage Temperature	-4° F – 140° F	
Power Consumption	20W	25W
OSD Control	HDMI, VGA, Audio, PIP, System	
OSD Languages	English	
Auto Adjustment	Yes	
De-interlace	Yes	
Wall Mount	Optional	
Accessories	Remote, Adaptor, Power Cord, Manual, VGA cable, PC Audio Cable	
Safety	FCC, CE, RoHS	
Tilt	10° – 15°	
Humidity	20% – 85%	
Monitor Scan	Microprocessor controlled	
Pixel Pitch	0.24825 (H) x 0.24825 (V)	
Pixel Format	1920 x 1080	
Response Time	5ms	
Color Depth	16.7 million colors	
Viewing Angle	Left 85° / Right 85° / Up 80° / Down 80° CR > 10	
Display Area	16.13" (H) x 9.07" (V)	18.41" (H) x 10.56" (W)
Dimensions	17.44" (W) x 13.70" (H) x 2.17" (D)	20.31" (W) x 16.20" (H) x 2.38" (D)
Weight	6.17 lbs.	7.94 lbs.



M215LED



M19LED

Optional Accessory



LCDVLW2
10" Extension Arm