

4 ft Heavy Duty 14 AWG Computer Power Cord - NEMA5-15P to C15

StarTech ID: PXT515C154



The PXT515C154 4-foot Computer Power Cord features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to NEMA 5-15P Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this 5-15P to C15 power cable is backed by our Lifetime Warranty.

Applications

- Compatible with Cisco, HP and other hardware devices with C15 power connections
- Connect large servers to PDUs, even in high-temperature environments

Features

- 1x NEMA 5-15 Plug
- 1x IEC 60320 C15 connector
- Rated to carry 125V at 15A
- 14 AWG wire
- UL, RoHS compliant
- Fully molded strain relief connectors
- Temperature Rating of 105°C

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Type	SJT
Number of Conductors	3
Connector A	1 - NEMA 5-15 Power (North America) Plug
Connector B	1 - IEC 60320 C15 Power
Cable Length	4 ft [1.2 m]
Color	Black
Product Length	4 ft [1.2 m]
Product Weight	8 oz [226 g]
Wire Gauge	14 AWG
Input Current	15 A
Input Voltage	125 AC
Package Quantity	1
Shipping (Package) Weight	8 oz [227 g]
Included in Package	1 - 4 ft Heavy Duty Computer Power Cord - NEMA5-15P to C15

Certifications, Reports and Compatibility

