

# WorkForce WF-7110DTW



## DATASHEET



This business printer with Wi-Fi and Ethernet connectivity is ideal for printing A3 documents on a regular basis. It helps increase office efficiency with its fast business-quality print speeds of up to 18ppm<sup>1</sup>, 5.6cm LCD screen and two 250-sheet front-loading paper trays. You can also cut printing costs with XXL black ink which delivers a yield of up to 2,200 pages<sup>2</sup>.

### A3 duplex printing

This A3 business printer offers A3 duplex printing for more convenient office printing. As well as the front loading paper trays, the rear speciality paper path means you can print on a wide range of thicker paper, envelopes or labels to suit your business needs.

### Mobile printing

Epson Connect<sup>3</sup> allows you to print important office documents from smartphones and tablets. You can also print from anywhere in the world by emailing files directly to the printer. In addition, this printer is also Google Cloud Print and Apple AirPrint compatible. For added versatility, Wi-Fi Direct™ allows easy printing from wireless devices without having to connect to a wireless router.

### New printhead


PrecisionCore, Epson's most advanced printhead technology, powers the industry-leading output quality and durability that Epson is renowned for, at the high speeds required for office, commercial and industrial printing.

### Durable ink

Epson's DURABrite Ultra Ink is ideal for producing laser-like business documents. Documents are water, smudge and highlighter resistant, while its quick-drying properties make it perfect for duplex printing. Available in 27XXL, 27XL and standard sizes, these high-capacity, individual ink cartridges offer great savings, with a 50% lower cost-per-page than competitive lasers<sup>4</sup>.

## KEY FEATURES

- **A3 duplex printer**  
Print A3-sized business documents
- **Fast print speeds**  
Business-quality 18ppm printing<sup>1</sup>
- **Connectivity**  
Wi-Fi, Wi-Fi Direct and Ethernet
- **Dual paper trays**  
Two A3 250-sheet capacity trays
- **Epson Connect**  
Freedom to print from anywhere



## PRODUCT SPECIFICATIONS

|                               |                                                                                                                                                                                                                                                                                                                       |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>TECHNOLOGY</b>             |                                                                                                                                                                                                                                                                                                                       |
| Printing Method               | PrecisionCore™ Print Head                                                                                                                                                                                                                                                                                             |
| Minimum Droplet Size          | 2.8 pl                                                                                                                                                                                                                                                                                                                |
| Ink Technology                | DURABrite™ Ultra                                                                                                                                                                                                                                                                                                      |
| <b>PRINT</b>                  |                                                                                                                                                                                                                                                                                                                       |
| Printing Speed ISO/IEC 24734  | 18 Pages/min Monochrome, 10 Pages/min Color                                                                                                                                                                                                                                                                           |
| Printing Resolution           | 4,800 x 2,400 dpi                                                                                                                                                                                                                                                                                                     |
| Max Duty cycle                | 20,000 Pages per month                                                                                                                                                                                                                                                                                                |
| Colours                       | Black, Cyan, Yellow, Magenta                                                                                                                                                                                                                                                                                          |
| <b>CONNECTIVITY</b>           |                                                                                                                                                                                                                                                                                                                       |
| Interfaces                    | Hi-Speed USB - compatible with USB 2.0 specification, Ethernet interface (100 Base-TX / 10 Base-T), Wireless LAN IEEE 802.11b/g/n, Wi-Fi Direct                                                                                                                                                                       |
| WLAN Security                 | WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)                                                                                                                                                                                                                                                                |
| <b>PAPER / MEDIA HANDLING</b> |                                                                                                                                                                                                                                                                                                                       |
| Paper Formats                 | A3+, A3, A4, A5, A6, B4, B5, C4 (Envelope), C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, 9 x 13 cm, 10 x 15 cm, 13 x 18 cm, 16:9, User defined, Legal                                                                                                                                                     |
| Duplex                        | Yes                                                                                                                                                                                                                                                                                                                   |
| Paper Tray Capacity           | 500 Sheets Standard, 500 Sheets maximum                                                                                                                                                                                                                                                                               |
| Number of paper trays         | 2                                                                                                                                                                                                                                                                                                                     |
| <b>GENERAL</b>                |                                                                                                                                                                                                                                                                                                                       |
| Energy Use                    | 1.5 W (sleep mode), 22 W (printing), 5.8 W (Ready), 0.3 W (Power off), ENERGY STAR® qualified all-in-one                                                                                                                                                                                                              |
| Product dimensions            | 567 x 424 x 304 mm (Width x Depth x Height)                                                                                                                                                                                                                                                                           |
| Product weight                | 14.9 kg                                                                                                                                                                                                                                                                                                               |
| Compatible Operating Systems  | Mac OS 10.5.9, Mac OS 10.6+, Mac OS 10.7.x, Mac OS 10.8.x, Windows 7, Windows 7 x64, Windows 8 (32/64 bit), Windows Server 2003 (32/64bit), Windows Server 2008 (32/64bit), Windows Server 2008 R2, Windows Server 2012 (64bit), Windows Vista, Windows Vista x64, Windows XP, Windows XP x64, Windows server 2003 R2 |
| <b>OTHER</b>                  |                                                                                                                                                                                                                                                                                                                       |
| Warranty                      | 12 months On site service                                                                                                                                                                                                                                                                                             |

## LOGISTICS INFORMATION

|                          |                    |
|--------------------------|--------------------|
| SKU                      | C11CC99301         |
| Barcode                  | 8715946529707      |
| Dimensions Single Carton | 720 x 570 x 405 mm |
| Carton Weight            | 18.46 Kg           |
| Multiple Order Quantity  | 1 Units            |
| Country of Origin        | Indonesia          |
| Pallet Size Euro         | 10 Units (2 x 5)   |
| Pallet Size Block        | 10 Units (2 x 5)   |



For more information please contact:

Telephone: 0871 222 6702 (UK)+  
01 436 7742 (Republic of Ireland)  
E-mail: [enquiries@epson.co.uk](mailto:enquiries@epson.co.uk)  
Fax: 0871 222 6740

Web: [www.epson.co.uk](http://www.epson.co.uk)  
[www.epson.ie](http://www.epson.ie)

+ Calls cost 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

## WorkForce WF-7110DTW

### WHAT'S IN THE BOX

- CD Manual
- Driver and utilities (CD)
- Individual Ink Cartridges
- Main unit
- Power Code
- Quick Start Guide
- Software (CD)
- Warranty document

### INK CARTRIDGE COMPATIBILITY



### INK YIELD DATA

|       | Alarm clock 27 | Alarm clock 27XL | Alarm clock 27XXL |
|-------|----------------|------------------|-------------------|
| ●     | 350 pages*     | 1,100 pages*     | 2,200 pages*      |
| ● ● ● | 300 pages*     | 1,100 pages*     |                   |

\* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

1. - Determined in accordance with ISO/IEC 24734 showing the average of ESAT from the Office Category Test for default A4 simplex and duplex. For more information, please visit [www.epson.eu/testing](http://www.epson.eu/testing) 2 - Approx. page yield based on ISO/IEC 24711/24712. Actual yield will vary depending on images printed and usage conditions. For more information visit [www.epson.eu/pageyield](http://www.epson.eu/pageyield) 3 - Epson iPrint requires a wireless connection and the Epson printing app. Epson Email print and Epson Remote Print Driver require a connection to the internet. For more information, supported languages and devices, please visit [www.epsonconnect.eu](http://www.epsonconnect.eu) 4 - For more information, please visit [www.epson.eu/inkjetsaving](http://www.epson.eu/inkjetsaving)

**EPSON®**