

7m Coax High Resolution Monitor VGA Video Cable - HD15 to HD15 M/M

StarTech ID: MXTMMHQ7M



The MXTMMHQ7M 7m long VGA cable allows you to connect your VGA monitor or projector at distances of up to 25 feet from your computer, video switch or other VGA device. The high-resolution cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

This 7m VGA cable is backed by StarTech.com's lifetime warranty.

Applications

- Connect a high-resolution display to a desktop PC or video switch, up to 7 meters away

Features

- 2x VGA HD15 male connectors
- Triple coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Supports high resolution VGA monitors (1920x1200)

Technical Specifications

Warranty	Lifetime
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector Plating	Nickel
Fire Rating	CMG Rated (General Purpose)
Number of Conductors	14
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Cable Length	7 m [23 ft]
Color	Black
Product Length	7 m [23 ft]
Product Weight	767 g [27.1 oz]
Wire Gauge	28 AWG
Package Quantity	1
Shipping (Package) Weight	777 g [27.4 oz]
Included in Package	1 - 7m Coax High Resolution Monitor VGA Cable - HD15 M/M

Certifications, Reports and Compatibility

