



15.6", 18.5", or 21.5" Widescreen Medix KW features an IP65 rated front panel, and is designed with either the Intel® Atom™ CPU or the Intel® Core™ i series, making it an ideal all-in-one PC for healthcare environments.

The NEMA 4 standard front panel seal protects Medix KW against water and dust intrusion. VESA compliant mounting provides installation flexibility.

Optional features, including multi-touch and barcode scanner make Medix KW a highly functional and versatile computing device.

## Specifications

### Display

21.5", 18.5", or 15.6" LCD  
LED backlit LCD  
"True Flat" resistive touch (21.5" only available with multi-touch)  
*Optional:* Multi-Touch capacitive

### Processor

Intel® Atom™ D525, 1.8GHz (Fanless),  
or Intel® Core™ i5-2390T, 2.7GHz

### Chipset

Intel NM10 (w/ Intel Atom), or  
Intel Q67 (w/ Intel Core i)

### Operating System

Windows® 7

### Storage

2.5" HDD, 160GB  
*Optional:* 2.5" HDD up to 500GB, 2.5" SSD up to 160GB

### Video

Integrated Intel GMA 3150 (w/ Intel Atom), or  
Intel HD 3000/2000 (w/ Intel Core i)

### Memory

Up to 4GB DDR2 SDRAM (w/ Intel Atom), or  
Up to 8GB DDR3 SDRAM (w/ Intel Core i)

### Audio

Integrated audio, integrated speakers

### Network Interface

1x Gbit Ethernet (w/ Intel Atom), or  
2x Gbit Ethernet (w/ Intel Core i)

### Wireless Connection

*Optional:* 802.11 a, g, n

### Power

Input: 100-240V AC, 1.4A;  
Output: 19V DC, 4.74A

### I/O Ports

4x USB 2.0  
4x Serial (RJ45 w/adapter)  
1x Parallel  
2x RJ45 (1x RJ45 w/ Intel Atom)  
1x VGA  
1x RJ11 w/12V or 24V output  
Audio ports

### Expansion Slots

1x Mini PCIe

### Multimedia

1.3 Mpixel camera

### I/O Devices

*Optional:* Barcode scanner (w/resistive touch only)

### Dimensions / Weight

15.6": 15.6" W x 9.6" H x 1.9" D, 11.0 lb.  
18.5": 18.3" W x 11.2" H x 1.9" D, 15.0 lb.  
21.5": 21" W x 12.9" H x 1.9" D, 16.3 lb.

### Enclosure

IP65 rated

### Mounting

VESA compliant

### Environmental

Operating temp: 32° - 104° F (0° - 40°C)  
Humidity: 5% - 95% non-condensing

### Certification

EN 60601, FCC Class A, CE, LVD

### Limited Warranty

1-Year parts & labor, return to depot

Call 1.888.TANGENT

[www.tangent.com](http://www.tangent.com)