



SB-87-TP-M

SKINNYBOARD™ MOBILE KEYBOARD WITH TOUCHPAD

The SkinnyBoard™ SB-87-TP-M is one of iKey's thinnest keyboards to date. Its sealed, streamlined case and silicone rubber keys meet IP65 standards, making it fully resistant to spills, cleaning procedures and the elements. Built for convenience and versatility in mobile computing applications, the SB-87-TP-M features an integrated touchpad, eliminating the need for an external pointing device. In addition, its red LED backlighting is ideal for nighttime or ambient-light use. An integrated AMPS mounting pattern makes it ideal for in-vehicle mounting. Features: 12 Function Keys Red Backlit Keys Integrated Touchpad Silicone Rubber AMPS Mounting Pattern Ultra-Thin Design

Product Code SB-87-TP-M

CERTIFICATIONS	NEMA 4X UL60950, FCC Part 15 Class B, IP65
SHOCK	3x11 ms pulses of 50g on each of 3 axes
CABLE	LENGTH: 55" +/- 2" (straight USB)
KEY SWITCH	MATERIAL: Industrial Silicone rubber LIFE: Greater than 10 million cycles TRAVEL: 0.055" (1.4mm) ACTUATION FORCE: 7.05 oz +/- 1.06 oz (200g +/- 30g) FEEDBACK: Tactile with mechanical snap
VIBRATION	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2kHz DURATION OF TEST PER AXIS: 3 hours
POWER	USB: 200mA@5V (from CPU port)
COMPATIBILITY	All Windows and Macintosh OS
TEMPERATURE RANGE	Storage -40C to +90C (-40F to +194F) Operating -40C to +70C (-40F to +158F)
WEIGHT	1.4 lbs +/- 0.10 lbs (0.64 kg +/- 0.05kg)
WARRANTY	1 Year Limited Warranty
DIMENSIONS	11.66" x 7.57" x 0.83" (w-h-d)
MODEL NUMBERS	SB-87-TP-M-USB: With USB cable