


CS72D/CS74D

2/4-Port USB DVI KVM Switch

- The CS72D / CS74D 2/4-Port USB DVI KVM Switch allows you to control two or four computers using one USB mouse, USB keyboard and Digital Visual Interface (DVI) monitor console. It supports digital video devices, such as flat panel displays, data projectors, plasma displays and digital TVs.

The CS72D / CS74D comes with ATEN's Video DynaSync™ technology, which eliminates boot-up display problems and optimizes resolution; it carries several convenient features, such as Power On Detection, 2.1 channel audio capability and USB2.0 peripheral sharing, as well as provides quick and easy methods to access computers.




Features

- Fully compliant with DVI specification (Digital only)
- Supports multi-function and wireless mouse/keyboard
- Audio enabled – full bass response provides a rich experience for 2.1 channel surround sound systems
- Superior video quality – 1920 x 1200@60Hz
- Multiplatform support – Windows, Linux, Mac, FreeBSD and Sun
- HDCP compliant
- Power on detection – if one computer is powered off, the switch will automatically switch to the next powered-on computer
- Video DynaSync™ – exclusive ATEN technology optimizes display resolution and eliminates boot-up display problems
- Computer selection via front panel pushbuttons, hotkeys, and mouse switching function*
- USB 2.0 mouse port can be used for USB hub and USB peripheral sharing
- Complete keyboard emulation for error-free booting
- Firmware upgradeable
- Non-powered (CS72D only)
- Mac/Sun keyboard support and emulation**

*Mouse port switching is only functional under mouse emulation mode and USB 3-key wheel mouse

**PC keyboard combinations emulate Mac/Sun keyboards; Mac/Sun keyboard work only with their own computers



Specification

Function			CS72D	CS74D
Computer Connections			2	4
Console Connections			1	1
Port Selection			Hotkey, Mouse switch, Pushbutton	
Connectors	Console ports	Keyboard	1 x USB Type A Female (Iron)	
		Video	1 x DVI-D Female (White)	
		Mouse	1 x USB Type A Female (Iron)	
		Speakers	1 x Mini Stereo Jack Female (Green)	
	Computer Port 1	KB/ Mouse/ Video/ Speakers	1 x 44-pin Connector Female	
		Computer Port 2	Mouse/ Video/ Speakers	N/A
		Power	N/A	1 x DC Jack
LEDs	Selected	2 (Green)	4 (Green)	
Pushbuttons		2	4	
Cable Length		1.2 m x 1 (44 pin)	1.2 m x 1, 1.8m x 1 (44 pin)	
Power Consumption		DC 5.0V, 5.0W	DC 5.3V, 5.3W	
Emulation	KB / Mouse	USB		
Video		1920 x 1200 @60Hz; 1920 x 1080 Full HD		
Scan Interval		3, 5, 10, 20 seconds (5 secs. default)		
Environment	Operation Temperature		0–50°C	
	Storage Temperature		–20–60°C	
	Humidity		0–80% RH, Non-condensing	
Physical Properties	Housing		Metal	
	Weight		0.33 kg	0.51 kg
	Dimension (L x W x H)		12.30 x 7.54 x 2.28 cm	19.80 x 7.54 x 2.28 cm

ATEN International Co., Ltd.

3F., No.125, Sec. 2, Datong Rd., Sijhih District., New Taipei City 221, Taiwan
Phone: 886-2-8692-6789 Fax: 886-2-8692-6767
www.aten.com E-mail: marketing@aten.com

Printed 11/2013 V1.0



© Copyright 2013 ATEN® International Co., Ltd.
ATEN and the ATEN logo are trademarks of ATEN International Co., Ltd.
All rights reserved. All other trademarks are the property of their respective owners.