

# HANNES·G

## HE195ANB


47cm / 18.5" Diagonal LED Monitor

US/CN/  
TW/EU




- LED Backlight Monitor
- 1366 x 768 WXGA Resolution
- 40,000,000:1 Active Contrast
- 5ms Fast Response Time
- Low Power Consumption
- Multi-Video Modes : PC / Movie / Game / ECO
- Tilt and Wall-Mountable (VESA)
- ECO Friendly




Backlight  
**LED**



1366 x 768  
RESOLUTION



40,000,000:1



# HE195ANB

47cm / 18.5" Diagonal LED Monitor

US/CN/  
TW/EU

HANNSPREE

LCD Panel	Display size	47cm / 18.5" Diagonal White LED-Backlight
	Brightness	200cd/m2
	Contrast	600:1 (Typical) 40,000,000:1(Active contrast)
	Pixel pitch	0.3(H) x 0.3(V) mm
	Resolution (H x V)	1366 x 768
	Aspect Ratio	16:9
	Response time	5ms
	View angles LR,UD	H/V 90°/65°
	Color	WARM,NATURE,COOL, User Mode
	Panel surface	Anti-Glare
	Display colors	16.7M Colors
PC Input Range	Horizontal Freq.	30 to 61 kHz
	Vertical Freq.	56Hz to 75Hz
	Max. display frequency (Resolution H*V/Fv)	1366 x 768 /60Hz
Interface	Input	D-Sub x 1
Output Terminal	Eaphone	NA
	Speaker	NA
Power	Consumption	On: 20 W; Standby<=0.5W, Off<=0.5W
	AC Power Range	AC 100~240V, 50~60Hz
	Power Mode Indicator Light	Power on : Green (LED) Power saving : Amber (LED)
Operating Condition	Temperature	5°C ~ 35°C
	Humidity	20% ~ 85%, non-condensing
Physical	Dimension (W*D*H)	444 X 185 X 329 mm
	Packing Dimension (W*D*H)	492 X 117 X 377 mm
	Net weight	2.56 Kg
	Gross weight	3.35 Kg
	Tilt	-3~ +17
	Kensington Lock	Yes
	VESA mounting	100 x 100mm

Controls	Front control	Menu, Bri (+), (-) Input/Enter, Power
	On Screen Display	12 language : EN, TC, DE, FR, ES, IT, PT, NL, SC, JS, KR, Russian
	Preset Mode	PC, Movie, Game, ECO Modes
Container Loading	40' HQ	US: 2,520
	40' Standard	US: 2,100 EU/others: 2,304
	20' Standard	US: 1,000 EU/others: 960
Accessories	Power Cable(1.5m),VGA Cable(1.5m),User Manual (CD), Quick Start Guide (Paper) & Warranty	
Color Plan	Black glossy: front bezel, arm, base Black texture: back cover	
Carton box	Brown	
Green product (Jan. 2009)	Yes	
Window 7	NA	
HDMI Logo	YNA	
Certification	FCC, UL/CUL, 3C, China energy level 1, BSMI, EnergyStar 5.0, CE, CB, GOST	

Contact Information

Actual products may differ slightly from those illustrated on this promotion material. Please refer to actual samples for final selection. The products displayed on this promotion material may not be available for purchase in your particular country or locality. Please check with your local Hannspree authorized representatives for the availability of specific products in your area. Hannspree reserves the right to alter design and specifications as well as to change the accessories with equivalents without notice.