



With its fast data processing features, it is ideal for easy document workflow. Document Capture Pro allows multiple users to benefit from Push Scan features and the Network Interface Unit means this model is ideal for sharing across office/department networks in government, banks and healthcare establishments.

Performance and productivity

This scanner features a compact footprint and high speed scanning of up to 65ppm / 130ipm, even at 300dpi in colour. This, combined with hardware JPEG compression, makes large scan jobs faster to process. Its ReadyScan technology certifies mercury-free products and guarantees no warm-up time before scanning.

Seamless integration into document management and cloud systems

Epson Document Capture Pro makes it easy to integrate this business scanner into your document management system, speeding up workflow and enabling you to capture, convert and distribute scanned information into your document filing system. In addition, barcode recognition and Zonal OCR help automate large document processes. It can also Push Scan from the device, via network or USB, which helps to increase office productivity.

Scan software included

Epson Scan offers a wide selection of advanced document imaging features, such as text enhancement and automatic de-skew, which help improve efficiency and increase workload output. It also scans to .docx, .xlsx and .pptx.

Easy network sharing via Ethernet

Combined with Document Capture Pro, the Network Interface Unit allows you to customise 'scan to' job commands, such as 'scan-to-email', 'scan-to-Microsoft SharePoint™' or 'Scan-to-Cloud', among others, directly from the scanner's panel.

KEY FEATURES

- **Easy network sharing via Ethernet**
Combined with Document Capture Pro, the Network Interface Unit lets you customise 'scan to' job commands
- **Epson Push Scan**
Text enhancement and automatic de-skew help improve efficiency
- **Fast scanning speeds**
High-speed scanning of up to 65ppm / 130ipm, even at 300dpi in colour.
- **Seamless integration into document management and cloud systems**
Document Capture Pro
- **Wide range of driver support**
WIA, TWAIN and ISIS

PRODUCT SPECIFICATIONS

TECHNOLOGY

Scanner type	Sheetfed Scanner
Scanning Resolution	600 dpi x 600 dpi (Horizontal x Vertical)
ADF Minimum Document Size	52 mm x 50.8 mm (Horizontal x Vertical)
ADF Maximum Document Size	216 mm x 356 mm (Horizontal x Vertical)
Paper Formats	A3 with stitching function, A4, A6, B5, B6, Letter, Postcard, Plastic cards, Legal
Color Depth	Input: 48 Bits Color / 16 Bits Monochrome, Output: 24 Bits Color / 8 Bits Monochrome
Ultrasonic Sensor	Yes

SCANNER

Light Source	ReadyScan LED technology
--------------	--------------------------

SCAN SPEED

Scanning Speed	Monochrome: 65 Pages/min - Colour: 65 Pages/min , Resolution: 200 / 300 dpi, Monochrome: 130 image/min - Colour: 130 image/min measured with Size: A4 , Resolution: 200 / 300 dpi
----------------	---

PAPER / MEDIA HANDLING

ADF Paper Setting Capacity	80 Sheets
Reliability Daily Duty Cycle	6,000 Pages
Duplex Scan	Yes

SCANNING FEATURES

Features	Standalone operation, RGB colour dropout / enhance, Skip blank page, A3 stitching (without carrier sheet), Punch holes removal, Pre-defined scanning settings, Automatic area segmentation, Automatic de-skew, Dual Image Output (Windows only), Auto-rotation, Text enhancement, Edge enhancement, Unsharp Mask (USM), Descreening, Barcode Recognition, Zonal OCR A & B support, Manual / Automatic Job Separation, Scan to Cloud Storage
Output formats	BMP, JPEG, TIFF, multi-TIFF, PDF, searchable PDF, secure PDF, PDF/A
File compression features	Hardware JPEG compression, PDF Compression

CONNECTIVITY

Interfaces	Ethernet interface (100 Base-TX / 10 Base-T), Gigabit ethernet interface
Network Interface Panel / Unit	Built-in
Ethernet settings	10BASE-T / 100BASE-TX / 100BASE-T / Full-duplex / Half-duplex
Panel type	5-line LCD with Push Scan features
Protocol support	TCP/IP, DHCP, DNS, SNMP, SLP, HTTP
Panel Lock with password	Yes (with Document Capture Pro solutions)

LOGISTICS INFORMATION

SKU	B11B222401BU
Barcode	8715946541631
Dimensions Single Carton	576 x 185 x 376 mm
Carton Weight	5.6 Kg
Multiple Order Quantity	1 Units
Pallet Size Euro	360 Units (60 x 6)
Pallet Size Block	360 Units (60 x 6)

WorkForce DS-860N

WHAT'S IN THE BOX

- Warranty document
- USB cable
- Setup guide
- Power cable
- Main unit
- Driver and utilities (CD)

OPTIONAL ACCESSORIES

- Carrier Sheet x 5
B12B813431
- Roller Assembly Kit for DS-760/860
B12B813581
- Network Interface Unit
B12B808451BY

For more information please contact:

Telephone: 0871 222 6702 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

+ Calls cost 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners.
Product information is subject to change without prior notice.

EPSON®