

HSM[®] Classic

390.3 L6 shredder

Professional high security device can handle large workloads and use by 15-20 person departments



EPL Listed*

- Auto stop when container is full or door is open
- Practical storage space for paper stacks
- Features include auto start/stop and automatic reverse
- Powerful, specially adjusted motor for longer periods of use - with thermal protection for high performance
- Tried and tested closed tooth wheel drive prevents penetration of dirt and slows wear, increasing the service life
- Enclosed housing protects against the spread of paper dust and provides for quiet operation
- Casters for increased mobility and shared use
- Anti-Jam technology designed to easily and quickly reverse out paper in the event the machine is overloaded
- External auto-oiler included
- Uses a 58 gallon capacity shred bag; Part #HSM2117



| | |
|---|------------------------------|
| HSM part# | HSM16604 |
| Cutting type | Cross cut |
| Cutting size | 1/32" x 3/16" |
| Security level DIN 32757-1 | 6 |
| Security level DIN 66399 | P-7 F-3 |
| Cutting capacity per run in sheets | 10 - 12 [^] |
| Cutting Speed | 27 ft / min |
| Throat opening | 16" |
| Motor at maximum number of sheets | 1600W |
| Motor power (horsepower) | 1.88 |
| Voltage | 115 V / 60Hz |
| Dimensions (H x W x D) | 35 7/10" x 23 2/5" x 18 1/2" |
| Weight | 132 lbs |
| Shred-bin volume | 39 gal |
| Cutting capabilities | |

All technical specifications are approximate values. Technical and design modifications reserved.

*Meets DOD and NSA/CSS 02-01 mandatory security requirements

[^]Sheet capacity will vary depending on paper size, weight, quality and proper power supply.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM[®]