


HSM® Powerline

FA 400.2 Premium shredder

Designed for destroying large amounts of media
and for continuous operation.



- Material infeed via a conveyor belt—for optimum loading and maximum throughputs.
- Practical loading table for simple loading.
- Touch-sensitive keypad for continuous and reverse operation.
- Auto stop with LED indicates when shred-bin bag is full.
- Automatic reverse for paper jams.
- Convenient trolley with extremely sturdy, reusable shred-bin bag.
- Very sturdy gear motor with chain drive for maximum throughputs.
- The tried-and-tested closed-tooth wheel drive prevents penetration of dirt and slows wear, increasing the service life.
- Transportable on wheels.
- Table extension available as accessory upon request.
- Anti-Jam Technology designed to easily and quickly reverse out paper in the event that the machine is overloaded.



HSM part#	HSM1513	HSM1514
Cutting type	Strip cut	Cross cut
Cutting size	1/4"	1/4" x 2"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / O-2 / F-2 / E-2	P-3 / O-2 / T-3 / E-2
Cutting capacity per run in sheets	130	120
Cutting speed	41 ft / min	49 ft / min
Throat opening	17"	17"
Motor at max. no. of sheets	4000W	4000W
Voltage	3x208 V / 60 Hz	3x208 V / 60 Hz
Dimensions (H x W x D)	65" x 45.5" x 61.7"	65" x 45.5" x 61.7"
Weight	937 lbs	937 lbs
Shred-bin volume	104 gallons (optional 2 x 61 gallon)	104 gallons (optional 2 x 61 gallon)
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service 800.613.2110

Great Products, Great People.

HSM®