

Product datasheet

Specifications



Galaxy VM UPS Modular Battery Cabinet Narrow for 6 battery modules

GVMMODBCN

Overview

Presentation Narrow modular battery cabinet with up to a 6 string modular battery capacity. To be used with the GVMMBTU modular battery string. Batteries are not included in the sku and must be purchased separately.

Lead Time Usually Ships within 2 Weeks

Main

Main Input Voltage 480 V 3 phases

Battery Type VRLA

Provided Equipment Installation guide

Batteries & Runtime

Battery Location Battery cabinet

Number Of Battery Blocks Per String 40

Number Of Battery Free Slots 6

Number Of Battery Filled Slots 0

Device Mounting Enclosed battery cabinet

Battery Voltage 480 V

Physical

Colour White

Height 197 cm

Width 37 cm

Depth 85.4 cm

Net Weight 139 kg

Input

Network Frequency 40...70 Hz

Conformance

Standards EN/IEC 62040-3
FCC part 15 class A
UL 1778

Environmental

Ambient Air Temperature For Operation 0...40 °C

Operating Altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...40 °C
Storage Altitude	0.00...14999.82 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	215 cm
Package 1 Width	106 cm
Package 1 Length	75 cm
Package 1 Weight	164 kg

Contractual warranty

Warranty	1 year repair or replace
-----------------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information Yes

Eu Rohs Directive Compliant with Exemptions
