

WorkForce Pro WF-5690DWF



With features designed for easy business integration, the 4-in-1 multifunction WF-5690DWF also benefits from low running costs, low power consumption and fast print speeds. Automatic double-sided printing, scanning, copying and faxing makes any job easy and efficient. Directly print and scan using a USB memory stick, and securely print using a PIN code to release jobs at the printer.

Low running costs

The WorkForce Pro WF-5690DWF has an up to 50 percent lower cost per page than competitive colour lasers¹, saving you money as you take advantage of this printer's high capacity ink cartridges of up to 4,000 pages². And there are fewer parts to replace than a laser.

Ecological

The WF-5690DWF uses up to 80 percent less power than competitive colour lasers¹ thanks, in part, to its no heat technology. No ozone gases are emitted, and an improved quiet print mode and no fan noise during or after printing makes it ideal for the work environment.

Save time

This efficient multifunction business printer is faster than a laser on typical print jobs¹, with print speeds of up to 34ppm in mono and 30ppm in colour, or 20ppm ISO print speed in both³. Its high paper capacity of 580 sheets means less time is spent refilling, and it has a high monthly duty cycle of up to 35,000 pages⁴.

Built for business

PrecisionCore technology powers the output quality that Epson is known for, at the speeds required for office, commercial and industrial printing. Prints dry fast thanks to the DURABrite Ultra ink. Scan-to functions, LDAP support and PDL emulations help this printer easily integrate into the business environment. Its intuitive large colour touch-screen makes functions readily available, and the rear manual paper tray lets you print on a range of media.

DATASHEET



KEY FEATURES

- **Low running costs**
Up to 50 percent lower cost per page than competitive colour lasers¹
- **Ecological**
Uses up to 80 percent less power than competitive colour lasers¹
- **Save time**
Automatic double-sided printing, scanning, copying and faxing
- **Built for business**
Scan-to functions, LDAP address book support and PDL emulations
- **PrecisionCore technology**
Epson's most advanced printhead technology

PRODUCT SPECIFICATIONS

TECHNOLOGY	
Printing Method	PrecisionCore™ Print Head
PRINT	
First Page Out	Monochrome 7 Seconds, Color 7 Seconds
Printing Speed ISO/IEC 24734	20 Pages/min Monochrome, 20 Pages/min Color
Maximum Printing Speed	34 Pages/min Monochrome (plain paper), 30 Pages/min Color (plain paper)
Duplex Printing Speed	11 A4 Pages/min Monochrome, 11 A4 Pages/min Color
ISO/IEC 24734	
Printing Resolution	4,800 x 1,200 dpi
Max Duty cycle	35,000 Pages per month
For detailed information on printing speeds please visit http://www.epson.eu/testing .	
SCAN	
Scan speed colour A4	300 dpi (with ADF), 4.5 ipm with ADF scan 200 dpi (flatbed) 14 sec. with flatbed scan
Advanced document integration	E-mail, FTP, Network folders, Computer (Epson Document Capture Pro), Microsoft SharePoint with Epson Document Capture Pro, USB Memory Device / Card
FAX	
Fax Transmission Speed	Up to 33.6kbps / Approx. 3 sec/page
Page memory	Up to 550 pages/ 6MB (ITU-T No. 1 chart)
COPY	
Copy Speed	up to 19 ipm Black, up to 19 ipm Colour *Simplex ADF 600 x 600 dpi (ISO/IEC 24735)
CONNECTIVITY	
Interfaces	Hi-Speed USB - compatible with USB 2.0 specification, Ethernet Interface (1000 Base-T/ 100-Base TX/ 10-Base-T), USB host, Wireless LAN IEEE 802.11b/g/n, Wi-Fi Direct
PAPER / MEDIA HANDLING	
Paper Formats	A4, A5, A6, B5, C4 (Envelope), C6 (Envelope), No. 10 (Envelope), Letter, 10 x 15 cm, 13 x 18 cm, 20 x 25 cm, 16:9, Legal
Automatic Document Feeder	35 Pages
Standard Paper input	330 Sheets Standard, 80 Sheets MP tray, 250 Sheets paper tray
Optional paper tray(s)	250-sheet paper tray
ADDITIONAL FEATURES	
Features	Direct scan-to-print without PC, Direct print from USB
OTHER	
Warranty	12 months On site service

LOGISTICS INFORMATION

SKU	C11CD14301 C11CD14301BY
Barcode	8715946537849
Dimensions Single Carton	610 x 520 x 490 mm
Carton Weight	17.48 Kg
Multiple Order Quantity	1 Units
Pallet Size Euro	8 Units (2 x 4)



* Warranty offers are not available for all countries. Please contact your local Epson representative.

For further information please contact your local Epson office or visit www.epson-europe.com
 Austria 01 253 49 78 333 Belgium +32 (0)2 792 04 47 Czech 800/142 052 Denmark 44 50 85 85 Finland 0201 552 091 France 09 74 75 04 04
 (Cost of local call, operator charges may apply) Germany +49 (0) 2159/92 79 500 Greece 210-8099499 Hungary 06800 147 83
 Ireland 01 436 7742
 Italy 02-660321 10 (0,12 /min) Luxembourg +352 27860692 Middle East +9714 8872172 Netherlands +31 (0)20 708 5099 Norway
 +47 67 11 37 00 Poland 0-0-800 4911299 (0,16 zł/min) Portugal 707 222 111 Russia (095) 777-03-55 Slovakia 0850 111 429
 South Africa (+2711) 465-9621
 Spain 93 582 15 00 Sweden 0771-400135 (Mobilsamtal – 0,99 kr/min, Lokala samtal – 0,30 kr/min, Utlandssamtal – 0,89 kr/min)
 Switzerland 022 592 7923 Turkey (0212) 3360303 United Kingdom 0871 222 6702

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

WorkForce Pro WF-5690DWF

WHAT'S IN THE BOX

- Quick Setup Guide
- Individual Ink Cartridges
- Main unit
- Warranty Documents
- Power cable
- Driver and utilities (CD)

INK YIELD DATA



T789

● 4,000 pages*

●●● 4,000 pages*



Tower of
Pisa 79

Tower of
Pisa 79XL

● 900 pages* 2,600 pages*

●●● 800 pages* 2,000 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield>

SUPPLIES

- WF-5xxx Series Ink Cartridge XXL Black
C13T789140 (4,000 pages)
- WF-5xxx Series Ink Cartridge XXL Cyan
C13T789240 (4,000 pages)
- WF-5xxx Series Ink Cartridge XXL Magenta
C13T789340 (4,000 pages)
- WF-5xxx Series Ink Cartridge XXL Yellow
C13T789440 (4,000 pages)

1. - For more information visit www.epson.eu/inkjetsaving2 - Approx. page yield based on ISO/IEC 24711/24712. Actual yield will vary depending on images printed and usage conditions. For more information visit <http://www.epson.eu/pageyield3> - Determined in accordance with ISO/IEC 24734 showing the average of ESAT from the Office Category Test for default A4 simplex and duplex. For more information, please visit www.epson.eu/testing4 - The maximum number of printed pages per month based on the performance capabilities of the printer, including ISO rated print speeds and paper handling capacities.

EPSON®