

1U 17" HD 1080p Rackmount LCD Console with Front USB Hub

StarTech ID: RKCONS17HDGB



The RKCONS17HDGB 17" Full HD LCD Rack Console lets you control server equipment from a centralized, 17in 1080p KVM console, with an integrated 2-port front USB hub.

The integrated single port KVM module offers universal support for DVI or VGA, and USB or PS/2 console connections and includes all of the necessary cabling to get you up and running. Connect the console to either a single system, or a multi-port KVM switch to manage multiple systems.

The front panel USB hub places two easily accessible USB 2.0 ports at your disposal for connecting external storage and other peripherals as needed.

For added security in your server room, this rackmount LCD also includes a physical key-lock.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Ideal for high resolution applications in the server room, where the previous standard 1024x768 17" screens are not sufficient
- Centralized control of a single system, or dozens of PCs when connected to a KVM switch
- Improving the internal space-efficiency of existing cabinets
- Manage cabinet-mounted servers and KVM switches

Features

- Supports HD resolutions up to 1920x1080
- Durable 1U rack mountable design
- LED Backlight; reduced power consumption
- 2 front USB Hub ports
- VGA or DVI video input support
- Compatible with USB or PS/2 PCs and KVMs
- On Screen Display (OSD) control and LED indicators for easy monitoring
- Integrated 106-key US standard keyboard with touchpad

Technical Specifications

Warranty	2 Years
Audio	No
Cables Included	Yes
Daisy-Chain	Yes
Display Size	17in
Key Lock	Yes
KVM Ports	1
Multi-Monitor	No
Panel Type	Active Matrix TFT LCD
PC Interface	USB and PS/2
PC Video Type	DVI+VGA
Rack-Mountable	Yes
U Height	1U
Console Interface(s)	1 - DVI-I (29 pin) Female
Console Interface(s)	1 - VGA (15 pin; High Density D-Sub) Female
Console Interface(s)	2 - PS/2 (6 pin; Mini-DIN) Female
Console Interface(s)	2 - USB A (4 pin) Female
Other Interface(s)	2 - USB A (4 pin) Female
Aspect Ratio	Wide (16:9)
Brightness	300 cd/m ²
Color Depth	8-bit, 16.7M colors
Contrast Ratio	650:1
IP Control	No
Maximum Number of Users	1
MTBF	50, 000 Hrs
Pixel Pitch Support	0.264 x 0.264 mm
Response Time	2ms
Viewing Angle	140° (H), 120° (V)
OS Compatibility	OS independent; No software or drivers required
Color	Black
Enclosure Type	Heavy Duty Steel
Maximum Mounting Depth	1000 mm [39.4 in]
Minimum Mounting Depth	504 mm [19.8 in]
Product Height	44 mm [1.7 in]

Product Length	460 mm [18.1 in]
Product Weight	13 kg [28.7 lb]
Product Width	448 mm [17.6 in]
Center Tip Polarity	Positive
Input Current	1.7 A
Input Voltage	100 ~ 240 AC
Output Current	1.7 A
Output Voltage	12 DC
Power Consumption	23.35 W
Humidity	10~90% RH
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Shipping (Package) Weight	20.5 kg [45.3 lb]
Included in Package	1 - 1U Rack Console
Included in Package	1 - Set, Mounting Rails
Included in Package	2 - Extended Brackets
Included in Package	2 - Short Brackets
Included in Package	2 - Short Bracket Attachments
Included in Package	2 - Keys
Included in Package	1 - 6ft (1.8m) PS/2 VGA KVM Cable
Included in Package	1 - 6ft (1.8m) USB A-A Cable
Included in Package	6 - #6-32x6 Flat Screws
Included in Package	6 - M4x5 Screws
Included in Package	1 - Power Adapter
Included in Package	1 - UK Power Cord
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility



Operating System
Independent

RoHS Compliant
Available