

WP4

NEMA Rated Outdoor Power Supply/Battery Enclosure

Description

Altronix WP4 is a UL Listed, NEMA 4/4X, IP66-11 Rated power supply/battery outdoor enclosure. It can accommodate a wide variety of Altronix power supplies, sub-assemblies, and accessories.



WP4

Specifications

Features

- Lightweight molded fiberglass reinforced polyester enclosure is corrosion resistant and does not contain halogens.
- Lockable stainless steel latch.
- Integral flanges simplify wall or pole mounting.

Capacity

- Fits two (2) 12VDC/4AH batteries.

Agency Listings

UL Listed Enclosure.
CE European Conformity.

Physical and Environmental

Dimensions (H x W x D)

9.32" x 7.32" x 4.92" (236.7mm x 185.9mm x 125mm).

Product Weight 1.8 lbs. (0.8 kg).

Shipping Weight 2.6 lbs. (1.17 kg).

Accessories

PMK1 Pole Mount Kit (order separately)

PMK1 pole mount kit is designed to simplify installation of outdoor units. It accommodates 2" - 8" (diameter) poles.

Kit includes:

- Two (2) powder coated steel mount brackets.
- Four (4) stainless steel bolts.
- Four (4) stainless steel lock washers.
- Two (2) wormgear quick release straps.



PMK1


WP4 NEMA Rated Outdoor Power Supply/Battery Enclosure




Dimensions and Drawing

Dimensions (H x W x D approximate)
9.32" x 7.32" x 4.92" (236.7mm x 185.9mm x 125mm)


FRONT VIEW



RIGHT SIDE VIEW




FRONT VIEW
COVER - REMOVED



316 STAINLESS STEEL
PADLOCK LATCH ATTACHED
WITH RIVETS. Ø0.375" (9.5mm)
PADLOCK EYE

10-32 X 0.25" (6.4mm)
4 PLACES

END VIEW



END VIEW
COVER - REMOVED

