

HS Hybrid Digital Video Recorder with Real-Time Recording

D8HS 8 Channel IP & Analog Hybrid DVR

D16HS 16 Channel IP & Analog Hybrid DVR

Storage 1TB – 9TB

D8HS1TB	D8HS4TB	D16HS1TB	D16HS4TB
D8HS2TB	D8HS6TB	D16HS2TB	D16HS6TB
D8HS3TB	D8HS9TB	D16HS3TB	D16HS9TB




Front panel



Rear panel

D8HS shown

15" (W) x 13.4" (D)



2.83" (H)

Features

EZ Set-Up Wizards: One click wizard guides you to set up essentials of the system in a logical and easy to understand sequence.

- Date/Time - Recording method - Recording video quality - Network
- Port forwarding

EZ Camera: quickly discovers and installs IP cameras

EZ Search: quickly search events from thumbnails

EZ Record: quickly setup recording resolutions and recording type

EZ Copy: auto copy what you are playing onto a USB flash drive

- Video Out: 1 HDMI®, 1 VGA, 1 CVBS, 1 Spot
- Real-time recording rate at 30fps/channel for analog channels at 960H and IP channels at Full HD (1920x1080)
- Up to 5MP resolution on the last channel
- Plug & play feature with Speco's OnSIP/IP/ZIP cameras
- ONVIF support*
- Dual network ports for isolating IP camera network and remote network traffic
- Each channel is configurable for either IP or analog
- H.264 video compression
- Networkable hybrid DVR with free Speco DDNS server
- Digital Deterrent® for triggering audio message via motion detection or sensor
- 2-way audio communication
- Programmable recording on motion detection, sensor, schedule, continuous and manual
- Supports wireless access point for viewing and configuration
- Built-in S.M.A.R.T. Technology (Self-Monitoring, Analysis and Reporting Technology for HDD)

- Switch between low and high quality stream during simultaneous Continuous + Motion or Continuous + Sensor recording modes for storage optimization
- Easy firmware upgrade by USB port or network
- User Access: up to 4 concurrent users
- Remote monitoring / recording / playback / configuration / software upgrades and PTZ control via internet
- Network software supports Static IP, DHCP and DDNS
- Network accessible via SpecoTech Multi-Client Software, SecureGuard® CMS, Internet Explorer Web-Viewer and Speco Player Mobile Viewer
- PC and MAC® compatible
- IR remote control & mouse included
- Rack mountable (hardware included)
- 3 year warranty

Free Apps with support for view on most smart devices

*Visit www.specotech.com/onvif.html for latest ONVIF support. iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Rev. 9/9/14



Optional Accessories



ERS1V
Vented Rack Shelf



IRRPTKIT
IR Repeater Kit



DSWFUSB
USB Wireless Access Point



Technical Specifications:

HS Hybrid Digital Video Recorder with Real-Time Recording

Model			D8HS	D16HS	
Video	Input	IP Channels	Up to 8	Up to 16	
		Analog Channels	Up to 8	Up to 16	
	Output	HDMI®	1 HDMI (1280x720 / 1920x1080)		
		VGA	1 VGA (1280x720 / 1920x1080)		
		CVBS	1		
		SPOT	1 (Analog channels only)		
Loopouts	8 (Analog channels only)	16 (Analog channels only)			
Audio	Input		8 line input, 8 IP input	16 line input, 16 IP input	
	Output	Local Output (RCA)	1	1	
	Audio Codec		G.711		
Alarm	Sensor Input	Local Input	4	4	
		Remote Input from IP Camera	8	16	
	Alarm Output		1	1	
Serial	RS-232C	Debugging Only	1		
	RS-485	PTZ	1		
Recording	Compression		H.264 (baseline, main, high profile)		
	Resolution	IP	2592x1944 (5MP)	Channel 8 only	Channel 16 only
			1920x1080 (1080p)	240fps	480fps
			1280x720 (720p)	240fps	480fps
	Analog	960H	240fps	480fps	
		D1	240fps	480fps	
		CIF	240fps	480fps	
	Recording Quality Grade (Analog Only)		5 levels		
Recording Mode		Continuous / Motion / Sensor / Schedule / Manual / Continuous + Sensor / Continuous + Motion			
Pre-Recording		Max. 20 minutes			
Post Recording		Max. 60 seconds			
Playback	Search		EZ Search, Date/Time, Event, Archive, Log		
	Multi-Decoding		1, 4, 8	1, 4, 9, 16	
	Playback Speed		x0.25, x0.5, x2, x4, x8, x16, x32, x64		
Backup	Media		USB Drive, External HDD, Network		
	Format		BMP, AVI, Proprietary Format		
	Large Backup		Yes (max. 24 hours)		
Storage	HDD	Capacity of 1 HDD	3TB		
		Internal HDDs	3		
		e-SATA	1		
USB		2 front, 1 rear			
User I/F	Menu Display		GUI		
	Input Method		Front Buttons, IR, Mouse, Keyboard Controller		
Network	Interface		Dual Network Ports 10/100/1000Base-T		
	Streaming	IP Channel	Depends on profile		
		Analog Channel	CIF @ 30fps/channel		
	Dual Encoding for Network		Yes		
Max. Throughput		40Mbps			
Network Access	Mobile Viewer		Speco Player (Live, Search, PTZ, 2-Way Audio)		
	PC Web Viewer		IE, Chrome, Firefox, Safari (Live, Search, Backup, PTZ, Remote Setup)		
	PC Client		SpecoTech Multi-Client Viewer and SecureGuard® CMS		
Features	Digital Deterrent®		Default + up to 8 audio files		
	Digital Zoom		Yes		
	DLS (Daylight Savings)		Yes		
	EZ Record		Yes		
	S.M.A.R.T		Yes		
	Internal Beep		Yes		
	Multi-Language		Yes		
	Dynamic DNS		Yes (free Speco DDNS)		
	SW Upgrade		USB and remote software upgrade		
	E-mail Notification		Yes		
NTP (Network Time Protocol)		Yes			
Power Source	Power Supply Voltage		12VDC, 5A		
Allowable Operating Temperature / Humidity			41° F - 104° F / 20% - 80% RH (non-condensing)		
Allowable Storage Temperature			14° F - 122° F		
Weight	Unit Weight (Gross Weight)		12 lbs.		
Dimensions	Unit Dimensions (W x H x D)		15" (W) x 2.83" (H) x 13.4" (D)		

Please note that specifications and unit exterior design are subject to change without notification.