

## 12U Office Server Cabinet w/ Wood Finish and Casters

StarTech ID: *RKWOODCAB12*



The RKWOODCAB12 12U Office Server Cabinet lets you store your server, network or AV equipment discreetly in the office, with a stylish wood finish. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Designed to blend in with your office or boardroom furniture, this 12U server cabinet features wood laminate exterior panels with a shaded glass front window that keeps your equipment visible for monitoring, as well as front and rear key-locks to prevent unauthorized access. To help keep your valuable equipment running cooler, we've included a ventilation panel to maximize airflow. The cabinet also features durable casters, so that positioning your server equipment as needed isn't a hassle.

The 4-post enclosed rack supports a weight capacity of up to 300lbs (136kg) and offers rails with adjustable mounting depth from 16.7in (423mm) to 20.6in (523mm) to accommodate various sizes of equipment. Making it easy to route your cables where you need them, the 12U cabinet offers cable grommets on the rear and top panels, and a cable entry panel at the base.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applicazioni

- Mount server or networking equipment in a well-furnished boardroom
- Add an attractive server cabinet that won't be an eyesore in small / home-office areas with limited space

**Caratteristiche**

- 12U Enclosed cabinet with a stylish wood finish
- Supports a weight capacity of up to 300lbs (136kg)
- TAA compliant for GSA Schedule purchases
- Adjustable mounting depth from 16.7in (423mm) to 20.6in (523mm)
- Ventilation and cable entry panels
- Casters included
- Front and rear key-lock
- Flat-packed for easy shipping

**Specifiche tecniche**

Warranty	2 Years
Back Door Type	Wood
Casters	Included
Frame Type	Enclosed Cabinet
Front Door Type	Wood w/ Glass Window
Industry Standards	EIA-310-D
Key Lock	Yes
Rack Type	4-Post
Side Panel Type	Wood
U Height	12U
Weight Capacity	136.1 kg [300.7 lb]
External Depth	660 mm [26 in]
External Height	664 mm [26.1 in]
External Width	560 mm [22 in]
Internal Height	538 mm [21.2 in]
Internal Width	520 mm [20.5 in]
Maximum Mounting Depth	523 mm [20.6 in]
Minimum Mounting Depth	423 mm [16.7 in]
Flat Pack	Yes
Shipping (Package) Weight	34.3 kg [75.7 lb]
Included in Package	1 - Right Side Panel
Included in Package	1 - Left Side Panel
Included in Package	1 - Rack Top
Included in Package	1 - Rack Bottom
Included in Package	1 - Rear Panel
Included in Package	1 - Front Door
Included in Package	4 - Rack Rails
Included in Package	2 - Front/Rear Support
Included in Package	1 - Ventilation Panel
Included in Package	1 - Cable Entry Panel
Included in Package	4 - Panel Brackets
Included in Package	1 - Strike Plate
Included in Package	1 - Round Grommet

Included in Package	2 - Locking Latches (with 2 keys each)
Included in Package	4 - Casters
Included in Package	32 - M6x12 Screws
Included in Package	8 - M5x12 Screws
Included in Package	2 - M4x12 Screws
Included in Package	4 - M6x15
Included in Package	12 - Cams
Included in Package	12 - Connecting Bolts
Included in Package	16 - Dowel Pins
Included in Package	30 - Each, M6 Cage Nuts / Screws
Included in Package	1 - Instruction Manual

## Certificazioni, report e compatibilità

