

Elite[™] Cabinet & Rack Enclosures

Custom enclosures without the custom price

- » Fully customizable for your specific applications
- » Numerous cooling options
- » Extensive cable management
- » Two-day custom turnaround
- » Lifetime guarantee

.....

Get exactly what you need and want.



Robust cabinets for any application

More features.

The Elite Cabinet family from Black Box delivers more features and options than any other Black Box cabinet—more door and panel choices, more cable management, features like high-flow mesh on all mesh doors, and dual universal PDU mounting brackets.

Plus Elite Cabinets feature heavy-duty, welded steel construction and come with the protection of a lifetime Black Box[®] Double Diamond[™] warranty. The cabinets arrive fully assembled and ready to populate.

More choices.

Elite Cabinets are specifically designed to be adaptable to your exact needs. Whether you need a high-airflow cabinet for your data center or a small, secure cabinet for an office, the Elite Cabinet family has exactly the cabinet for you.

Select a pre-configured cabinet or have one customized to your specifications and shipped in only two business days. Choose from a wide range of sizes to suit all your data and server cabinet needs. Our Tech Support experts will help you specify the cabinet you need— FREE of charge.

More cable management.

Cable management is easy—extensive cable knockouts on the top and sides provide convenient cable entry. The cabinets feature multiple lacedown points throughout. For even more cable management, add our Horizontal and Vertical Lacing Bars or Front-to-Back Cable Managers (page 13).

More versatility.

Because Elite Cabinets come with a wide range of choices in frame sizes, rails, doors, and top and side panels, they adapt to nearly any application.

Choose your rails. Rails with M6 square holes are standard in server cabinets. They enable you to use vendor-supplied server rails that latch into the square holes to support servers, or to convert the square hole to a threaded M6, 10-32, or 12-24 hole by using cage nuts.

Use rails with 10-32 tapped holes for audio, datacomm, and telco equipment. Most shelves are also compatible with 10-32 rails.

Cabinet doors are available in solid, high-flow mesh, split high-flow mesh, smoked PLEXIGLAS[®], or solid with fans. You also can choose a cabinet with no doors. Side panels can be solid or vented, or you can leave them off. All Elite Cabinets have our high-flow mesh, which improves airflow approximately 10% over typical cabinets.

Cabinet tops are customizable, too—choose a top panel with or without fans, or use the top opening to rackmount up to 12U of shallow components such as patch panels or power strips. For more information, call our FREE Tech Support.


For data center installations, Elite Cabinets are Ladder Rack ready with the addition of the optional Ladder Rack Bracket (page 14).

• ****** WARRANTY — Lifetime

Protect your IT investments

Environmental monitoring is a cost-effective, proactive way to protect your investments from climate, overheating, theft, etc. Find out more about AlertWerks[™] at **blackbox.com/go/AlertWerks** or get FREE, live help in less than 30 seconds at **724-746-5500**.

More features and options than any other Black Box cabinet.



Most common cabinet configurations are ready to ship today.

These popular Elite Cabinet configurations are in stock and ready to ship now. Don't see what you need here? Just turn the page for details on customizing your cabinet to your exact specifications.



EC45U2436SMDSSNK: left: front view; right: rear view



EC45U2436SPDS3NK: left: front view; right: rear view

Item	Code
Elite™ Cabinets	
84"H (45U) x 24"W x 36"D	
Mesh Front and Rear Doors, Solid Side	e Panels, Keyed Lock
M6 Rails	-
Mesh Top Panel	EC45U2436SMMSMNK
3-Fan Top Panel	EC45U2436SMMS3NK
6-Fan Top Panel	EC45U2436SMMS6NK
10-32 Tapped Rails	
Mesh Top Panel	EC45U2436TMMSMNK
3-Fan Top Panel	EC45U2436TMMS3NK
6-Fan Top Panel	EC45U2436TMMS6NK
Mesh Front Doors, Split Mesh Rear Do	oor, Solid Side Panels, Keyed Lock
M6 Rails	
Mesh Top Panel	EC45U2436SMDSMNK
3-Fan Top Panel	EC45U2436SMDS3NK
6-Fan Top Panel	EC45U2436SMDS6NK
10-32 Tapped Rails	
Mesh Top Panel	EC45U2436TMDSMNK
3-Fan Top Panel	EC45U2436TMDS3NK
6-Fan Top Panel	EC45U2436TMDS6NK

Item	Code
Elite Cabinets (Continued)	
84"H (45U) x 24"W x 36"D (Continued)	
PLEXIGLAS [®] Front Door, Mesh Rear Door, Solid S	Side Panels, Keyed Lock
M6 Rails	
Mesh Top Panel	EC45U2436SPMSMNK
3-Fan Top Panel	EC45U2436SPMS3NK
6-Fan Top Panel	EC45U2436SPMS6NK
10-32 Tapped Rails	
Mesh Top Panel	EC45U2436TPMSMNK
3-Fan Top Panel	EC45U2436TPMS3NK
6-Fan Top Panel	EC45U2436TPMS6NK
PLEXIGLAS® Front Door, Split Mesh Rear Door, So	olid Side Panels, Keyed Lock
M6 Rails	-
Mesh Top Panel	EC45U2436SPDSMNK
3-Fan Top Panel	EC45U2436SPDS3NK
6-Fan Top Panel	EC45U2436SPDS6NK
10-32 Tapped Rails	
Mesh Top Panel	EC45U2436TPDSMNK
3-Fan Top Panel	EC45U2436TPDS3NK
6-Fan Top Panel	EC45U2436TPDS3NK
No Doors or Sides, Mesh Top Panel	
M6 Rails	EC45U2436SNNNMNN
84"H (45U) x 24"W x 42"D	
Mesh Front and Rear Doors, Solid Side Panels, Ke	eyed Lock
M6 Rails, Mesh Top Panel, Anti-Tip Legs	
	EC45U2442SMMSMYK
Mesh Front Door, Split Mesh Rear Door, Solid Sic	le Panels, Keyed Lock
M6 Rails, Mesh Top Panel, Anti-Tip Legs	-
	EC45U2442SMDSMYK

Item	Code
	Coue
Elite [™] Cabinets (Continued) 84"H (45U) x 30"W x 32"D	
PLEXIGLAS® Front Door, Mesh Rear Door	Solid Side Panels Keved Lock
M6 Rails	, Solid Side Fallels, Reyed LOCK
3-Fan Top Panel	EC45U3032SPMS3NK
10-32 Tapped Rails	EC450505251 MI5510K
Mesh Top Panel	EC45U3032TPMSMNK
3-Fan Top Panel	EC45U3032TPMS3NK
6-Fan Top Panel	EC45U3032TPMS6NK
PLEXIGLAS Front Door, Split Mesh Rear D	
M6 Rails	Jool, Jolid Side Fallels, Reyed Lock
3-Fan Top Panel	EC45U3032SPDS3NK
10-32 Tapped Rails	EC450505251 D5510K
Mesh Top Panel	EC45U3032TPDSMNK
3-Fan Top Panel	EC45U3032TPDS3NK
6-Fan Top Panel	EC45U3032TPDS5NK
84"H (45U) x 30"W x 36"D	LC45050521FD30NK
PLEXIGLAS Front Door, Mesh Rear Door,	Solid Side Papels, Keved Lock
M6 Rails	Solid Side Fallels, Reyed LOCK
3-Fan Top Panel	EC45U3036SPMS3NK
10-32 Tapped Rails	EC450505051 WISSINK
Mesh Top Panel	EC45U3036TPMSMNK
Solid Top Panel	EC45U3036TPMSSNK
3-Fan Top Panel	EC45U3036TPMS3NK
6-Fan Top Panel	EC45U3036TPMS6NK
PLEXIGLAS Front Door, Split Mesh Rear D	
M6 Rails	Jool, Jolid Side Fallels, Reyed Lock
3-Fan Top Panel	EC45U3036SPDS3NK
10-32 Tapped Rails	EC430303031 D3311K
Mesh Top Panel	EC45U3036TPDSMNK
Solid Top Panel	EC45U3036TPDSSNK
3-Fan Top Panel	EC4503036TPDS3NK
6-Fan Top Panel	EC4503036TPDS6NK
84"H (45U) x 30"W x 42"D	20430303011230111
Mesh Front and Rear Doors, Solid Side Pa	anels Keved Lock
M6 Rails, Mesh Top Panel, Anti-Tip Leg	
	EC45U3042SMMSMYK
Mesh Front Door, Split Mesh Rear Door, S	
M6 Rails, Mesh Top Panel, Anti-Tip Leg	
	EC45U3042SMDSMYK
79"H (42U) x 30"W x 42"D	2045050425100510111
Mesh Front and Rear Doors, Solid Side Pa	anels Keved Lock
M6 Rails	
Mesh Top Panel	EC42U3042SMMSMNK
PLEXIGLAS Front Door, Mesh Rear Door,	
10-32 Tapped Rails	Solid Side Fallels, Reyed Ebelt
Mesh Top Panel	EC42U3042TPMSMNK
6-Fan Top Panel	EC42U3042TPMS6NK
Mesh Front Door, Split Mesh Rear Door, S	
M6 Rails	Solid Side Fallels, Reyed Lock
Mesh Top Panel	EC42U3042SMDSMNK
PLEXIGLAS Front Door, Split Mesh Rear D	
10-32 Tapped Rails	soon, sona side raneis, riegea zoek
Mesh Top Panel	EC42U3042TPDSMNK
6-Fan Top Panel	EC42U3042TPDS6NK
79"H (42U) x 24"W x 42"D	
Mesh Front and Rear Doors, Solid Side Pa	anels Keved Lock
M6 Rails	ATCIS, REYEU LOCK
Mesh Top Panel	EC42U2442SMMSMNK
Mesh Front Door, Split Mesh Rear Door, S	
M6 Rails	Jona Jiac I ancis, NEYEU LUCK
Mesh Top Panel	EC42U2442SMDSMNK
Mesh top fuller	

Item	Code
Elite Cabinets (Continued)	
72"H (38U) x 30"W x 32"D	
PLEXIGLAS Front Door, Mesh Rear Door, Solid Side	e Panels, Keyed Lock
M6 Rails	-
3-Fan Top Panel	EC38U3032SPMS3NK
10-32 Tapped Rails	
Mesh Top Panel	EC38U3032TPMSMNK
Single-Fan Top Panel	EC38U3032TPMS1NK
3-Fan Top Panel	EC38U3032TPMS3NK
6-Fan Top Panel	EC38U3032TPMS6NK
PLEXIGLAS Front Door, Split Mesh Rear Door, Solic	l Side Panels, Keyed Lock
M6 Rails	
3-Fan Top Panel	EC38U3032SPDS3NK
10-32 Tapped Rails	
Mesh Top Panel	EC38U3032TPDSMNK
Single-Fan Top Panel	EC38U3032TPDS1NK
3-Fan Top Panel	EC38U3032TPDS3NK
6-Fan Top Panel	EC38U3032TPDS6NK
48"H (24U) x 24"W x 42"D, M6 Rails	
Mesh Front and Rear Doors, Solid Side Panels, Mes	
Mark Frank Dans, Calit Mark Dans Dans, Calid Cida	EC24U2442SMMSMNK
Mesh Front Door, Split Mesh Rear Door, Solid Side Mesh Top Panel, Keved Lock	
	EC24U2442SMDSMNK
PLEXIGLAS Front Door, Mesh Rear Door, Solid Side	EC24U2442SPMSMNK
Mesh Top Panel, Keyed Lock PLEXIGLAS Front Door, Split Mesh Rear Door, Solic	
Mesh Top Panel, Keyed Lock	EC24U2442SPDSMNK
No Doors or Sides, Mesh Top Panel	EC2402442SPDSIVINK EC2402442SNNNMNN
48"H (24U) x 30"W x 32"D, 10-32 Tapped Rails	
PLEXIGLAS Front Door, Mesh Rear Door, Solid Side	Panels Keved Lock
Mesh Top Panel	EC24U3032TPMSMNK
Solid Top Panel	EC2403032TPMSSNK
Single-Fan Top Panel	EC24U3032TPMS1NK
3-Fan Top Panel	EC24U3032TPMS3NK
6-Fan Top Panel	EC24U3032TPMS5NK
PLEXIGLAS Front Door, Split Mesh Rear Door, Solic	
Mesh Top Panel	EC24U3032TPDSMNK
Solid Top Panel	EC24U3032TPDSSNK
	EC24U3032TPDS3NK EC24U3032TPDS1NK
Single-Fan Top Panel 3-Fan Top Panel	EC24U3032TPDS1NK EC24U3032TPDS3NK
6-Fan Top Panel	EC24U3032TPDS5NK EC24U3032TPDS6NK

Don't see what you need here? To configure your own Elite Cabinet, see pp. 6–7.

| 5

Don't see exactly what you want? We'll build it for you in two days or less.

If one of our pre-configured cabinets doesn't work for you, it's easy to build your own Elite[™] Cabinet to your specifications. Just use the codes (**right**) to fill in the line on the **bottom of the facing page**, matching colors as you go. When you're done, just call us at **724-746-5500** with the number, and we'll have your custom-built cabinets on your doorstep in a flash.

The example **below** is a 79"H (42U) x 30"W x 42"D cabinet with M6 rails, a mesh front door, a split mesh rear door, solid side panels, a mesh top, anti-tip legs, and keyed locks. Need help? Call our fast, FREE Tech Support at **724-746-5500**.


Example:


E C 4 2 U 3 0 4 2 S M D S M	YK		М	S	D	Μ	S	2	4	0	3	U	2	4	С	Ε	
-----------------------------	----	--	---	---	---	---	---	---	---	---	---	---	---	---	---	---	--



Step 1:

Choose your enclosure.





Fill in the blocks below to get your ideal cabinet's SKU. For help configuring your cabinet, call our FREE Tech Support at 724-746-5500.

* Doors have either a keyed, combination, biometric, or hybrid lock. Choose "None" when there is no door.

† Biometric locks are not compatible with split doors. The Biometric option includes a biometric lock on one door and a keyed lock on the other; the Hybrid option includes a biometric lock on one door and an electronic lock on the other. For more information on Intelli-Pass[™] Biometric Access Control for Cabinets, see page 8.

| 7

The cabinet lock that's highly secure, yet opens at the touch of a fingertip.

- Eliminates keys that can be lost, stolen, or duplicated; no need to remember combinations.
- The lock opens only when an authorized user touches the fingerprint scanner—one fingertip provides cabinet access.
- LEDs on front of the handle monitor status.
- Manageable across your network as part of the Intelli-Pass biometric access control system. For more information, see blackbox.com/go/Intelli-Pass.
- Continues to operate normally even if your network fails network communication isn't required for fingerprint verification.
- Controller unit and optional backup battery are housed in a compact 1U rackmount chassis.
- **WARRANTY** 1 Year

The Intelli-Pass™ Biometric Access Control for Cabinets provides the perfect blend of security and simplicity—the touch of one fingertip gives authorized users access. One control unit unlocks the front door andwith the purchase of an additional electric-lock door handle-the rear door.

Secure two-part architecture

The Intelli-Pass cabinet lock features the same unique two-part architecture as the rest of the Intell-Pass family (for details, visit blackbox. com/go/Intelli-Pass). A reader unit mounts outside the cabinet on the locking handle, and a controller unit is rackmounted inside the cabinet. Because the reader and controller units are separate, no connections in the reader unit are exposed to the outside. The controller is secure inside the cabinet, and a hacker can't cut wires or spoof the signals to open the door.

Secure locking

The Intelli-Pass system in each cabinet operates independently, so if the network fails, your cabinet locks will not.

If you're using Intelli-Pass in a cabinet without a UPS for backup power, order model SAC550CAB with battery backup. This optional battery backup ensures that Intelli-Pass works even if power fails.

Integrates seamlessly into your Intelli-Pass system

Intelli-Pass Biometric Access Control for Cabinets works as part of a complete Intelli-Pass solution. Intelli-Pass Management and Enrollment Software audits when someone accesses the cabinet using their biometric fingerprint. The software monitors real-time status information, provides an access trail, and enables you to handle all the enrollment and management of the secure cabinets from a single desktop.

Alarming

Intelli-Pass can work with your building's alarm system to automatically open cabinets when the alarm goes off, allowing emergency access to critical equipment. The door handle is also equipped with a keyed lock for emergency access. Plus you can connect the controller to door sensors, enabling the system to alert you if a door is opened.

Order with your cabinet or install it later

If you wish to install the Intelli-Pass Biometric Access Control on an existing Elite Cabinet, order the system at right, or you can specify it when you order an Elite Cabinet. It also fits many other standard server cabinets. For more information, call our FREE Tech Support at 724-746-5500.



TECH SPECS Power — Internal power supply:

100-240-VAC, 50/60 Hz, 3.5 amps

Size — Chassis: 1.75"(1U) H x 19"W x

Door handle: Fits 1" x 5.9"

(2.5 x 15 cm) opening

8"D (4.4 x 48.3 x 20.2 cm);

Environmental — Operating Temperature: 32 to 158° F

(0 to 70° C)

Connectors — Chassis:

- (1) RJ-45 network, (1) RJ-45 front door,
- (1) RJ-45 rear door,
- (1) 6-position terminal block,
- (1) 12-position terminal block

What's Included:

- Fingerprint sensor unit
- Door handle with integrated lock
- 1U rackmount chassis containing control unit and optional battery
- Power cord
- (2) patch cables
- (2) keys

Item	Code
Intelli-Pass Biometric Access Control for Cabinets	
with Battery Backup	SAC550CAB
without Battery Backup	SAC550CABNB
If you also need a lock for the rear door, order	
Door Handle with Integrated Lock	SAC550CABL
To detect forced entry, order	
Security Sensor	SAC550CABS


Accessorize!

Add accessories to add function.

After you select the right cabinet configuration, it's time to accessorize your cabinet with cable management, keyboard trays, and all the parts that make your Elite[™] Cabinet perfect for your application.

Change your cabinet configuration.

If you already own an Elite Cabinet, it's easy to change top panels and other parts when your requirements change—parts such as top panels can be changed in a just few minutes with basic tools.




Coolness for your cabinets—everything you need to improve ventilation in your Elite Cabinet.

Top Fan Panels





ECTOP2F



- Help cool cabinets by drawing air upward. ٠
- Change top panels when your ventilation needs change.

Item

Split Fan

84" x 30"

- Deliver up to 1100 cfm of ventilation.
- **WARRANTY** Lifetime

Split Fan Doors



Item

Top Fan Panels

. 3-Fan 225-cfm

6-Fan 450-cfm

Single 10" Fan 550-cfm

Dual 10" Fan 1100-cfm



ECTOPF10

Code

ECTOPF
ECTOP2F
ECTOPF10
FCTOP2F10



- Keep the equipment in your Elite[™] Cabinet cool.
- Doors can be mounted on the front or rear of the cabinet.
- For 220-VAC power environments. IEC-60320-C13 outlet; power cord
- is not included.
- WARRANTY Lifetime

em	Code
olit Fan Doors	
24U 48" x 24"	EC480324SF220
48" x 30"	EC480330SF220
38U 72" x 30"	EC720330SF220
42U 79" x 24"	EC790324SF220
79" x 30"	EC790330SF220
45U 84" x 24"	EC840324SF220

EC720330SF220

Bottom Filter Kits

- Fit in the large bottom opening of Elite Cabinets.
- Permit air circulation while filtering out dust and other airborne debris.
- **WARRANTY** Lifetime

GUARANTEED ECBFKL3042

EC840330SF220

Air Dams Mount on the front rails of Elite Cabinets. Keep cool air in the front of the cabinet where it can be used by equipment. **WARRANTY** — Lifetime Code Item Code Air Dams for 24" Wide 42U & 45U Cabinets 80324SF220 80330SF220 ECAD24 for 30" Wide 42U & 45U Cabinets 20330SF220 90324SF220 ECAD30 90330SF220 for 24" Wide 24U & 38U Cabinets

ECAD24S for 30" Wide 24U & 38U Cabinets FCAD30S

Filler Panels

- Keep cool air from dissipating before it reaches the top of the rack
- Matte black finish. ٠
- Mount easily to a 19" cabinet or rack with four included 10-32 screws.
- **WARRANTY** Lifetime

RoHS — Yes

Filler Panels, Black

1U (1.75")

2U (3.50")

4U (7.00")

5U (8.75")

6U (10.50")

(5.25") 3U

Item





Code

RMTB01
RMTB02
RMTB03
RMTB04
RMTB05
RMTB06

for 24"W x 36"D Cabinets for 24"W x 42"D Cabinets for 30"W x 32"D Cabinets for 30"W x 36"D Cabinets for 30"W x 42"D and 48"D Cabinets

Code ECBFKL2436

ECBFKL2442 ECBFKL3032 ECBFKL3036 ECBFKL3042

BLACK BOX

724-746-5500 blackbox.com/go/Elite

10

Item

Bottom Filter Kits



Chimney Top

- Provides a closed hot air return between the top of an Elite cabinet and a drop ceiling plenum.
- Includes a chimney for the Elite Cabinet small 3U top opening plus a solid panel to cover the large top opening.
- · Chimney adjusts from 20" to 34".
- Add the Fan Tray to the Chimney Top to increase its efficiency.
- The Fan Tray has two fans providing 600-cfm of air movement.

• ++ WARRANTY — Lifetime	
Item	Code
Chimney Top	ECTOPCHIM
To improve airflow, add Fan Tray for ECTOPCHIM (600-cfm)	ECTOPCHIMFT

Enclosure Blower



- Cools cabinets by improving air circulation.
- Draws cool air from the bottom of the cabinet and delivers it right across the front of servers or other network components.
- Air distribution cools cabinet hot spots by 15° F, extending server life and minimizing downtime.
- Requires only 2U of mounting space.
- Fits on standard 19" rails.
- Installs easily on bottom of any EIA-30 compliant cabinet.
- Designed for quiet, long-life operation.
- Keep circulating air free of dust. The optional Filter Assembly removes up to 80% of 2-micron particles from circulating air.
- **WARRANTY** 1 Year

NOTE: Works with any EIA-30 compliant cabinet from any manufacturer.

Item	Code
Enclosure Blower	RM801
You may also need	
Enclosure Blower Filter Assembly	RM802
Enclosure Blower Replacement Filters (12)	RM803

Air Funnel Kits

GUARANTE



- Cool cabinets by improving air circulation.
- Draw cool air from the bottom of the cabinet and deliver it right across the front of servers or other network components.
- Air distribution cools cabinet hot spots by 15° F, extending server life and minimizing downtime.
- Require only 2U of mounting space.
- Fit on standard 19" rails.
- WARRANTY Lifetime

Code Item Air Funnel Kits for 24"W x 36"D ECAIRFLOW36 for 24"W x 42"D and 30"W x 42"D ECAIRFLOW42 Air Funnel Kits with Dual Fan Tray for 24"W x 36"D ECAIRFLOW2436FT for 24"W x 42"D ECAIRFLOW2442FT for 30"W x 42"D ECAIRFLOW3042FT

Cold Aisle Containment System



- Use this kit to shut off the aisle ends to contain cool air for cold aisle containment.
- Create more efficient cold or hot aisles by reducing air recirculation.
- Includes one pair of center-opening doors and all the parts you need for installation.
- **WARRANTY** Lifetime

Item

Cold Aisle Containment System 42 U 45 U

Code

EC42U48WCD EC45U48WCD

FREE, live help in 30 seconds or less!

A little organization makes cabinets more efficient.

guaranteed

Code

Code

ECTOPB

EC24WTCTK

Cable Trough Kits for Elite Cabinets

- Route cables across the top of an Elite Cabinet in multicabinet installations.
- Install anywhere along the top of the cabinet.
- Include (10) 10-32 mounting screws
- **WARRANTY** Lifetime



Item	
Cable Trough Kits 24" Wide	
30" Wide	

Brush Grommet Top Panel

- Top panel keeps your cable entry organized and clean.
- Fits top opening in Elite Cabinets.
- Includes grommet kit and mounting hardware.
- **WARRANTY** Lifetime



Item

Brush Grommet Top Panel

Brush Grommet Kit for 3U Opening



- Fits the small 3U opening on the top of Elite Cabinets.
- Brushes enable you to run cable into the cabinet while keeping out dust and contaminants.
- Can be installed along with the Elite Cabinet Waterfall Brackets for 3U Top Opening (ECW3U), above, right.

WARRANTY — Lifetime

Item

12

Brush Grommet Kit for 3U Opening

C	Code
ECBO	GK3U

Code

EC3UGP

Gland Plate





Item

Gland Plate

- Fits the top rear 3U opening on an Elite Cabinet or an Elite Wallmount Cabinet.
- Enables you to route cables into the cabinet while sealing off the opening to help prevent dust or to control ventilation.
- WARRANTY Lifetime



724-746-5500 | blackbox.com/go/Elite

Waterfall Brackets for 3U Top Opening

- Fit the small 3U opening on the top of Elite Cabinets.
- Enable you to maintain bend radius when routing cable into the top of the cabinet.

WARRANTY — Lifetime

Item

Waterfall Brackets for 3U Top Opening

Conduit Knockout Panel

- Fits the small 3U opening on the top of Elite[™] Cabinets.
- Three knockout plates on 5" centers enable you to route 1", 2", or 3" conduit.
- Includes eight screws.
- **WARRANTY** Lifetime ٠

Item

Conduit Knockout Panel

Light Kit

- Illuminates your Elite Cabinet to make your work easier.
- 18-watt fluorescent light.
- WARRANTY Lifetime



Item Light Kit

Bottom Brush Grommet Kits

- Run cable into the cabinet while limiting airflow and keeping out dust and contaminants.
- Bottom Brush Grommet Kits fit over the large bottom opening in your Elite cabinet and include a cover for the rear cable cutout.
- **Bottom Rear Brush Grommet** Kits fit the rear cable cutout.
- **WARRANTY** Lifetime

Item

Bottom Brush Grommet Kits	
for 24"W x 36"D Cabinets	ECBGKL2436
for 24"W x 42"D Cabinets	ECBGKL2442
for 30"W x 32"D Cabinets	ECBGKL3032
for 30"W x 36"D Cabinets	ECBGKL3036
for 30"W x 42"D & 48"D Cabinets	ECBGKL3042
Bottom Rear Brush Grommet Kits	
for 24"W Cabinets	ECBBGKS24
for 30"W Cabinets	ECBBGKS30

ECBGKL2436



guaranteed

Code

ECW3U

Code ECP3U

Code

Elite Cabinet Accessories

GUARANTEED

ECVCM

ECVLB72

GUARANTEED

ECJACKPANEL46



Vertical Lacing Bars for Elite Cabinets

- Attach cables to this bar to keep your Elite cabinet organized and neat.
- Requires a Horizontal Lacing Bar (ECHLB22, ECHLB36, ECHLB42, below) for mounting.
- Order (2) for a 48"H cabinet, (3) for a 72"H or 79"H cabinet, or (4) for an 84"H cabinet.
- **WARRANTY** Lifetime

Vertical Sectional Cable Manager

- · Adds vertical cable management in 11U increments.
- **WARRANTY** Lifetime

tem	Code
ertical Lacing Bars for Elite Cabinets	
for 48"H Cabinets	ECVLB48
for 72"H Cabinets	ECVLB72
for 79"H Cabinets	ECVLB79
for 84"H Cabinets	ECVLB84
ertical Sectional Cable Manager	FCVCM

Vertical Jack Panels

- Hold connectors vertically outside the rails. · Maximum-density design makes the most of
- your precious cabinet space. • Support many media types, including jacks and
- adapters for copper UTP and STP, fiber, and S-Video.
- Connections look neat because the panel's industry-standard keystone openings enable flush fitting of jacks.
- Use with any keystone jacks; we recommend GigaBase2 CAT5e Jacks and GigaTrue2 CAT6 Jacks, see blackbox.com.
- Use with 30"W Elite Cabinets only.
- Mounting hardware included.
- **WARRANTY** Lifetime

Code ECJACKPANEL46 ECJACKPANEL92

Horizontal Lacing Bars



- Attach cables to this bar to keep your Elite Cabinet organized and neat.
- **WARRANTY** Lifetime

Code Horizontal Lacing Bars for 30"W x 32"D Cabinets ECHLB32 for 30"W x 36"D Cabinets ECHLB36 for 30"W x 42"D and 48"D Cabinets ECHLB42

FREE, live help in 30 seconds or less!



Additions and replacement parts for your Elite Cabinet.

High-Flow Mesh Door

- Higher open area than standard mesh doors for optimal airflow to hot servers.
- EC790224MHF provides 840.2 square inches of open area; EC840224MHF provides 914.4 square inches of open area.
- **++ WARRANTY** Lifetime

Item Code High-Flow Mesh Door

for 42U x 24"W Cabinets EC790224MHF for 45U x 24"W Cabinets EC840224MHF

Extra Sets of Rails

- Elite Cabinets come standard with two sets of rails (front and back). Add an extra set to mount shallow patch panels or PDUs behind equipment on the primary rails.
- Choose from M6 square holes or 10-32 tapped holes.
- 12-gauge rails are marked in 1U increments for easy equipment installation.
- Fully adjustable front to rear.
- **WARRANTY** Lifetime

Item

Extra Sets of Rails	
M6	
for 48"H Cabinets	EC48M6
for 72"H Cabinets	EC72M6
for 79"H Cabinets	EC79M6
for 84"H Cabinets	EC84M6
10-32	
for 48"H Cabinets	EC48T
for 72"H Cabinets	EC72T
for 79"H Cabinets	EC79T
for 84"H Cabinets	EC84T

Anti-Tip Legs

- Telescoping legs help prevent your Elite Cabinet from tipping over.
- Easy to install.
- Project 11" from base of cabinet.
- **** WARRANTY** Lifetime

ltem

Anti-Tip Legs





Ladder Rack Bracket

- Easily attach a ladder rack to an Elite[™] Cabinet for cable management.
- Includes mounting hardware.
- **++** WARRANTY Lifetime

ltem

Solid and Perforated Top Panels

• Fit the large top opening on Elite Cabinets.

Ladder Rack Bracket, 24"W

- Choose the Perforated Top Panel for additional ventilation.
- For Top Fan Panels, see page 10.
- **++** WARRANTY —Lifetime

ltem

Top Panels	
Solid	ECTOPS
Perforated	ECTOPP

guaranteed

Code

EC24LR

Code

SOLUTE

GUARANTEED

Solid Rear Bottom Panels



- Cover the cable cutout on the bottom rear of Elite[™] Cabinets.
- Standard Elite Cabinets have rectangular cable cutouts at the bottom rear of the cabinet—this panel can cover that opening if you don't wish to use it for cable management.
- ****** WARRANTY Lifetime

Item	Code
Solid Rear Bottom Panels for 24"W Cabinets for 30"W Cabinets	ECBSKS24 ECBSKS30
Solid Bottom Panels	— —
 Standard Elite Cabinets are open on the bottom—this panel covers the large bottom opening. WARRANTY — Lifetime 	GUARANTEED
Item	Code
Solid Bottom Panels	
for 24"W x 36"D Cabinets for 24"W x 42"D Cabinets	ECBSKL2436 ECBSKL2442

Code ECAT1	 for 30"W x 32"D Cabinets for 30"W x 36"D Cabinets for 30"W x 42"D & 48"D Cabinets	ECBSKL3032 ECBSKL3036 ECBSKL3042

14 | *** BLACK BOX** 72

724-746-5500 | blackbox.com/go/Elite

GUARANTEEL

23" Mounting Kits for 30"W Elite Cabinets



- Enable you to convert standard 19" rails to 23" rails.
- Include four (4) brackets and eight (8) screws.
- **++** WARRANTY Lifetime

Item

23" Mounting Kits for 30"W Cabinets
for 30"W x 32"D Cabinets
for 30"W x 36"D Cabinets
for 30"W x 42"D Cabinets

EC2	3MK32
EC2	3MK36
EC2	3MK42

Code

Vertical PDU 19" Mounting Kit, 0U

- Mounts a PDU or other 19" 1U rackmount equipment behind the rails without using any rack space.
- Includes (2) 1U brackets.
- **WARRANTY** Lifetime

Item Vertical PDU 19" Mounting Kit, 0U GUARANTEED

Code ECPDUMK

Dual PDU Mounting Brackets



ECPDUMK24

- Provide an additional pair of brackets to mount more than two PDUs or to mount PDUs in more than one corner of the cabinet.
- ****** WARRANTY Lifetime

Item	Code
Dual PDU Mounting Brackets, 1 Pair*	
for 24"W Cabinets	ECPDUMK24
for 30"W Cabinets	ECPDUMK30
* A pair of Dual PDU Mounting Brackets is included with the Elite	e Cabinet base frame.

Networking Hardware/Baying Kit

- Kit for baying or networking two Elite Cabinets together.
- Includes (4) ⁵/₆ wing nuts,
 (4) ⁵/₆ thumbscrews with shoulder, (4) ⁵/₆ split lock washers, and (8) ⁵/₆ flat washers
- **** WARRANTY** Lifetime

ltem

Networking Hardware/Baying Kit

Code ECNH


Black Box Custom Solutions

Don't see what you need? Chances are we can build it.

Whether you manage a small-office network or a large data center, you know it can be difficult to pin down an enclosure that:

- Fits your space.
- Holds components compactly and securely.
- Leaves room for expansion.
- Provides adequate cooling.
- Has room for power distribution.
- Manages cable neatly.
- Makes components easy to access.
- Locks when you need it to.

You can count on Black Box to engineer a cabinet solution to match your space and application. Black Box engineers have been designing data centers for more than 25 years let us use our experience to help you build yours.



Typical hot aisle/cold aisle configuration with hot air vent to the plenum via a Chimney Top (ECTOPCHIM), **p. 11**. Also shown is the Cold Aisle Containment System (EC45U48WCD), **p. 11**.


The wallmount cabinet that makes adding equipment easy!

- Large openings in back panel enable you to easily install patch panels or other prewired equipment.
- Accessories that fit the 3U opening in other Elite cabinets also fit into these cabinets' 3U opening.
- Doors can be reversed to open left or right.
- Double hinged for easy access to rear of equipment.
- Have keylocks on front and side.
- Ship with one conduit panel.
- Include one pair of 10-32 rails. Order additional rails for 4-point mounting.
- **++** WARRANTY Lifetime

Elite Wallmount Cabinets from Black Box have all the quality you've come to expect plus features that set them apart from other wallmount cabinets. They feature large openings on the back panel that enable you to simply slide in a loaded patch panel.

If you want to add fans, a Brush Grommet Kit, a Waterfall Radius Bracket, or other accessory, it couldn't be easier. That's because just about any Elite accessory that fits into the 3U opening on the top of an Elite cabinet will work with the wallmount cabinet.

For even more versatility, optional brackets attach to the back panel of the cabinet and enable you to rackmount patch panels behind the equipment in the cabinet at 45° or 90° angles.



Cabinet backs have openings that enable you to insert loaded patch panels without having to rewire.

Smoked PLEXIGLAS® front door.

Keylocks on front and side.


Openings on back enable you to insert_ loaded patch panels without rewiring.

Cutouts for ventilation.

The cabinet is reversible top to bottom, so the back section opens left or right.










Optional Waterfall Bracket (ECW3U) installs in 3U top opening. For information, see page 12

Buyer's Guide | Elite Wallmount Cabinets

							,
Code	G Rear Section Depth	Main Body Depth	Interior Width	● Rack Units	G Exterior Depth	Exterior Width	Exterior Height
EWM12U242418	7"	9.125"	23.75"	12U	18"	24"	24"
EWM12U242424	7"	15.125"	23.75"	12U	24"	24"	24"
EWM12U242430	7"	21.125"	23.75"	12U	30"	24"	24"
EWM20U362418	7"	9.125"	23.75"	20U	18"	24"	36"
EWM20U362424	7"	15.125"	23.75"	20U	24"	24"	36"
EWM20U362430	7"	21.125"	23.75"	20U	30"	24"	36"
EWM26U482418	7"	9.125"	23.75"	26U	18"	24"	48"
EWM26U482424	7"	15.125"	23.75"	26U	24"	24"	48"
EWM26U482430	7"	21.125"	23.75"	26U	30"	24"	48"



Item		Code
Elite Wallmount Cabinets		
24"H x 24"W (12U)		
18"D	EWM12U	J242418
24"D	EWM12U	
30"D	EWM12U	242430
36"H x 24"W (20U)		
18"D	EWM20U	
24"D	EWM20U	
30"D	EWM20U	362430
48"H x 24"W (26U)		
18"D	EWM26U	
24"D	EWM26U	482424
30"D	EWM26U	482430
You may also need		
90° Angle Bracket, 2U, Pair		
	EWN	190DAB
45° Angle Bracket, 4U, Pair		
	EWN	145DAB
Spare Rails		
12U		/12URK
20U		120URK
26U		<u>126URK</u>
Fans	F	RMT373

© Copyright 2011. Black Box Corporation. All rights reserved. Black Box® and the Double Diamond logo are registered trademarks, and Elite[™], AlertWerks[™], and Intelli-Pass[™] are trademarks, of BB Technologies, Inc. Any third-party trademarks appearing in this publication are acknowledged to be the property of their respective owners.

EC45U2436SMMSMNK_(27033)_4-11v2