

2m Computer Power Cord - BS-1363 to IEC 320 C19

StarTech ID: PXTUKC192M



The PXTUKC192M 2m Computer Power Cord features a BS 1363 (Type G) plug on one end and an IEC 320 C19 connector on the other - a durable, heavy duty cable designed to power your computer or server room equipment from a grounded power outlet.

This high quality C19 UK Power Cord is backed by StarTech.com's Lifetime Warranty.

Applications

- Can be used in a server room to provide a reliable power connection for server applications
- Power your computer or other C19 equipped device from a BS-1363 UK power outlet

Features

- Rated to carry 250V at 13A
- 1.5mm² wire
- BSI, RoHS approval
- Fully molded strain relief connectors

Technical Specifications

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Type	PVC - Polyvinyl Chloride
Connector B	1 - IEC 60320 C19 Power Receptacle
Connector A	1 - BS 1363 Power (UK) Plug
Color	Black
Wire Gauge	1.5mm ²
Cable Length	2 m [6.6 ft]
Product Length	2 m [6.6 ft]
Product Weight	350 g [12.4 oz]
Input Voltage	250 AC
Input Current	13 A
Shipping (Package) Weight	350 g [12.4 oz]
Package Quantity	1
Included in Package	1 - 2m Computer Power Cord - BS-1363 to IEC 320 C19

Certifications, Reports and Compatibility

