

## Cisco IP Phone 8841



The Cisco® IP Phone 8841 is a business-class collaboration endpoint that delivers high-fidelity, reliable, secure, and scalable voice communication for small to large enterprise businesses.

With the Cisco IP Phone 8841, you can increase personal productivity through an engaging user experience that is both powerful and easy-to-use. The IP Phone 8841 combines an attractive new ergonomic design with wideband audio for crystal clear voice communications, “always-on” reliability, encrypted voice communications to enhance security, and access to a comprehensive suite of unified communication features from Cisco on-premises and hosted infrastructure platforms and third party hosted call control.

The Cisco IP Phone 8841 offers five programmable line keys. You can configure keys to support either multiple directory numbers or call features such as speed dial. You can also boost productivity by handling multiple calls for each directory number, using the multicall-per-line feature. Fixed function keys give you one-touch access to applications, messaging, directory, as well as often-used calling features such as hold/resume, transfer, and conference. Backlit acoustic keys provide flexibility for audio path selection and switching.

Other key features of the phone follow:

- The Cisco IP Phone 8841 offers a 5-in. high-resolution (800 x 480) widescreen VGA backlit color display. Localized language support, including right-to-left on-screen text, meets the needs of global users.
- The phone supports a built-in Gigabit Ethernet switch for your PC connection.
- Support for Cisco EnergyWise™ technology makes the Cisco IP Phone 8841 more energy-efficient and ecofriendly; the phone is qualified by Energy Star organization.
- An optional wall-mount kit is orderable as a spare part for customers seeking this capability.

## Features and Benefits

Table 1 lists features and benefits of the Cisco IP Phone 8841.

**Table 1.** Features and Benefits

Features	Benefits
<b>Hardware Features</b>	
<b>Ergonomic design</b>	<ul style="list-style-type: none"> <li>The phone offers an easy-to-use interface and provides a traditional telephony-like user experience.</li> </ul>
<b>Graphical display</b>	<ul style="list-style-type: none"> <li>The 800 x 480, 24-bit color, 5-in. WVGA display provides scrollable access to calling features and text-based XML applications.</li> </ul>
<b>Handset</b>	<ul style="list-style-type: none"> <li>The handset is a standard wideband-capable audio handset (connects through an RJ-9 port).</li> <li>The standard coiled cord has a custom end for concealed cable routing beneath the phone (cord length is approximately 21 in. [55 cm] coiled and up to 72 in. (183 cm) extended).</li> <li>The handset is hearing aid-compatible (HAC) and meets Federal Communications Commission (FCC) loudness requirements for the Americans with Disabilities Act (ADA). Section 508 loudness requirements can be achieved using industry-standard inline handset amplifiers such as Walker Equipment W-10 or CE-100 amplifiers. The dial pad is also ADA-compliant.</li> </ul>
<b>Speaker phone</b>	<ul style="list-style-type: none"> <li>A full-duplex speakerphone gives you flexibility in placing and receiving calls with hands free. For added security, the audible dual tone multifrequency (DTMF) tones are masked when the speakerphone mode is used.</li> </ul>
<b>Analog headset</b>	<ul style="list-style-type: none"> <li>The analog headset jack is a standard wideband-capable RJ-9 audio port.</li> </ul>
<b>AUX port</b>	<ul style="list-style-type: none"> <li>You can use an auxiliary port to support electronic hookswitch control with a third-party headset connected to it.</li> </ul>
<b>Ethernet switch</b>	<ul style="list-style-type: none"> <li>An internal 2-port Cisco Ethernet switch allows for a direct connection to a 10/100/1000BASE-T Ethernet network (IEEE 802.3i/802.3u/802.3ab) through a RJ-45 interface with single LAN connectivity for both the phone and a co-located PC.</li> <li>The system administrator can designate separate VLANs (IEEE 802.1Q) for the PC and phone, providing improved security and reliability of voice and data traffic.</li> </ul>
<b>Keys</b>	<ul style="list-style-type: none"> <li>The phone has the following keys: <ul style="list-style-type: none"> <li>Line keys</li> <li>Soft keys</li> <li>Back and release keys</li> <li>Four-way navigation and select keys</li> <li>Hold/Resume, Transfer, and Conference keys</li> <li>Messaging, Application, and Directory keys</li> <li>Standard keypad</li> <li>Volume-control toggle key</li> <li>Speakerphone, headset, and mute keys</li> </ul> </li> </ul>
<b>Backlit indicator</b>	<ul style="list-style-type: none"> <li>The phone supports backlit indicators for the audio path keys (handset, headset, and speakerphone), select key, line keys, and message waiting.</li> </ul>
<b>Replaceable bezel</b>	<ul style="list-style-type: none"> <li>The phone includes a black bezel; an optional silver bezel is also orderable separately.</li> </ul>
<b>Dual-position foot stand</b>	<ul style="list-style-type: none"> <li>The display is easy-to-view and the buttons and keys are easy-to-use. The two-position foot stand supports viewing angles of 35 and 50 degrees; you can remove the foot stand for wall mounting, with mounting holes located on the base of the phone.</li> </ul>
<b>Wall-mountable</b>	<ul style="list-style-type: none"> <li>You can install the phone on a wall using an optional wall-mount kit (orderable separately).</li> </ul>
<b>Physical security</b>	<ul style="list-style-type: none"> <li>The phone is compatible with the Kensington Security Slot (K-Slot) antitheft system.</li> </ul>
<b>Power Features</b>	
<b>IEEE Power over Ethernet (PoE)</b>	<ul style="list-style-type: none"> <li>IEEE Power over Ethernet class 2. The phone is compatible with both IEEE 802.3af and 802.3at switch blades and supports both Cisco Discovery Protocol and Link Layer Discovery Protocol - Power over Ethernet (LLDP-PoE).</li> </ul>
<b>Cisco IP Phone Power Cube 4</b>	<ul style="list-style-type: none"> <li>This optional power cube is used as an AC-to-DC (48V) power supply for non-PoE deployments. Use of the power cube 4 also requires the use of one of the corresponding AC country cords.</li> </ul>

Features	Benefits
<b>Call-Control Support</b>	
<b>Cisco Unified Communications Manager</b>	<ul style="list-style-type: none"> <li>• 8.5.1 (Non-secured mode Only)</li> <li>• 8.6.2</li> <li>• 9.1.2</li> <li>• 10.5.2</li> <li>• 11.0 and later</li> </ul>
<b>Cisco Unified Communications Manager Express (Unified CME)</b>	<ul style="list-style-type: none"> <li>• 10.0 and later through fast track</li> </ul>
<b>Cisco Business Edition 6000 (BE 6000)</b>	<ul style="list-style-type: none"> <li>• 8.6.2</li> <li>• 9.1.2</li> <li>• 10.5.2</li> <li>• 11.0 and later</li> </ul>
<b>Cisco Hosted Collaboration Solution (HCS)</b>	<ul style="list-style-type: none"> <li>• 8.6.2 and later (using supported UCM versions above)</li> </ul>

## Licensing

The Cisco IP Phone 8841 requires an Enhanced User Connect License (UCL) in order to connect to Cisco Unified Communications Manager.

## Product Specifications

Table 2 lists the features and specifications of the Cisco IP Phone 8841.

**Table 2.** Features and Specifications

Features	Specifications
<b>Audio codec support</b>	<ul style="list-style-type: none"> <li>• G.711a-law and mu-law, G.722, G.729a, Internet Low Bitrate Codec (iLBC), and Internet Speech Audio Codec (iSAC)</li> </ul>
<b>Call features</b>	<ul style="list-style-type: none"> <li>• + Dialing</li> <li>• Abbreviated dialing</li> <li>• Adjustable ring tones and volume levels</li> <li>• Adjustable display brightness</li> <li>• Agent greeting</li> <li>• Auto-answer</li> <li>• Auto-detection of headset</li> <li>• cBarge</li> <li>• Busy Lamp Field (BLF)</li> <li>• Busy Lamp Field (BLF) Pickup</li> <li>• Busy Lamp Field (BLF) speed dial</li> <li>• Callback</li> <li>• Call forward</li> <li>• Call forward notification</li> <li>• Call filter</li> <li>• Call history lists</li> <li>• Call park</li> <li>• Call pickup</li> <li>• Call timer</li> <li>• Call waiting</li> <li>• Call chaperone</li> <li>• Caller ID</li> <li>• Corporate directory</li> <li>• Conference, including traditional Join feature</li> <li>• Cross Cluster Extension Mobility (EMCC)</li> <li>• Direct transfer</li> </ul>

Features	Specifications
	<ul style="list-style-type: none"> <li>• Extension mobility</li> <li>• Fast-dial service</li> <li>• Forced access codes and client matter codes</li> <li>• Group call pickup</li> <li>• Hold</li> <li>• Intercom</li> <li>• Immediate divert</li> <li>• Malicious-caller ID</li> <li>• Message-waiting indicator (MWI)</li> <li>• Meet-me conference</li> <li>• Mobility</li> <li>• Music on hold (MoH)</li> <li>• Mute</li> <li>• Network profiles (automatic)</li> <li>• On- and off-network distinctive ringing</li> <li>• Personal directory</li> <li>• PickUp</li> <li>• Predialing before sending</li> <li>• Privacy</li> <li>• Private Line Automated Ringdown (PLAR)</li> <li>• Redial</li> <li>• Ring tone per line appearance</li> <li>• Service Uniform Resource Locator (URL)</li> <li>• Shared line</li> <li>• Silent monitoring and recording</li> <li>• Speed dial</li> <li>• Time and date display</li> <li>• Transfer</li> <li>• Uniform Resource Identifier (URI) dialing</li> <li>• Visual voice mail</li> <li>• Voice mail</li> <li>• Whisper coaching</li> </ul>
<b>Electronic hookswitch</b>	<ul style="list-style-type: none"> <li>• You can control the hookswitch electronically with a third-party headset connected to the auxiliary port.</li> </ul>
<b>Quality-of-service (QoS) options</b>	<ul style="list-style-type: none"> <li>• The phone supports Cisco Discovery Protocol and 802.1Q/p standards, and can be configured with an 801.1Q VLAN header containing the VLAN ID overrides configured by the Admin VLAN ID.</li> </ul>
<b>Network features</b>	<ul style="list-style-type: none"> <li>• Session Initiation Protocol (SIP) for signaling</li> <li>• Session Description Protocol (SDP)</li> <li>• IPv4 and IPv6</li> <li>• User Datagram Protocol (UDP) (used only for Real-Time Transport Protocol [RTP] streams)</li> <li>• Dynamic Host Configuration Protocol (DHCP) client or static configuration</li> <li>• Gratuitous Address Resolution Protocol (GARP)</li> <li>• Domain Name System (DNS)</li> <li>• Trivial File Transfer Protocol (TFTP)</li> <li>• Secure Hypertext Transfer Protocol (HTTPS)</li> <li>• VLAN</li> <li>• Real-Time Transport Protocol (RTP)</li> <li>• Real-Time Control Protocol (RTCP)</li> <li>• Cisco Peer-to-Peer Distribution Protocol (PPDP)</li> <li>• Cisco Discovery Protocol</li> <li>• LLDP (including LLDP-MED)</li> <li>• Switch speed auto-negotiation</li> </ul>

Features	Specifications
<b>Security features</b>	<ul style="list-style-type: none"> <li>• Secure boot</li> <li>• Secure credential storage</li> <li>• Device authentication</li> <li>• Configuration file authentication and encryption</li> <li>• Image authentication</li> <li>• Random bit generation</li> <li>• Hardware cryptographic acceleration</li> <li>• Certificate Authority Proxy Function (CAPF)</li> <li>• Manufacturer-Installed Certificates (MIC)</li> <li>• Locally Significant Certificates (LSC)</li> <li>• Ethernet 802.1x supplicant options: Extensible Authentication Protocol-Flexible Authentication via Secure Tunneling (EAP-FAST) and Extensible Authentication Protocol-Transport Layer Security (EAP-TLS)</li> <li>• Signaling authentication and encryption using TLS</li> <li>• Media authentication and encryption using SRTP</li> <li>• HTTPS for client and server</li> <li>• Secure Shell (SSH) Protocol server</li> <li>• SSL-based VPN client</li> </ul>
<b>Physical dimensions (H x W x D)</b>	<ul style="list-style-type: none"> <li>• 9.02 x 10.13 x 1.57 in. (229.1 x 257.34 x 40 mm) (excluding foot stand)</li> </ul>
<b>Weight (with handset)</b>	<ul style="list-style-type: none"> <li>• 2.58 lb (1.17 kg)</li> </ul>
<b>Phone-casing composition</b>	<ul style="list-style-type: none"> <li>• Polycarbonate acrylonitrile butadiene styrene (ABS) textured plastic; Cosmetic class A</li> </ul>
<b>Operational temperature</b>	<ul style="list-style-type: none"> <li>• 32 to 104°F (0 to 40°C)</li> </ul>
<b>Nonoperational temperature shock</b>	<ul style="list-style-type: none"> <li>• 14 to 140°F (-10 to 60°C)</li> </ul>
<b>Humidity</b>	<ul style="list-style-type: none"> <li>• Operating 10 to 90%, noncondensing</li> <li>• Nonoperating 10 to 95%, noncondensing</li> </ul>
<b>Language support</b>	<ul style="list-style-type: none"> <li>• Arabic (Arabic Area)</li> <li>• Bulgarian (Bulgaria)</li> <li>• Catalan (Spain)</li> <li>• Chinese (China)</li> <li>• Chinese (Hong Kong)</li> <li>• Chinese (Taiwan)</li> <li>• Croatian (Croatia)</li> <li>• Czech (Czech Republic)</li> <li>• Danish (Denmark)</li> <li>• Dutch (Netherlands)</li> <li>• English (United Kingdom)</li> <li>• Estonian (Estonia)</li> <li>• French (France)</li> <li>• French (Canada)</li> <li>• Finnish (Finland)</li> <li>• German (Germany)</li> <li>• Greek (Greece)</li> <li>• Hebrew (Israel)</li> <li>• Hungarian (Hungary)</li> <li>• Italian (Italy)</li> <li>• Japanese (Japan)</li> <li>• Latvian (Latvia)</li> <li>• Lithuanian (Lithuania)</li> <li>• Korean (Korea Republic)</li> <li>• Norwegian (Norway)</li> <li>• Polish (Poland)</li> <li>• Portuguese (Portugal)</li> <li>• Portuguese (Brazil)</li> </ul>

Features	Specifications
	<ul style="list-style-type: none"> <li>• Romanian (Romania)</li> <li>• Russian (Russian Federation)</li> <li>• Spanish (Columbia)</li> <li>• Spanish (Spain)</li> <li>• Slovak (Slovakia)</li> <li>• Swedish (Sweden)</li> <li>• Serbian (Republic of Serbia)</li> <li>• Serbian (Republic of Montenegro)</li> <li>• Slovenian (Slovenia)</li> <li>• Thai (Thailand)</li> <li>• Turkish (Turkey)</li> </ul>

## Product Specifications

Table 3 gives ordering information for the phone and its accessories.

**Table 3.** Ordering Information

Product Number	Description
CP-8841-K9=	• Cisco IP Phone 8841, Charcoal
CP-8841-W-K9=	• Cisco IP Phone 8841, White
CP-DX-HS=	• Spare Handset for Cisco 7800, 8800, DX600 Series, Charcoal
CP-DX-CORD=	• Spare Handset Cord for Cisco 8800, DX600 Series, Charcoal
CP-DX-W-HS=	• Spare Handset for Cisco IP Phone 7800, 8800, DX600 Series, White
CP-DX-W-CORD=	• Spare Handset Cord for Cisco IP Phone 8800, DX600 Series, White
CP-8800-WMK=	• Spare Wallmount Kit for Cisco IP Phone 8800 Series
CP-8800-FS=	• Spare Foot stand for Cisco IP Phone 8800 Series
CP-8800-B-BEZEL=	• Spare Black Bezel for Cisco IP Phone 8800 Series
CP-8800-S-BEZEL=	• Spare Silver Bezel for Cisco IP Phone 8800 Series
CP-PWR-CUBE-4	• Cisco Power Cube 4
CP-PWR-CORD-AP=	• Power Cord Asia Pacific
CP-PWR-CORD-AR=	• Power Cord Argentina
CP-PWR-CORD-AU=	• Power Cord Australia
CP-PWR-CORD-BZ=	• Power cord for Brazil
CP-PWR-CORD-CE=	• Power Cord European
CP-PWR-CORD-CN=	• Power Cord China
CP-PWR-CORD-JP=	• Power Cord Japan
CP-PWR-CORD-NA=	• Power Cord North America
CP-PWR-CORD-SW=	• Power Cord Switzerland
CP-PWR-CORD-UK=	• Power Cord United Kingdom

## Warranty

The Cisco IP Phone 8841 phones are covered by a Cisco standard 1-year replacement warranty.

---

## Cisco Unified Communications Services

Cisco and our certified partners can help you set up a secure, dependable Cisco Unified Communications Solution, meeting aggressive deployment schedules and accelerating business advantage. Cisco's portfolio of services is based on proven methodologies for unifying voice, video, data, and mobile applications on fixed and mobile networks.

Our unique lifecycle approach to services defines what's needed at each phase of the solution lifecycle. Customized planning and design services help you create a solution that meets your business needs. Award-winning technical support helps you boost your operational efficiency. Remote management services simplify day-to-day operations. And optimization services let you modify and improve your network solution when business needs change.

## Cisco Capital

### Financing to Help You Achieve Your Objectives

Cisco Capital can help you acquire the technology you need to achieve your objectives and stay competitive. We can help you reduce CapEx. Accelerate your growth. Optimize your investment dollars and ROI. Cisco Capital financing gives you flexibility in acquiring hardware, software, services, and complementary third-party equipment. And there's just one predictable payment. Cisco Capital is available in more than 100 countries. [Learn more.](#)

## More Information

For additional details about the Cisco IP Phone 8800 Series, go to <http://www.cisco.com/go/ipphones/8800>.



---

Americas Headquarters  
Cisco Systems, Inc.  
San Jose, CA

Asia Pacific Headquarters  
Cisco Systems (USA) Pte. Ltd.  
Singapore

Europe Headquarters  
Cisco Systems International BV Amsterdam,  
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at [www.cisco.com/go/offices](http://www.cisco.com/go/offices).

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: [www.cisco.com/go/trademarks](http://www.cisco.com/go/trademarks). Third party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1110R)