

3m DVI-D Single Link Cable - M/M

StarTech ID: DVIDSMM3M



The DVIDSMM3M DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 3m DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-mylar foil with braided shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (19 pin) Male
Connector B	1 - DVI-D (19 pin) Male
Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	3 m [9.8 ft]
Product Length	3 m [9.8 ft]
Product Weight	0.3 kg [0.6 lb]
Package Quantity	1
Shipping (Package) Weight	302 g [10.7 oz]
Included in Package	1 - 3m DVI-D Single Link Cable - M/M

Certifications, Reports and Compatibility

