12U Rack Enclosure Server Cabinet - 21.5 in. Deep - Quiet - Wood Finish

Product ID: RKQMCAB12

The RKQMCAB12 12U Quiet Office Server Cabinet lets you store your server, network or AV equipment discreetly in the office, with a stylish, sound-insulated server cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Designed to keep your workspace or boardroom quiet, this server cabinet features top, bottom, and rear foam-insulation for maximum noise reduction. Minimizing operating equipment noise ensures less distraction for you and your colleagues, so you can deploy vital IT hardware even in sound-sensitive environments.

To ensure peak performance from your valuable equipment, the server cabinet offers maximum airflow and a cooler operating environment with an integrated 3-fan (3.5in) module (120 CFM). Plus, this quiet cabinet blends in with your office or boardroom furniture with a stylish wood laminate desktop and a shaded glass front window that keeps your equipment visible for monitoring, as well as front and rear key-locks to prevent unauthorized access.

Providing versatile installation options, this 4-post enclosed cabinet offers adjustable mounting depths from 17.60in (447mm) to 21.54in (547mm) to accommodate various sizes of equipment, and supports a weight capacity of up to 600lbs (272kg). The cabinet comes fully assembled, and also features durable casters, so that positioning your server equipment as needed isn't a hassle.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

RoHS & REACH
DOWNLOAD DECLARATION

CE

CE

TAA COMPLIANT

Applications

- Enclose loud equipment and reduce operating noise in sound sensitive areas such as office settings, boardrooms, and classrooms
- Mount server or networking equipment in a well-furnished boardroom
- Add an attractive server cabinet that won't be an eyesore in small / home-office areas with limited space

Features

- Sound attenuating and quiet 12U enclosed cabinet
- Integrated fan module with (3) 3.5in fans
- TAA compliant for GSA Schedule purchases
- Stylish wood finish desktop with tinted glass front window
- Supports a weight capacity of up to 600lbs (272kg)
- Adjustable mounting depth from 17.60in (447mm) to 21.54in (547mm)
- Front and rear key-lock
- Ventilation and rear cable ports with foam grommet kit
- Comes fully assembled
- Casters included

	Warranty	2 Years
Hardware	Fan Options	Three Fans Included: 92 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Wood with Glass Window
	Front Door Features	Secure Key Lock
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	G-Shape
	Rack Type	4-Post
	Rear Door Construction	Steel
	Side Panel Construction	Steel
	Special Features	Adjustable Mounting Rails
		Casters (Included)
		Ships Fully Assembled
	U Height	12U
	Wallmountable	No
Performance	Airflow Rate	40 CFM
	Audible Noise	36 dBA @ 1 Meter
	Weight Capacity (Stationary)	600 lb [271.5 kg]
Physical Characteristics	Color	Dark Gray with Wood Finish Top
	Rear Door Features	Secure Key Lock with Removable Back Door
Product Measurements	Internal Depth	28.4 in [72.1 cm]
	Internal Width	18.6 in [47.2 cm]
	Maximum Mounting Depth	21.6 in [54.8 cm]
	Minimum Mounting Depth	14.1 in [35.9 cm]
	Product Height	25.3 in [64.2 cm]
	Product Height with Casters	28.1 in [71.3 cm]
	Product Length	30.8 in [78.3 cm]
	Product Width	27.8 in [70.5 cm]
	Weight of Product	182.4 lb [82.6 kg]

Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	34.2 in [86.8 cm]
	Package Length	31.3 in [79.5 cm]
	Package Width	29.8 in [75.7 cm]
	Shipping (Package) Weight	192.5 lb [87.1 kg]
What's in the Box	Included in Package	1 - 12U Rack
		4 - Keys (2 Front, 2 Back)
		30 - M6 Screws
		30 - M6 Cage Nuts

Product appearance and specifications are subject to change without notice.