ECOR960 16F2

16 Channel W D1 / 960H DVR





















16 CH WD1 recording and playback

- WD1 capability provides higher resolution (960x576 / 960x480) compared to traditional D1 cameras
- H.264 compression format for enhanced recording capacity and improved network image transmission speed
- Free EverFocus DDNS Service static IP address is not required for reliable remote access
- Multiple Main Monitors: Separately configured HDMI or VGA (1080p) Main monitor outputs
- Supports live monitoring and playback of video from mobile devices via MobileFocus/ MobileFocusPlus Apps.
- Remote configuration support from built-in web interface
- Dual USB 2.0 ports for video archive and mouse control
- Integration with PowerVideo Plus
- Multi-language support

Specifications

Item	Model Name	ECOR960 16F2
System	os	Embedded Linux
Video	Analog Video Input	16 CH
	Compression	H.264
	Video Interface	16 BNC
Audio	Input / Output	16 / 1 (Line level)
Display	Main Monitor Outputs	VGA / HDMI
	Call Monitor Outputs	BNC
Recording	Rate/ Resolution	480 NTSC / 400 PAL (WD1) 480 NTSC / 400 PAL (Half WD1) 480 NTSC / 400 PAL (4CIF / D1) 480 NTSC / 400 PAL (2CIF) 480 NTSC / 400 PAL (CIF)
	Recording Mode	Continue, Schedule and Event
Playback	Rate/ Resolution	240 NTSC / 200 PAL (WD1) 240 NTSC / 200 PAL (Half WD1) 240 NTSC / 200 PAL (4CIF / D1) 240 NTSC / 200 PAL (2CIF) 240 NTSC / 200 PAL (CIF)
	Search Mode	Time search, Event search, Smart search, Snapshot search
Video Detectior & Alarm	Alarm Input / Output	4 / 1
Network	Network / Protocol	Gigabit Ethernet; TCP-IP / DHCP/ PPP0E / Everfocus DDNS / RTSP / RTP / HTTP / SMTP / POP3 / SSL
	Max. User Access	3 Levels of User Access Defined
	Smart Phone	MobileFocus Apps for iOS and Android devices MobileFocus HD for iPad
	Internal HDD	2 x SATA HDD (Max 8TB)
External Interface	USB Interface	2 x USB 2.0 ports
	RS-485	x1
General	PTZ Protocols Supported	EverFocus, Pelco D, Pelco P, Samsung, Transparent
	Power Source	12VDC / 5A
	Working Temperature	0°C~40°C / 32°F~104°F (20~80% humidity)
	Dimension (W × D × H)	320 x 255 x 50mm "
	Weight	6.0kgs / 13.23lbs (without HDDs)
	Certificates	CE, FCC, UL



All product specifications are subject to change without notice

Models vary in different countries. Please visit Ever Focus regional websites for detailed ordering information

Lens models and availbility vary in different regions