



CONFERENCE MATE™

Portable NFC Enabled *Bluetooth®* Speakerphone

Professional sounding phone calls
when paired with your cell phone or tablet
 And you'll love how it plays music
when paired with your A2DP devices



Your choice of Marble White (MCP-3020) or Obsidian Black (MCP-3022)



Bottom View
showing downward facing speaker

- Pro-quality conference room speaker in a portable 4" x 4" package! Pair this portable speaker with your smart phone (iPhone or Android), tablet (iPad or other), PC/Mac, or other A2DP *Bluetooth®* device. Non-*Bluetooth®* devices can also connect, via the 3.5mm jack (using your own audio cable).
- NFC (Near Field Communications) chip means you can touch your NFC capable device to Conference Mate™ and it will pair automatically, instead of the standard *Bluetooth®* method of pairing.
- Full duplex, so you can speak and hear the other party at the same time.
- DSP for noise cancellation and echo suppression.
- Advanced Audio Distribution Profile (A2DP) for high fidelity *Bluetooth®* wireless audio.
- Dual high quality omni-directional mic array so the unit will capture everything you say, and clearly. Enough volume so you'll be heard well at the other end.
- Stream full, rich sounding music from your A2DP *Bluetooth®* device when you're not on a call.
- Simple, capacitive touch controls.
- 7+ hours of talk time; USB recharges high power density Lithium Polymer battery.
- Downward facing speaker with passive bass radiator means a realistic, deep bass and rich sounding audio.




Download the **FREE Bongiovi DPS App** to improve the quality of your compressed audio playback, for an even fuller and deeper sound. Available now for iOS and coming soon for Android.



CONFERENCE MATE™

Portable NFC Enabled Bluetooth® Speakerphone



Sleek design, small package, easy to use, high quality audio in a wireless portable speaker: who says you can't have it all? Take or make phone calls with Conference Mate™, and when you're done conferencing, listen to music from your Bluetooth® enabled device.



Download the **FREE Bongiovi DPS App** and improve the quality of your compressed audio playback even more.

PRODUCT SPECIFICATIONS

Features	Controls and Interfaces
A2DP Bluetooth® speaker for high fidelity wireless audio	ON/OFF
DSP (Digital Signal Processing) based noise cancellation	Call Answer
Make and receive calls using the mobile phone hands free function	Volume: Up, Down
Downward aimed speaker and passive radiator produce rich, deep, bass	Mic Mute
Compact and lightweight	Play/Pause
Uses Lithium Polymer battery or USB AC adapter	NFC (Near Field Communications) for pairing with NFC equipped devices (Android phones and tablets)
Quick and easy set up	Blue LED for Bluetooth® status
NFC to automatically pair your Android phone or tablet without having to use the standard Bluetooth® pairing method	Red LED for Low Battery and Charging
Electrical, Audio Specifications	Package Includes
Bluetooth® range: 33'(10 meters)	P/N: MCP-3020
Playback time Talk Time/Music Playback: up to 7 hours typical	Conference Mate™ Portable Wireless Speaker
Audio input jack: 3.5 mm	USB cable
Loudspeaker output power: 2 x 2 W	AC adapter for wall power
Audio Bandwidth: Voice, 8 Khz sampling; Music, 44KHz sampling	Lithium Polymer rechargeable battery (internal)
700 mVpp (at 10 kΩ)	Users Guide / Quick Start / Registration Card
Certifications: FCC, CE, C-Tick, RoHS	3.5mm jack to connect to non-Bluetooth devices
Mechanical Specifications	
Dimensions	4"(100mm) L x 2"(52mm) H x 4"(100mm) W
Weight	8.4 oz. (238 gm)
	Package dim.: 5.5"(140 mm) x 3.1"(79mm) x 5.5"(140 mm)
	1 year limited warranty

Download the **FREE Bongiovi DPS App** to improve your compressed audio playback

© 2013 Spracht. All Rights Reserved. Spracht, the Spracht logo, and Conference Mate are trademarks and registered trademarks of Spracht. All other trademarks are the property of their respective owners.

All information is believed to be reliable, however specifications are subject to change without notice.