



LaserJet Enterprise MFP M725 series

M725dn • M725f • M725z • M725z+

Enable large-volume printing on a wide range of paper sizes—up to Ledger/A3—with a 4,600-sheet maximum input capacity.² Preview and edit scanning jobs. Centrally manage printing policies. Safeguard sensitive business information.

Print speed:¹² Up to 40 ppm black (letter)

Print resolution: Up to 1200 x 1200 dpi black (best)

Scan resolution: Up to 600 x 600 dpi hardware, Up to 600 dpi Optical

Standard connectivity: 2 Hi-Speed USB 2.0 Host, 1 Hi-Speed USB 2.0 Device, 1 Gigabit Ethernet 10/100/1000T network, 1 Foreign Interface, 1 Hardware Integration Pocket, 2 Internal USB Host

Duplex print options: Automatic (standard)

Mobile printing capability: HP ePrint, Apple AirPrint™



(HP LaserJet Enterprise MFP M725dn shown)



HP LaserJet Enterprise
MFP M725f



HP LaserJet Enterprise
MFP M725z



HP LaserJet Enterprise
MFP M725z+

Expand your options with sharp Ledger/A3 printing

- Empower your teams to do more—print, scan, copy, and fax¹ on paper sizes up to Ledger/A3—from a desktop-sized MFP.
- Stay focused on work—paper capacity up to 4,600 sheets and high-capacity cartridges limit interruptions.^{2,4}
- Get impressive document quality with near edge-to-edge printing and a convenient, built-in stapler.⁵
- Print what you need, even on the go—from your smartphone or tablet—using HP ePrint³ or Apple AirPrint™.⁶

Quicken your business pace

- Streamline tasks—print, scan, copy, and fax¹ projects directly at the MFP's large color touchscreen.
- Save time by launching one-touch workflows with HP Quick Sets.
- Get just the results you need—using touchscreen controls to preview, edit, and reorder scans at the device.
- Easily send scanned files to a fax, folder, email, or USB. Print right from a memory device via the USB port.

Manage and protect your fleet for the long run

- Simplify fleet management using world-class tools such as HP Web Jetadmin,⁷ and reliably safeguard devices.
- Safeguard data—at rest or in transit—with an encrypted hard drive, user authentication, and security features.
- Add security tools—such as card and badge readers—via the hardware integration pocket.⁸
- Extend the capabilities of workteam print environments, using a rich array of easy-to-integrate solutions.

Help save energy and reduce environmental impact

- Reduce energy use with HP Auto-On/Auto-Off Technology,⁹ and conserve power with Instant-on Technology.¹⁰
- Conserve resources and save paper—use automatic two-sided printing.
- Easily recycle Original HP LaserJet toner cartridges through HP Planet Partners.¹¹

HP EcoSolutions

- Reduce energy use with Instant-on Technology.¹
- Reduce paper use by up to 50%, using automatic two-sided printing.
- Reduce waste—scan, store, and distribute documents digitally.

Join HP in more sustainable printing
hp.com/ecosolutions




¹ Compared with products that use traditional fusing.

¹ Fax capabilities are available with an optional fax card on the HP LaserJet Enterprise MFP M725dn. ² Maximum paper capacity of 4,600 sheets requires the purchase of optional paper tray accessories. ³ Requires an Internet connection to HP web-enabled printer and HP ePrint accounts registration for a list of eligible printers, supported documents and image types and other HP ePrint details, see hpconnected.com. Mobile devices require Internet connection and email capability. May require wireless access point. Separately purchased data plans or usage fees may apply. Print times and connection speeds may vary. Some HP LaserJet printers may require firmware upgrades. ⁴ High-capacity cartridges are optional for the HP LaserJet Enterprise 700 MFP Series M725. ⁵ In-line stapler is not available on the HP LaserJet Enterprise MFP M725dn or M725f. ⁶ Supports the following devices running iOS 4.2 or later: iPad®, iPad® 2, iPhone® (3GS or later), iPod touch® (3rd generation or later). Works with HP's AirPrint-enabled printers and requires the printer be connected to the same network as your iOS device. Wireless performance is dependent upon physical environment and distance from the access point. AirPrint, the AirPrint Logo, iPad, iPhone, and iPod touch are trademarks of Apple® Inc., registered in the U.S. and other countries. ⁷ HP Web Jetadmin is free and can be downloaded at hp.com/go/webjetadmin. ⁸ Solutions deployed through the hardware integration pocket may require additional purchase. ⁹ HP Auto-On/Auto-Off Technology capabilities subject to printer and settings; may require a firmware upgrade. ¹⁰ Compared with products that use traditional fusing. ¹¹ Program availability varies. Original HP cartridge return and recycling is currently available in more than 50 countries, territories and regions in Asia, Europe, and North and South America through the HP Planet Partners program. For more information, visit: hp.com/recycle. ¹² Measured using ISO/IEC 24734, excludes first set of test documents. For more information see hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity.

HP LaserJet Enterprise MFP M725 series

- 1 100-sheet automatic document feeder
- 2 Intuitive 8-inch pivoting color touchscreen control panel with FutureSmart firmware and scan preview
- 3 Hardware integration pocket (HIP) for solution integration
- 4 Easy-access USB port to save and print files directly
- 5 In-line stapler with 500-sheet output bin
- 6 Built-in automatic two-sided printing
- 7 Two 250-sheet input trays, one supporting up to legal and one supporting up to ledger/A3
- 8 3,500-sheet high-capacity feeder and stand for a 4,100-sheet total input capacity
- 9 250-sheet output bin
- 10 Side door allows convenient access to the all-in-one HP print cartridge
- 11 100-sheet multipurpose tray 1 supports a wide variety of paper sizes and types
- 12 800 MHz processor, 1 GB standard memory
- 13 Two internal USB Host ports (for connecting third-party devices)
- 14 HP High-Performance Secure Hard Disk
- 15 Fax port
- 16 Foreign Interface port
- 17 HP Jetdirect Gigabit Ethernet print server
- 18 Hi-Speed USB 2.0 device port
- 19 Hi-Speed USB 2.0 Host port

HP LaserJet Enterprise MFP M725z+ printer shown



Front view

Close-up of I/O port

Series at a glance



Part number	M725dn MFP	M725f MFP	M725z MFP	M725z+ MFP
Gigabit Ethernet networking	✓	✓	✓	✓
Automatic two-sided printing	✓	✓	✓	✓
100-sheet multipurpose tray 1	✓	✓	✓	✓
2 x 250-sheet trays 2 and 3	✓	✓	✓	✓
500-sheet tray¹	Optional	✓	Not available	Optional
500-sheet feeder with cabinet and stand¹	Optional	✓	Not available	Not available
3 x 500-sheet feeder and stand¹	Optional	Not available	✓	Not available
3,500-sheet high-capacity feeder and stand¹	Optional	Not available	Not available	✓
500-sheet in-line stapler	Not available	Not available	✓	✓
HP High-Performance Secure Hard Disk	✓	✓	✓	✓
Fax	Optional	✓	✓	✓
ENERGY STAR® qualified	✓	✓	✓	✓

¹ Up to 6 input trays are supported on the M725dn and M725z+ models, including the multipurpose tray and the standard 2 x 250-sheet trays. (The 3 x 500-sheet trays and stand counts for 3 trays; the 3,500-sheet HCI feeder and stand counts for 2 trays.) The 500-sheet tray is not stackable.

Top features

Get precise document finishing, one-touch workflows, and many scan-to options on a versatile Ledger/A3 MFP.

Do more—with document sizes up to Ledger/A3, and high-capacity cartridges³ and paper trays. Print nearly to the page's edge, and even staple (Only on Z and Z+ models). Copy, scan, and fax¹—and print from smartphones and tablets from virtually anywhere with HP ePrint.²

Set a swift pace—use this powerful MFP to keep your work moving. Save time and make your job easier, using HP Quick Sets. Preview and control jobs on the 8-inch color touchscreen. Scan to multiple locations, and print via an easy-access USB port.

Monitor your devices with industry-leading tools, including HP Web Jetadmin.⁴ Help protect data both in transit and at rest. Enhance security with PIN printing. Add safeguards via the hardware integration pocket. Integrate tomorrow's solutions with ease.

Help conserve resources and meet corporate environmental goals. HP Auto-On/Auto-Off Technology helps reduce energy use.⁵ Easily manage printing policies with HP EcoSMART Fleet.⁶ Save paper, using automatic two-sided printing.

Get the most out of your printer with HP accessories, supplies, and services.

HP services

Downtime can have serious consequences, so HP provides support beyond the standard warranty. You benefit from reduced risk, maximized uptime, predictable service delivery and no unbudgeted repair costs. Choose from:

Optimized Care (optimum performance and stability):

4 hour Onsite Support, Maintenance Kit Replacement Service, Installation with Network Configuration Service

Standard Care (high level of uptime):

Next Business Day Onsite Support, Maintenance Kit Replacement Service, Installation with Network Configuration Service

Basic Care (minimum recommended support):

Next Business Day Onsite Support

4 hr Onsite Support: Onsite support within four hours after a service call received within the coverage window

Next Business Day Onsite Support: Onsite service the next business day after the service call is received

Maintenance Kit Replacement Service: Onsite replacement of your printer's maintenance kit including parts, materials, and labor

Installation with Network Configuration Service: Assembly, network configuration, and basic administrator familiarization

For more information about HP Care Pack, HP Contractual, or HP Managed Print Services, visit hp.com/go/printservices

Printers

HP LaserJet Enterprise 700 MFP M725dn	CF066A
HP LaserJet Enterprise 700 MFP M725f	CF067A
HP LaserJet Enterprise 700 MFP M725z	CF068A
HP LaserJet Enterprise 700 MFP M725z+	CF069A

Toner Cartridges

HP 14A Black LaserJet Toner Cartridge (10,000 pages)	CF214A
HP 14X Black LaserJet Toner Cartridge (17,500 pages)	CF214X

Accessories

500-sheet feeder and tray assembly	CF239A
1x500-sheet feeder, cabinet, and stand	CF243A
3x500-sheet feeder and stand	CF242A
3,500-sheet HCl and stand	CF245A
110v Maintenance/Fuser Kit	CF249A
220v Maintenance/Fuser Kit	CF254A
HP 200-pin DDR2 512MBx64 DIMM	CF306A
HP staple cartridge refill	C8091A
HP LaserJet MFP Analog Fax Accessory 500	CC487A
ADF Roller kit	L2718A

HP Care Pack

HP 3 year Next business day + Defective Media retention LaserJet M725 Multifunction printer Support	U7A14E
HP 4 year Next business day + Defective Media retention LaserJet M725 Multifunction printer Support	U7A15E
HP 5 year Next business day + Defective Media retention LaserJet M725 Multifunction printer Support	U7A16E
HP 3 year 4 hour 9x5 LaserJet M725 Multifunction printer Hardware Support	U7A08E
HP 4 year 4 hour 9x5 LaserJet M725 Multifunction printer Hardware Support	U7A10E
HP 5 year 4 hour 9x5 LaserJet M725 Multifunction printer Hardware Support	U7A12E
HP 1 year Post Warranty Next business day + Defective Media retention Laserjet M725 Multifunction printer Support	U7Y76PE
HP 1 year Post Warranty 4 hour 9x5 Laserjet M725 Multifunction printer Support	U7Y74PE

To know what HP Care Pack services exist for your product, please visit Care Pack Central at hp.com/go/cpc

Paper

hp.com/go/paper

Software

HP Web Jetadmin: hp.com/go/wja

HP Universal Print Driver: hp.com/go/upd

¹ Fax capabilities are available with an optional fax card on the HP LaserJet Enterprise MFP M725dn. ² Requires an Internet connection to HP web-enabled printer and HP ePrint account registration (for a list of eligible printers, supported documents and image types and other HP ePrint details, see hpconnected.com). Mobile devices require Internet connection and email capability. May require wireless access point. Separately purchased data plans or usage fees may apply. Print times and connection speeds may vary. Some HP LaserJet printers may require firmware upgrades. ³ High-capacity cartridges are optional for the HP LaserJet Enterprise 700 MFP Series M725. ⁴ HP Web Jetadmin is free and can be downloaded at hp.com/go/webjetadmin. ⁵ HP Auto-On/Auto-Off Technology capabilities subject to printer and settings; may require a firmware upgrade. ⁶ HP EcoSMART Fleet must be purchased separately.

HP LaserJet Enterprise MFP M725 series

	HP LaserJet Enterprise 700 MFP M725dn (CF066A)	HP LaserJet Enterprise 700 MFP M725f (CF067A)	HP LaserJet Enterprise 700 MFP M725z (CF068A)	HP LaserJet Enterprise 700 MFP M725z+ (CF069A)
All functions	Print, copy, scan			Print, copy, scan, fax
Print				
Duplex print options		Automatic (standard)		
Print speed ¹		Up to 40 ppm (Black, letter); First page out: As fast as 10 sec		
Print technology		Laser		
Print resolution	Black (best): Up to 1200 x 1200 dpi; Black (normal): HP FastRes 1200 (1200 dpi quality), 600 x 600 dpi with HP Resolution Enhancement technology			
Printer Smart Software features	HP ePrint, Apple AirPrint, Open Extensibility Platform, FutureSmart Firmware, HP Auto-On/Auto-Off technology, Easy Access USB, Image Preview			
Mobile printing capability		HP ePrint; Apple AirPrint		
Standard print languages		HP PCL 6; HP PCL 5e; HP postscript level 3 emulation; PDF 1.4		
Scan				
Scan type/technology		Flatbed, ADF; Technology: Charge Coupled Device (CCD)		
Scan speed ²		Letter: Up to 49 ppm (black and white), up to 30 ppm (color)		
Scan resolution		Hardware: Up to 600 x 600 dpi; Optical: Up to 600 dpi		
Scan file format		PDF, JPEG, TIFF, MTIFF, XPS, PDF/A		
Scan input modes		Copy, scan to e-mail, scan to network folder, scan to USB, save to device memory, fax, Open Extensibility Platform (OXP) applications		
Scan size maximum		ADF, Flatbed: 11 x 17 in (297 x 420 mm)		
Scanner advanced features		Optimize text/picture; Image adjustments; Job build; Output quality setting; Selectable scan resolution 75 to 600 dpi; Auto detect color; Edge erase; Auto tone; Auto job notification; Blank page suppression; HP Quick Sets		
Bit depth/Grayscale levels		24 bit/256		
Copy				
Copy speed ⁴		Up to 40 ppm (Black, letter)		
Copy resolution		Black (text and graphics): 600 x 600 dpi		
Max number of copies		Up to 9,999 copies		
Copier reduce/enlarge		25 to 400%		
Copier settings		Sides; Collate; Paper Selection; Reduce/Enlarge; Image Adjustment; Content Orientation; Pages per sheet; Booklet format; Edge to Edge; Optimize Text/Picture; Original Size; Job Build		
Digital Sending Standard features		Scan to e-mail; Save-to-Network Folder; Save-to-USB drive; Send to FTP; Send to LAN Fax; Send to Internet Fax; Local Address Book; SMTP over SSL		
Fax				
Transmission speed ⁵	Not Applicable		Up to 33.6 kbps; 3 sec per page	
Fax resolution	Not Applicable	Black (best): Up to 300 x 300 dpi (400 x 400 dpi for received faxes only); Black (standard): 204 x 98 dpi; Black and White (fine): 204 x 196 dpi, 256 levels of gray; Black Photo Grayscale: 300 x 300 dpi (400 x 400 dpi for received faxes only)		
Fax smart software features	Not Applicable	Stored faxes; fax archiving; fax forwarding; scale-to-fit; fax address book; LAN/Internet fax; fax number confirmation; Holiday fax schedule		
Fax memory	Not Applicable		Up to 100 pages	
Fax features	Not Applicable	Auto Fax Reduction Supported: Yes; Auto-Redialing: Yes; Fax Delayed Sending: No; Distinctive Ring Detection Supported: No; Fax Forwarding Supported: Yes; Fax Phone TAM Interface Supported: No; Fax Polling Supported: Yes (poll to receive only); Junk Barrier Supported: Yes; PC Interface Supported: Yes; Telephone Handset Supported: No; Fax Telephone Mode Supported: No		
Connectivity				
Standard connectivity		2 Hi-Speed USB 2.0 Host; 1 Hi-Speed USB 2.0 Device; 1 Gigabit Ethernet 10/100/1000T network; 1 Foreign Interface; 1 Hardware Integration Pocket; 2 Internal USB Host		
Network capabilities		Via HP Jetdirect Ethernet embedded print server (standard) supports: 10Base-T, 100Base-Tx, 1000Base-T; 802.3az (EEE) support on Fast Ethernet and Gig Links; IPsec (standard); 802.11b/g/n wireless networking (optional)		
Wireless capability		Optional, enabled with purchase of a hardware accessory		
Modem	Not Applicable		1 GB	33.6 kbps
Memory			800 MHz	
Processor speed			Up to 200,000 pages	
Duty cycle (monthly, A4)⁶			Up to 5000 to 20,000 pages	
Recom monthly page volume				
Paper handling				
Media type		Paper (color, letterhead, light, plain, preprinted, prepunched, recycled, rough, tough paper), bond, cardstock, envelope, labels, transparency, vellum		
Media weight		Tray 1: 16 to 53 lb (60 to 199 g/m ²); Trays 2-6: 16 to 32 lb (60 to 120 g/m ²)		
Custom media sizes		Tray 1: 3 x 5 to 12.3 x 18.5 in; Tray 2: 5.8 x 8.3 to 11.7 x 14.3 in; Trays 3-6: 5.8 x 8.3 to 11.7 x 17 in		
ADF capacity		Standard, 100 sheets		
Dimensions (W x D x H)	24.2 x 25.6 x 24 in (614 x 649 x 609 mm) Max: 34.1 x 38.9 x 24 in (865 x 989 x 609 mm)	29.3 x 26.8 x 45.7 in (745 x 681 x 1160 mm) Max: 36.1 x 40.6 x 45.7 in (917 x 1032 x 1160 mm)	29.3 x 26.8 x 46.9 in (745 x 681 x 1192 mm); Max: 36.1 x 40.6 x 46.9 in (917 x 1032 x 1192 mm)	
Weight	119.3 lb (54.11 kg)	192.3 lb (87.1 kg)	206.3 lb (92.35 kg)	225.8 lb (102.42 kg)
What's in the box⁸		M725dn: HP LaserJet Enterprise MFP M725; HP Black LaserJet Toner Cartridge (10,000 pages); Hardware Installation Guide, Support flyer, Warranty guide; Printer documentation and software on CD-ROM; Power cord. M725f, M725z & M725z+: Same as above plus Telecom cable		
Warranty features			One-year on-site warranty	
Compatible operating systems		Windows 10, Windows 8, Windows 7, Windows Vista, Windows XP (SP2+), Windows Server 2003 (SP1+), Windows Server 2008 (32 and 64-bit), Windows Server 2008 R2 (64-bit), Windows Server 2012 (64-bit); Mac OS X 10.6, OS X Lion, OS X Mountain Lion; For the latest operating system support see: Citrix and Windows Terminal Services (http://www.hp.com/go/upd); Novell (http://www.novell.com/iproprint); Linux (http://www.hplip.net); UNIX (http://www.hp.com/go/unix); http://www.hp.com/go/jetdirectunix_software ; SAP device types (http://www.hp.com/go/sap/drivers , http://www.hp.com/go/sap/print); HP ePrint Mobile Driver (http://www.hp.com/go/eprintmobiledriver)		
Minimum system requirements	PC: Windows 10, Windows 8, Windows 7, Windows Vista, Windows XP (SP2+), Windows Server 2003 (SP1+), Windows Server 2008, Windows Server 2008 R2, Windows Server 2012 (64-bit); available hard disk space; operating system compatible hardware system requirements, see http://www.microsoft.com Mac: Mac OS X 10.6, OS X Lion, OS X Mountain Lion; 1 GB available hard disk space; operating system compatible hardware system requirements, CD-ROM/DVD-ROM or Internet, see apple.com			
Fonts and Typefaces		105 internal TrueType fonts scalable in HP PCL, 92 internal scalable fonts in HP Postscript level 3 emulation (Euro symbol built-in); 1 internal Unicode Fonts (Andale Mono WorldType); 2 Internal		
Control panel		Windows Vista 8 Fonts (Calibri, Cambria); additional font solutions available via third-party flash memory cards; HP LaserJet Fonts and IPDS Emulation available at hp.com/go/laserjetfonts		
Software included		8.0-in (20.3 cm) color LCD with touchscreen; rotating (adjustable angle) display; illuminated Home button (for quick return to the Home menu); Easy Access USB; Hardware Integration Pocket		

Environmental ranges

Operating humidity range:	20 to 80% RH	Acoustic pressure emissions bystander (active, printing):	54 dB(A)
Non-operating humidity range:	10 to 90% RH	Acoustic pressure emissions bystander (ready):	36 dB(A)
Recommended operating humidity range:	30 to 70% RH		
Operating temperature range:	50 to 91° F (10 to 32.5° C)	Power⁹:	Built-in power supply
Recommended operating temperature range:	50 to 91° F (10 to 32.5° C)	Power supply type:	110-volt input voltage: (Option #BGJ, #201) 110 to 127
Storage temperature range:	32 to 140° F (0 to 60° C)	Power supply required:	VAC (+/- 10%), 50/60 Hz (+/- 2 Hz); 220-volt input voltage: (Option #AAZ) 220 to 240 VAC (+/- 10%), 50/60 Hz (+/- 2 Hz)
Acoustic¹⁰			(Not dual voltage, power supply varies by part number with # Option code identifier)
Acoustic power emissions:	6.8 B(A)	Power consumption:	890 watts (Active print/copy), 39 watts (Ready),
Acoustic power emissions (active copy):	7.1 B(A)		6.5 watts (Sleep), 0.3 watts (Off)
Acoustic power emissions (ready):	5.0 B(A)		3.31 kWh/Week (110/220 V), 2.8 kWh/Week (Blue Angel)
Acoustic pressure emissions bystander (active copy):	56 dB(A)	Typical Electricity Consumption (TEC):	

¹ Measured using ISO/IEC 24734, excludes first set of test documents. For more information see hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ² Exact speed varies depending on the system configuration, software application, driver and document complexity. ³ Actual speeds may vary depending on scan resolution, network conditions, computer performance and application software. ⁴ First Copy Out and Copy Speed measured using ISO/IEC 29183, excludes first set of test documents. For more information see hp.com/go/printerclaims. Exact speed varies depending on the system configuration, software application, driver, and document complexity. ⁵ Based on standard ITU-T test image #1 at standard resolution. More complicated pages or higher resolution will take longer and use more memory. ⁶ Duty cycle is defined as the maximum number of pages per month of imaged output. This value provides a comparison of product robustness in relation to other HP LaserJet or HP Color LaserJet devices, and enables appropriate deployment of printers and MFPs to satisfy the demands of connected individuals or groups. ⁸ Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages; this will damage the printer and void the product warranty. Values subject to change, see hp.com/support for current information. ⁹ Acoustic values are subject to change. For current information see hp.com/support. Configuration tested: base model, simplex printing, A4 paper at an average of 40 ppm.



© Copyright 2013 - 2015 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein. ENERGY STAR and the ENERGY STAR logo are registered U.S. marks. Windows is a registered trademark of Microsoft Corporation. AirPrint, iPad, iPhone, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries.

