

7m DVI-D Dual Link Cable – M/M

StarTech ID: DVIDDMM7M



The DVIDDMM7M 7m DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and offers 7 meters in cable length, making it perfect for longer connections between your desktop or laptop computer and a DVI-D monitor or projector.

The 7m DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-mylar foil with braided shielding
- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Technical Specifications

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	2
Industry Standards	DVI DDWG Standard
Connector A	1 - DVI-D (25 pin) Male
Connector B	1 - DVI-D (25 pin) Male
Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	7 m [23 ft]
Product Length	7 m [23 ft]
Product Weight	767 g [27.1 oz]
Package Quantity	1
Shipping (Package) Weight	777 g [27.4 oz]
Included in Package	1 - 7m DVI-D Dual Link Cable - M/M

Certifications, Reports and Compatibility

