


4K HDMI® 4-Port Video Splitter – 1x4 HDMI Splitter w/ Solid Aluminum Housing – 4K 30Hz

StarTech ID: ST124HD4K



The ST124HD4K 4-port 4K HDMI splitter lets you share an HDMI display or projector with four HDMI-enabled audio / video source devices, such as computers, Blu-ray players and cable TV set-top boxes.

With support for Ultra HD (4K) the HDMI splitter ensures astonishing picture quality, four times the resolution of high-definition 1080p at 30 Hz. The 4K splitter is also backward compatible with previous HDMI revisions, supporting 1080p / 720p HDMI video resolution devices. Even if you don't require 4K video today, the ST124HD4K ensures you'll be ready to take advantage of tomorrow's display technology.

Constructed of solid aluminum, the HDMI splitter casing is heavy enough to prevent the unit from shifting or sliding around when you move the attached HDMI cables. Plus, the small footprint allows for seamless integration into any digital signage application.

The ST124HD4K is backed by a StarTech.com 2-year warranty, and free lifetime technical support.

Applications

- Display a 4K HDMI signal on four different HDMI displays
- Use to showcase 4K displays, by outputting the same video source on multiple displays
- Display corporate information or advertising on multiple displays at a shopping center
- Use to display a stock ticker or promotional information at financial institutions
- Display the same information on multiple displays in waiting rooms in healthcare facilities

Features

- Supports Ultra HD video resolutions up to 4K @ 30Hz
- Support for 7.1 surround sound audio
- 4x HDMI outputs
- Solid aluminum housing
- Small footprint

Technical Specifications

Warranty	2 Years
Ports	4
Audio	Yes
Industry Standards	HDMI 1.4
Output Signal	HDMI
Connector A	1 - HDMI (19 pin) Female
Connector B	4 - HDMI (19 pin) Female
Maximum Digital Resolutions	4K @ 30 Hz
Supported Resolutions	3840x2160 (4K) 2560x1600 1920x1200 1920x1080 (1080p) 1280x720 (720p)
Wide Screen Supported	Yes
Audio Specifications	7.1 Surround sound
Color	Black
Product Length	5.5 in [139 mm]
Product Width	3.3 in [85 mm]
Product Height	0.6 in [14 mm]
Product Weight	10.1 oz [285 g]
LED Indicators	4 - Active port LED
LED Indicators	1 - Power LED
Input Voltage	100 ~ 240 AC
Input Current	0.35 A
Output Voltage	5 DC
Output Current	1 A
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-10°C to 80°C (14°F to 176°F)
Humidity	5% to 90%
Shipping (Package) Weight	0.9 lb [0.4 kg]
Included in Package	1 - 4-Port HDMI A/V Splitter
Included in Package	1 - Power Adapter (NA/EU/UK/AUS)
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

