

Single-Monitor Arm - One-Touch Height Adjustment

StarTech ID: ARMPIVOTE



The ARMPIVOTE Articulating Monitor Arm lets you mount a display to your desk or table, with extension, tilt, pan, swivel, pivot and gas-spring height adjustments.



The desk-mount monitor arm features a gas-spring cylinder to raise or lower your display with minimal effort, plus it offers a wide range of motion on several axes. For viewing longer pages or blocks of code without scrolling, the LCD arm also supports landscape to portrait display rotation.

Mounting your displays on a monitor arm above the desk surface enables you to adjust your display height, position and viewing angles easily for an ergonomic work environment, with the added benefit of reclaiming

valuable workspace on your desk.

Supporting 12 - 24" displays up to a maximum weight capacity of 11lbs (5kg), the monitor mounting arm holds your display with ease, and integrates a cable management channel to keep things neat. For added installation flexibility, the included mounting hardware can either clamp to the side of your desk / table or mount through a grommet hole, for a versatile monitor mounting solution.

Backed by a StarTech.com 2-year warranty and free, lifetime technical support.

Applications

- Mount a display to the side of your desk or table with a wide range of adjustment capability
- Grommet mount your display through a desk or above a server cabinet and position as needed
- Lift your display higher above your desk surface for ideal viewing angles
- Rotate displays to portrait orientation for web design and coding

Features

- Articulating monitor arm with a wide range of motion
- Gas-spring height adjustment cylinder
- Supports displays from 12 to 24" (11lbs / 5kg capacity)
- 360° rotation around the support post and at the elbow
- +/-90° Tilt and +/-90° Pan
- Maximum arm extension of 22.05in (560mm)
- Landscape to portrait screen rotation
- Includes convertible desk / grommet-mount clamp
- Clamp fits desks up to 2.95in (75mm) thick
- Integrated cable management

Technical Specifications

Warranty	2 Years
# of displays supported	1
Mounting Options	Desk / Grommet Clamp
One-touch height adjustment	Yes
VESA Hole Pattern(s)	75x75 mm
VESA Hole Pattern(s)	100x100 mm
Wallmountable	No
Display Rotation	360°
Height Adjustment	Yes
Maximum Arm Extension	22 in [560 mm]
Maximum Display Size	24in
Mounting Surface Thickness	0.39 - 2.95in (10 - 75mm)
Pan	+/- 90°
Swivel / Pivot	360° around the support post 360° at the elbow
Tilt	+/- 90°
Weight Capacity	11 lb [5 kg]
Color	Black
Enclosure Type	Steel and Plastic
Product Weight	5.1 lb [2.3 kg]
Shipping (Package) Weight	6 lb [2.7 kg]
Included in Package	1 - Gas Spring Arm
Included in Package	1 - Extension Arm
Included in Package	1 - Support Pole
Included in Package	1 - Clamp
Included in Package	1 - Cover and Bolt
Included in Package	5 - Cable Covers
Included in Package	4 - Spacers
Included in Package	4 - M4x12mm Screws
Included in Package	4 - M4x25mm Screws
Included in Package	1 - Cable Clip
Included in Package	2 - Plastic Gasket Cushions
Included in Package	1 - 4mm Allen Wrench
Included in Package	1 - 6mm Allen Wrench

Included in Package	4 - Thumb screws
Included in Package	5 - Cable ties
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

