

# Compact Laser All-in-One

with Wireless Networking  
and Advanced Duplex



Brother Printers  
September 2013



MFC-L2740DW

brother  
at your side



## MFC-L2740dw Compact Laser All-in-One with Wireless Networking and Advanced Duplex

The Brother™ MFC-L2740dw is a reliable, affordable monochrome laser all-in-one with an up to 35-page automatic document feeder for home or small office use. This desk-friendly, compact all-in-one has an up to 250-sheet capacity tray, connects with ease via wireless networking or Ethernet, and prints and copies at up to 32ppm. Automatic duplex printing, plus single-pass duplex scanning and copying.

### Specifications:

<b>Print Technology</b>	Electrophotographic Laser
<b>LCD Display (type/size)</b>	2.7" Color TouchScreen
<b>Paper Size (maximum)</b>	Paper Tray: Up to 8.5" x 14" (legal) Manual Feed Slot: 3" to 8.5" (W), 5" to 14" (L)
<b>Print Speed (maximum)</b>	Up to 32ppm
<b>Print Resolution (maximum)</b>	Up to 2400 x 600 dpi
<b>Emulations</b>	PCL6, BR-Script3 <sup>‡</sup>
<b>Memory (std./max.)</b>	64MB / 64MB
<b>Duplex Printing Capability</b>	Yes
<b>Paper Input Capacity (maximum)<sup>™</sup></b>	250-sheet capacity paper tray, plus a single-sheet manual feed slot
<b>Output Capacity (maximum)<sup>™</sup></b>	100 sheets (face down), 1 sheet (face up)
<b>Auto Document Feeder<sup>™</sup></b>	Up to 35 pages
<b>Standard Interfaces</b>	Wireless 802.11b/g/n, Ethernet, Hi-Speed USB 2.0
<b>Copy Speed (maximum)</b>	Up to 32cpm
<b>Automatic Duplex Scan/Copy</b>	Yes
<b>Copy Resolution (maximum)</b>	600 x 600 dpi
<b>Copy Reduction/Enlargement</b>	25% - 400% in 1% increments
<b>Copy Options</b>	Sorting, N-in-1, Multi-copying (up to 99), ID copy
<b>Scanner Type</b>	Color Flatbed with ADF
<b>Document Glass Size</b>	8.5" x 11" (letter)
<b>Scan Resolution (maximum)</b>	Optical: Up to 600 x 2400 dpi <sup>4</sup> Interpolated: Up to 19200 x 19200 dpi
<b>Scan To Capability</b>	File, Image, E-mail, OCR, FTP, E-mail Server <sup>1</sup> , Microsoft® SharePoint <sup>®</sup> *, Cloud (Web Connect <sup>ν</sup> )
<b>Web Connect<sup>ν</sup></b>	DROPBOX, GOOGLE DRIVE™, EVERNOTE®, ONEDRIVE, ONENOTE, BOX, FACEBOOK™, FLICKR® and PICASA Web Albums™
<b>Brother Cloud Apps<sup>†</sup></b>	Office Print, Outline&Copy, Outline&Scan, Easy Scan to E-mail, NoteScan
<b>Document Viewer / OCR Software</b>	Nuance™ PaperPort™ 12SE w/ OCR for Windows® Presto!® PageManager®9 w/ OCR for Mac® (by download)
<b>Fax Page Memory (maximum)</b>	Up to 500 pages <sup>2</sup>
<b>Speed Dial Locations</b>	200
<b>PC Fax Capability<sup>3</sup></b>	Yes
<b>Operating Systems Compatibility<sup>o</sup></b>	Windows®: XP Home / XP Professional / XP Professional x64 Edition / Windows Vista® / Windows® 7, 8, 8.1 / Windows Server® 2003 (32 / 64 bit) / 2008 / 2008 R2 / 2012 / 2012 R2 Mac® OS X® v10.7.5, 10.8.x, 10.9.x Linux
<b>Mobile Device Compatibility<sup>‡</sup></b>	AirPrint™, Google Cloud Print™, Brother™ iPrint&Scan, Cortado Workplace, Wi-Fi Direct®
<b>Warranty</b>	1-year limited warranty

### Key Features at a Glance:

- Fast, high-quality printing and copying at up to 32ppm
- Flexible connectivity via Wireless 802.11b/g/n, Ethernet and Hi-Speed USB 2.0 interfaces
- Wireless printing from your mobile device via<sup>‡</sup>: AirPrint™, Google Cloud Print™, Brother™ iPrint&Scan, Cortado Workplace and Wi-Fi Direct®
- 2.7" Color TouchScreen Display - Offers intuitive navigation and easy scanning to popular cloud services<sup>ν</sup>
- Automatic duplex printing for creating professional two-sided documents
- Scans both sides of the page in a single-pass for fast, two-sided copying, scanning, faxing
- Offers 'scan to' features including ID Scan\*, Blank page skip and more
- 250-sheet capacity tray adjustable for letter or legal size paper, plus a manual feed slot for envelope printing
- Helps lower operating costs with High-yield 2,600-page\* replacement toner cartridge available\*
- One year limited warranty with free phone support for the life of your product

### Supplies & Accessories\*:

TN-630	Standard Yield Toner (approx. 1,200 pages) <sup>ν</sup>
TN-660	High-Yield Toner (approx. 2,600 pages) <sup>ν</sup>
DR-630	Drum Unit (approx. 12,000 pages) <sup>ν</sup>
BP60MPLTR	Letter-size Multi Purpose Paper (500 sheets)



### Logistics Information:

<b>UPC Code</b>	012502638896
<b>Unit Dimensions</b>	16.1" W x 15.7" D x 12.5" H
<b>Unit Weight / Carton Weight</b>	25.8 lbs. / 31.3 lbs.
<b>Carton Dimensions</b>	22.3" W x 20.4" D x 17.1" H

- ∞ Maximum capacity based on using 20 lb. paper  
 \* Additional purchase required  
 ν Approximate toner cartridge yield in accordance with ISO/IEC 19752 (letter/A4)  
 ^ Drum yield is approx., and may vary by type of use  
 ‡ PostScript®3™ compatible  
 † Requires a connection to a wireless network. See www.brother.com for details, availability and mobile device compatibility  
 o Server 2003 / 2008 / 2012 network printing only  
 ♦ Feature available using ControlCenter  
 ν Requires an Internet connection and an account with desired service. See www.brother.com for details.  
 1 Requires SMTP/POP3 mail server support. Download from http://solutions.brother.com  
 2 Using ITU-T Test Chart #1 with JBIG coding and std. resolution  
 3 PC Fax Receive not available for Mac users. B&W only  
 4 Max. dpi from glass; max 600x600 dpi from ADF  
 † Requires an Internet connection. See www.brother.com for details.



Join BrotherOffice

