Advantage Deluxe Flectrol

Designed to eliminate the extra step of finishing the screen with trim, the Advantage line of projection screens is designed with ceiling trim already in place. Once the screen is installed, the screen's trim conceals the rough opening eliminating the need to complete additional trim work.

Sliding installation brackets make it easy to attach the screen housing to the structure above the drop ceiling.

All Deluxe screens feature a closure door that hides the open space and screen in the ceiling, providing a cleaner aesthetic.

The Advantage® Deluxe Electrol® screen features simple in ceiling installation that can be done in two stages. The screen case can be installed during the rough-in construction stage and the fabric assembly can be completed during the finishing stage.

The Advantage Deluxe Electrol does not include the Tensioning Cable System. See the Tensioned Advantage Electrol Deluxe to ensure an even lateral tension.

Features

- Standard Low Voltage Control (LVC) to keep your screen operation flexible
- UL Plenum rated case
- White powder-coated closure doors and case for a clean aesthetic
- Available with SCB-100 and SCB-200 (RS-232 serial control board) or Video Projector Interface (screen trigger) built into the case
- Decora-style, three-button wall switch
- Standard black backing retains projected brightness
- Seamless surfaces in all models

Optional Accessories:

- Radio Frequency Wireless Remote Red Laser Pointers
- · Infrared Wireless Remote
- Locking Switch Cover Plate
- Green Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer



16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
45" x 80"	114 x 203	92"	234	96¼"	244
52" x 92"	132 x 234	106"	269	1081/4"	275
54" x 96"	137 x 244	110"	279	1121/4"	285
58" x 104"	147 x 264	119"	302	1201/4"	305
65" x 116"	165 x 295	133"	338	1321/4"	336
78" x 139"	198 x 353	159"	404	1561/4"	397
90" x 160"	229 x 406	184"	467	1761/4"	448

16:10 Wide Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
50" x 80"	127 x 203	94"	239	96¼"	244
57½" x 92"	146 x 234	109"	277	108¼"	275
60" x 96"	152 x 244	113"	287	1121/4"	285
65" x 104"	165 x 264	123"	312	1201/4"	305
69" x 110"	175 x 279	130"	330	1261/4"	321
72½" x 116"	184 x 295	137"	348	1321/4"	336
87" x 139"	221 x 353	164"	417	1561/4"	397

4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
43" x 57"	109 x 145	72"	183	721/4"	184
50" x 67"	127 x 170	84"	213	821/4"	209
57" x 77"	145 x 196	96"	244	96¼"	244
60" x 80"	152 x 203	100"	254	961/4"	244
69" x 92"	175 x 234	120"	305	1081/4"	275
87" x 116"	221 x 295	150"	381	1321/4"	336
105" x 140"	267 x 356	180"	457	1561/4"	397
120" x 160"	305 x 406	200"	508	1761/4"	448





Matte WhiteHalf Angle: 60° Gain: 1.0



High Contrast Matte White Half Angle: 50° Gain: 1.1



Video Spectra 1.5 Half Angle: 35° Gain: 1.5



Silver Lite 2.5 Half Angle: 25° Gain: 2.5

Product images







Case Profile

In Ceiling (Closed)

In Ceiling (Open)



A Milestone AV Technologies Brand

3100 North Detroit Street Warsaw, Indiana 46582 P: 574.267.8101 or 800.622.3737 F: 574.267.7804 or 877.325.4832 E: info@da-lite.com www.da-lite.com

DL-0417 07.14