

Contour Electrol

The Contour® Electrol® is the latest ceiling or wall-mounted electric screen offering simple installation. A variety of finishes and veneer options make this a seamless addition to any room.

This screen does not include the Tensioning Cable System. See Tensioned Contour Electrol for this feature.



Features

- Standard Silent Drive System to keep your screen whisper quiet (sizes up to 10x10)
- Standard Low Voltage Control (LVC) to keep your screen operation flexible
- Simple Installation with a new installation kit and user-friendly packaging to keep you on schedule
- Support includes a comprehensive five-year warranty to keep you confident in your purchase
- Available with SCB-100 and SCB-200 (RS-232 serial control board) or Video Projector Interface (screen trigger) built into the case
- Decora-style, three-button wall switch
- Standard black backing retains projected brightness
- Seamless surfaces
- Standard white powder-coated aluminum finish; available in black, graphite or veneer upon request

Optional Accessories:

- Radio Frequency Wireless Remote
- Infrared Wireless Remote
- Locking Switch Cover Plate
- Red Laser Pointers
- Green Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer

16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
45" x 80"	114 x 203	92"	234	93¾"	238
52" x 92"	132 x 234	106"	269	105¾"	269
54" x 96"	137 x 244	110"	279	109¾"	279
58" x 104"	147 x 264	119"	302	117¾"	299
65" x 116"	165 x 295	133"	338	129¾"	330
78" x 139"	198 x 353	159"	404	153¾"	391
90" x 160"	229 x 406	184"	467	173¾"	441

16:10 Wide Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
50" x 80"	127 x 203	94"	239	93¾"	238
57½" x 92"	146 x 234	109"	277	105¾"	269
60" x 96"	152 x 244	113"	287	109¾"	279
65" x 104"	165 x 264	123"	312	117¾"	299
69" x 110"	175 x 279	130"	330	123¾"	314
72½" x 116"	184 x 295	137"	348	129¾"	330
87" x 139"	221 x 353	164"	417	153¾"	391
100" x 160"	254 x 406	189"	480	173¾"	441

4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
43" x 57"	109 x 145	72"	183	69¾"	177
50" x 67"	127 x 170	84"	213	79¾"	203
57" x 77"	145 x 196	96"	244	93¾"	238
60" x 80"	152 x 203	100"	254	93¾"	238
69" x 92"	175 x 234	120"	305	105¾"	269
87" x 116"	221 x 295	150"	381	129¾"	330
105" x 140"	267 x 356	180"	457	153¾"	391
120" x 160"	305 x 406	200"	508	173¾"	441

Available with the Following Screen Surfaces



Matte White

Half Angle: 60° Gain: 1.0



High Contrast Matte White

Half Angle: 50° Gain: 1.1



Video Spectra 1.5

Half Angle: 35° Gain: 1.5



Silver Lite 2.5

Half Angle: 25° Gain: 2.5

Product images



White Case (Standard)



Black Case



Graphite Case



Dark Veneer Case



Light Veneer Case



A Milestone AV Technologies Brand

3100 North Detroit Street
Warsaw, Indiana 46582
P: 574.267.8101 or 800.622.3737
F: 574.267.7804 or 877.325.4832
E: info@da-lite.com
www.da-lite.com

DL-0441 07:14

© 2014 Milestone AV Technologies LLC. Printed in U.S.A.