Tensioned Professional Electrol

For larger venue installs, the Tensioned Professional Electrol® is a tensioned screen that can be ceiling recessed, wall mounted or suspended from the ceiling. The screen features a wooden housing with adjustable brackets that can be used in any type of installation.

Available in sizes up to 21'8" wide

The Tensioned Professional Electrol does not include the ceiling trim flange or painted automatic closure door. See Tensioned Large Advantage Electrol for easy installation or Tensioned Large Advantage Deluxe Electrol for easy installation and the aesthetic of the white automatic closure door.


Features

- Slim-Tab, a lower profile and stronger tab design to keep your screen perfectly taut
- Smooth Roll Technology to keep your screen perfectly flat
- Tensioning Cable System to prevent warping and ensure even lateral tension
- Three-position, Decora-style switch
- Standard black backing retains projected brightness on front projection surfaces
- · Black painted case
- · Seamless surfaces in all models

Optional Accessories:

- Single Motor Low Voltage Control System
- Radio Frequency Wireless Remote
 Radio Frequency Wireless Remote Single Motor LVC
- Infrared Wireless Remote Single Motor LVC
- Video Projector Interface
- SCB-100
- Key Operated, 110 Volt Switch
- · Locking Switch Cover Plate

- Dual Motor Low Voltage Control System
- Dual Motor LVC
- · Infrared Wireless Remote Dual Motor LVC
- Red Laser Pointers
- Green Laser Pointers
- RF PowerPoint Remote with Green Laser Pointer



16:9 HDTV Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
92" x 164"	234 x 417	188"	478	185¾"	472
108" x 192"	274 x 488	220"	559	2151/4"	547
121" x 216"	307 x 549	247"	627	241¼"	613
135" x 240"	343 x 610	275"	699	267¼"	679
146" x 260"	372 x 660	298"	757	288¾"	733

4:3 Video Format

Viewing Area (H x W)		Nominal Diagonal		Overall Case Length	
in.	cm	in.	cm	in.	cm
108" x 144"	274 x 366	180"	457	167¼"	425
120" x 160"	305 x 406	200"	508	184¾"	469
126" x 168"	320 x 427	210"	533	193¾"	492
132" x 176"	335 x 447	220"	559	202¾"	515
144" x 192"	366 x 488	240"	610	2201/4"	559
162" x 216"	411 x 549	270"	686	245¾"	624





Da-Mat Half Angle: 60° Gain: 1.0



High Contrast Da-Mat Half Angle: 45° Gain: 0.8



Cinema Vision Half Angle: 45° Gain: 1.3



High Contrast Cinema Vision Half Angle: 50° Gain: 1.1



Pearlescent Half Angle: 40° Gain: 1.5



Dual Vision Half Angle: 65° Gain: 0.9



Da-Tex Half Angle: 30° Gain: 1.3



A Milestone AV Technologies Brand

3100 North Detroit Street Warsaw, Indiana 46582 P: 574.267.8101 or 800.622.3737 F: 574.267.7804 or 877.325.4832 E: info@da-lite.com www.da-lite.com

DL-0429 07.14

© 2014 Milestone AV Technologies LLC. Printed in U.S.A.