낃Quam system 5/25RS


SYSTEM 5/25RS is a complete, UL Listed, shallow depth, lightweight, 1' x 2' ceiling tile replacement loudspeaker system consisting of an 8" O.D., dual cone loudspeaker with a 5 oz. magnet and a 4W, 25V, rotary select transformer. The molded fiber enclosure is 617 CID. The SYSTEM 5/25RS has a powder coated steel baffle with standard perforation and four (4) seismic tie-off points. The cable clamp and one (1), 24", "T" rail are included. No assembly required.




APPLICATION	Intended Use: Program Material: Installation: City of Chicago Approved:	Indoor environment Signal tones, voice, and music Mounted parallel to floor plane in a 24" wide suspended ceiling tile grid Material and construction permits use where ceiling plenum is part of the air handling system
AUDIO	Average Sensitivity:	92dB SPL, 1W/1M
PERFORMANCE	Loudspeaker Power Rating:	12W RMS, EIA 426A Standard
	Maximum Power Rating:	15W @ 8 Ohms
	Calculated Output:	98dB SPL, 4W/1M
	Magnet Type & Weight:	BeFe Ceramic, 5 oz. Nominal
	Frequency Response:	65Hz - 17kHz, EIA 426A Standard
	Nominal Coverage Angle:	100° Included Angle, -6dB/2kHz, Half Space
	Audio Connection:	7 ½", Color-coded, Pre-tinned Leads
COMPONENT	Dimension:	3 ½" (H) x 23 ¹³ / ₁₆ " (W) x 11 ¹³ / ₁₆ " (D)
	Weight:	4.05 lbs.
	Loudspeaker Model:	8C5PAX
	Loudspeaker Specs:	8" O.D. loudspeaker, 5 oz. magnet
	Transformer:	4W, 25V, rotary select with 5 taps (0.25W, 0.50W, 1W, 2W, 4W)
	Integral Enclosure:	617 CID molded fiber
	Grille:	Standard perforated steel with four (4) seismic tie-off points
	Finish:	White powder coat finish
CERTIFICATION	UL Listed 1480	When installed with supplied installation instructions and requirements of

UL Listed 2043

When installed with supplied installation instructions and requirements of NEC /AHJ. (UEAY, UEAY7- Canada) Suitable for use in air-handling spaces





Quam Nichols Company | 234 East Marquette Road | Chicago, IL. 60637 | t: 800-633-3669 | f: 888-633-3669 | e: NeedNow@QNC.com | QuamSpeakers.com @2020 Quam Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice. | v.2014

