

# EPHD08


## 8 Channel Full HDcctv DVR



### Features

- Choice of 1080p or 720p HDcctv camera support for superlative image clarity
- MobileFocus: Supports iPhone®/iPad®/Android™/Blackberry®\*
- MobileView: Supports additional PDAs, Smartphones, Safari®
- Virtual Real Time Recording: 15 FPS @ 1080p, Real Time Recording: 30 FPS @ 720
- Dual Stream Controls: Record at a higher resolution but view at a lower resolution online/mobile device for faster viewing
- 2x, 4x, 8x, 16x zoom on local and remote live & playback
- Independent Channel Controls: Frame Rate/Record Quality
- Recording rate can be changed at different times of the day via scheduling
- Simultaneous Pentaplex Operation at DVR & Online: Live/Recording/Playback/Archiving/Remote View
- H.264 Compression for efficient disk and network utilization
- FREE DDNS Service Hosted by EverFocus for EASY Networking Options
- Main Monitor: Simultaneous Viewing at 1080 x 1080 on HDMI and VGA
- Built-in DVD burner
- Supports External Hard Drive Storage via eSATA
- Per-Camera Audio Channels
- Multiple control inputs: mouse/front panel/IR remote controller/EKB500 keyboard
- User Friendly GUI with graphical icons and visual indicators
- Local & Remote On-Screen PTZ Control
- Built-in recording calculator estimates storage capacity based on settings
- Smart Search: quickly identify motion in areas of interest from recorded video
- Event Search: Search date/time by an event (alarm, motion, video loss)
- Express Playback & Search: Point, Click, Drag playback bar for Instant Viewing
- Express Setup: A unique menu option for quick & easy installation
- Web Archive: From a PC you can copy video onto the PC
- 3 different administration levels to restrict or allow access to DVR controls (DVR/Online Interface)
- Online Web interface: Allows 10-users to simultaneously view online from a browser
- Rack Mountable (19") includes Rack Ears
- IR Remote & USB Mouse included

### Dimensions: mm/in



### Ordering Info

- EPHD08/4: 8 Ch HDcctv DVR, 4 TB, DVD
- EPHD08/8: 8 Ch. HDcctv DVR, 8 TB, DVD



**HDcctv**

### Specifications

| Part Number                  | EPHD08   |
|------------------------------|--|
| Channels                     | 8 HDcctv channels  |
| HD Recording & Playback Rate | 1080: 15/12.5 FPS per camera<br>720: 30/25 FPS per camera  |
| Export Video                 | Built-in DVD Burner, USB Port  |
| Internal HDD Max             | Supports up to 8 TB (4 HDD)  |
| External HDD Max             | 1 eSATA Supports up to 8 TB (4 HDD)  |
| HDD Combined Max             | 16 TB Combined Total   |
| Audio Input                  | One per channel  |
| Audio Output                 | 1-Output   |
| RS-485                       | 1 RS-485 (3 Terminal Connector)  |
| User Interface               | GUI (Graphical User Interface)   |
| Mobile Viewing               | Mobile Focus   |
| Recording Compression        | H.264  |
| Dual Streaming               | View remotely with reduced or full resolution bandwidth while recording full 1080/720            |
| Operating System             | Embedded Linux   |
| Network/Protocol             | Gigabit Ethernet, TCP-IP/DHCP/PPPoE/DDNS/UDP/SMTP/SSL/HTTP                                       |
| Pentaplex Operation          | Simultaneous Live, Recording, Playback, Archive and Remote Viewing                               |
| USB                          | 3 USB 2.0 port (2 on Front Panel, 1 on Back Panel)   |
| Main Monitor Output          | Main Monitor 1080p HDMI socket (Type A 19 pin F)   VGA: 1920x1080 @ 60Hz (D-Sub socket 15 pin F) |
| Playback Search              | Date/Time & Event, Smart Search  |
| Event Log                    | Yes  |
| Watch Dog Timer              | Yes  |
| Quick Archive                | Archive video instantly (to USB/DVD) while playing back  |
| Motion Detection             | Yes  |
| Video Loss Detection         | Yes  |
| Schedule Setting             | Supports Express and Advanced Schedule Setting   |
| Recording Modes              | Continuous, Schedule, and Event  |
| Video Pause                  | Yes  |
| User Access                  | 3 Levels of User Access Support  |
| Control PTZ via OSD          | Locally/Remote via OSD   |
| Supported PTZ Protocols      | EverFocus, Pelco D, Pelco P, Samsung, Transparent  |
| Language Support             | Multi-language support   |
| Alarm-In                     | 8 alarm inputs   |
| Alarm-Out                    | 2 alarm outputs- Form "C" rated at 30VDC, 1A   |
| Power Source                 | 100VAC-240VAC  |
| Power Consumption            | 130 W max. with 4x HDDs  |
| Environmental                | 32°F~104°F(20-80% humidity)  0°C~40°C  |
| Dimensions                   | 16.2" x 16.9" x 3.5"   |
| Certifications               | CE, FCC, UL  |

Note: \*Select Blackberry models and versions.

