

SP4AWET black, with transformer


SP4AWETW white, with transformer

Features

- Rounded, stylish design
- Horizontal-swivel mounting bracket
- Weather-resistant design
- 70/25V selectable transformer
- 5 year warranty
- NDAA Compliant*



Sold individually



Speaker Specifications

Model	SP4AWET/SP4AWETW
RMS Power	25W
Max Power	40W
Transformer Type	70/25V (selectable)
Transformer Power Taps	20W, 15W, 10W, 5W
Termination Type	Press terminal
Sensitivity (1W/1M)	84dB
Maximum SPL (Pmax/1M)	104dB
Driver Impedance	8 Ohms
Magnet	9 oz. ferrite
Frequency Response Range	74Hz ~ 20kHz
Dispersion @ 1000Hz	180° Conical
Drivers	4" Mica/Polypropylene woofer 0.75" Silk tweeter
Speaker Dimensions	6" (W) x 9.5" (H) x 6.5" (D)
Weight	5.5lbs
Material	Body: High impact polystyrene Grille: Treated metal Bracket: Treated metal

**NDAA
COMPLIANT**

*Products are in compliance with NDAA Section 889 Part B Guidelines