

G80-1800



Models may vary from the image shown

Small dimensions and top performance!

Standard? Yes! Boring? No - the compact design of the 19 inch PC keyboard is highly distinctive. For space-saving applications and optimum longevity requirements.

Key Benefits

- Individual keys with Gold Crosspoint contacts (MX technology)
- Codeset 3 support (PS/2 connection only) e.g. for Unix computers
- Perfect key feeling
- High quality and compact 19" PC keyboard - space-saving and ergonomic
- High-quality keyboard for outstanding writing performance, fulfilling even the highest demands
- Extremely high service life of individual keys

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing Color:

Product dependant, see table "Models"

Key Color:

Product dependant, see table "Models"

Weight (product):

approx. 920 g / 2.03 lb

Total Weight (with packaging):

approx. 1190 g / approx. 2.62 lb

Cable Length:

approx. 1.75 m / approx. 5.74 ft

Storage Temperature:

-20°C to 60°C / -4° F to 140° F

Operating Temperature:

0°C to 50°C / 32° F to 122° F

Current Consumption:

typ. 16 mA

Interface:

- USB (PS/2 via adapter)

Product Approvals:

- UL Recognized Component Approval
- CE
- FCC
- VDE



System Requirements:

- USB or PS/2 connection

Box Contents:

- G80-1800
- Printed instructions

Dimensions (product):


approx. 405 x 180 x 44 mm / approx. 15.94 x 7.09 x 1.73 in

Packaging Dimensions:

approx. 460 x 270 x 50 mm / approx. 18.11 x 10.63 x 1.97 in

Keyboard:

- Key Technology: MX
- Service life, standard key: > 50 million key operations
- Operation Characteristics: BLACK SWITCH Linear (60 cN)



- Inscription Technology: Laser
- Inscription Layout: Standard
- Number of Keys: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 18
- Number of master packages per pallet: 6

Warranty:

3-year limited manufacturer's guarantee

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

| |
|---|
| Errors, technical changes and delivery delays may occur. Technical information refers only to the specifications of the products. Features may differ from the information provided. |
|---|

Models:

(possible country/layout versions, others available on request)

| | Product Name | Order Number | EAN Code | Layout (country or language) | Housing Color | Key Color | Number of Keys |
|---|--------------|-----------------|---------------|------------------------------|---------------|------------|----------------|
| 1 | G80-1800 | G80-1800LPCDE-0 | 4025112064968 | Germany | light grey | light grey | 105 |
| 2 | G80-1800 | G80-1800LPCDE-2 | 4025112065040 | Germany | black | black | 105 |
| 3 | G80-1800 | G80-1800LPCES-0 | 4025112072000 | Spain | light grey | light grey | 105 |
| 4 | G80-1800 | G80-1800LPCEU-0 | 4025112064937 | US English with EURO symbol | light grey | light grey | 104 |
| 5 | G80-1800 | G80-1800LPCEU-2 | 4025112064975 | US English with EURO symbol | black | black | 104 |
| 6 | G80-1800 | G80-1800LPCFR-0 | 4025112064951 | France | light grey | light grey | 105 |
| 7 | G80-1800 | G80-1800LPCGB-0 | 4025112064944 | UK | light grey | light grey | 105 |
| 8 | G80-1800 | G80-1800LPCGB-2 | 4025112072031 | UK | black | black | 105 |
| 9 | G80-1800 | G80-1800LPCIT-0 | 4025112073335 | Italy | light grey | light grey | 105 |