


960H Dual Voltage Indoor Dome Camera with Built-In IR LEDs

- HLED33D7B** 3.6mm fixed lens, black housing
- HLED33D7W** 3.6mm fixed lens, white housing
- HLED33D1B** 2.8-12mm auto iris varifocal lens, black housing
- HLED33D1W** 2.8-12mm auto iris varifocal lens, white housing

Features

- 700 TV lines of resolution
- IR Range: 65'
- Smart DNR reduces noise in low light
- Smart IR reduces saturation of objects within close proximity to IR LEDs
- 3-axis design, both wall and ceiling mountable
- Digital wide dynamic range
- OSD for camera setting adjustments
- 12VDC/24VAC dual voltage operation
- 5 year warranty



Specifications

Image Sensor 1/3" color 960H CCD

Resolution..... 700 TV lines

Minimum Illumination..... 0 lux with IR on

S/N Ratio 50dB

Effective Pixels 976 (H) x 494 (V)

Total Pixels 1020 (H) x 508 (V)

Shutter 1/60 sec – 1/120,000 sec

Number of IR LEDs 24

IR Range 65 ft. (depending on scene reflection)

OSD..... Yes

Synchronization Internal

Privacy..... On / Off (8 zones)

Motion Detection..... On / Off (4 zones)

Mirror On / Off

DNR..... High / Middle / Low / Off

White Balance ATW / Push / Manual

Image..... BLC / HLC / D-WDR / Defog

AGC..... Level adjustable (0-20)

TV System..... NTSC

Housing High impact ABS

Operating Temperature.. 14° F - 122° F

Power Supply 12VDC, 24VAC (power supply not included)

Power Consumption 250mA

Dimensions..... 4.4" (Dia.) x 3.4" (H)

Weight 8 oz.

Included in Package Main unit, mounting screws, test monitor lead, DC lead, user manual

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 6/17/14



Optional Accessories



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply